



Plastic Bottle, 15 fl. oz.
078698217567

Plastic Bottle, 1 gal.
078698216959

WINDSHIELD WASHER SOLVENT WITH ANTI-FREEZE

WWCS15, WW CZ-1G (SUMMER FORMULAS)

GUNK® Windshield Washer Fluid Concentrate makes 55 gallons of ready-to-use streak-free windshield washer fluid. Won't harm automotive finishes yet quickly cuts through the toughest dirt, bird droppings and insect deposits. An environmentally preferable product because it is zero-VOC, formulated with readily biodegradable ingredients (by Modified Sturm Test), contains no butyl cellosolve, no phosphates, and no nonylphenol surfactants. Contains no alcohol or antifreeze agents.

APPLICATIONS:

- Heavy Duty Ammonia Formula
- Streak Free, Zero VOC

DIRECTIONS: Read entire label before using this product. Dilute one gallon concentrate with 54 gallons of water to make 55 gallons of heavy-duty ready-to-use windshield washer fluid. Consult Material Safety Data Sheet (MSDS) prior to using this product. Visit gunk.com for MSDS.

STORAGE, HANDLING & DISPOSAL: Store in cool, dry area. Do not expose the container to heat, sparks, or flame. Use with adequate ventilation. This water-based product will conduct electricity. Keep contents away from electrical sources including battery terminals, solenoids, electrical panels, and electronic components. Do not apply to energized equipment. Failure to observe this warning may result in serious injury from electrical shock. Dispose of product residue and empty container in accordance with all local, state, and federal laws and regulations. Empty containers are recyclable: consult your local recycling authority.

DANGER: EYE IRRITANT.

FIRST AID: EYE CONTACT: Flush thoroughly with water for 15 minutes while lifting eyelids and get prompt medical attention. SKIN CONTACT: Wash with soap and water. If irritation develops, get prompt medical attention. INGESTION: DO NOT INDUCE VOMITING. Call Poison Control Center, Physician, or Hospital Emergency Room immediately.

KEEP AWAY FROM CHILDREN AND ANIMALS

NOTICE: While this information is presented in good faith and believed to be accurate, Radiator Specialty Company does not guarantee satisfactory results from reliance thereon. The data is offered solely for your information and Radiator Specialty Company disclaims all liability for any loss or damage from its use. Thoroughly test any application according to the product directions and independently conclude satisfactory performance. Nothing contained herein is to be construed as a recommendation to use the product in violation of any patent.