

INDUSTRIAL HIGH OUTPUT HAND DRYERS

TECHNICAL data sheet

INDUSTRIAL HIGH OUTPUT HAND DRYERS

This series hand dryer is the industry standard for high speed hand dryers. Available in automatic or push-button. Longest life of all high speed hand dryers. Durable and vandal resistant porcelain enamel finishes. Stationary nozzle can be adjusted to swivel. Dryers are GreenSpec listed. Runs 2X faster and uses only 50% of the energy of standard dryers.



1GVL5, 3NXE9



4ZA64, 4ZA65

PRODUCT FEATURES AND BENEFITS

- Automatic or push-button operation
- Longest life of high speed hand dryers
- 15 second dry time; 2X faster than traditional dryers
- Uses only 1/2 the energy of standard dryers
- Low sound level
- Durable and vandal resistant
- Classic style design
- Surface or recess mounted with ADA compliance

DESIGN FEATURES

DRYER

- Automatic unit - Activated by infrared sensor, automatic drying cycle.
- Push-button unit - Activated by electro-mechanical timer with 25 Amp switch and 20 second cycle.
- Incorporates a 1600 watt Nichrome wire heating element Protected by an automatic-resetting, thermal cutoff
- Provides a 50°F temperature rise
- IPX1 ingress protection

MOTOR

- Thermally-protected, universal brush-type motor operating at 12,000 RPM
- Delivering 238 CFM air flow at a velocity of 8,624 LFM (98 MPH)

MATERIALS

- Cover material: Cast Iron with porcelain enamel finish. Optional 14GA polished or brushed finish #304S.S. or epoxy enamel finish C.R. Steel.

PRODUCT SPECIFICATIONS



	115 V	208 - 230 V
Amps	20	10
Watts	2300	2300
Hz	60	60

DRYER DIMENSIONS:

Unit Size (HxWxD) - 9.5" x 11.3" x 8.3"
 Unit Weight - Cast Iron 27.3 lbs, Steel 15.8 lbs
 Shipping Size (HxWxD) - 12.5" x 14.4" x 10.1"
 Shipping Weight - Cast Iron 29.8 lbs, Steel 18 lbs

PRODUCT DIMENSION DRAWINGS

CERTIFICATION APPROVED



IPX1



SKU NO.	NOZZLE TYPE	COVER MATERIAL	COVER FINISH	OPERATION	VOLTAGE	AMPS	DRY TIME
DAYTON INDUSTRIAL HIGH OUTPUT HAND DRYER							
4ZA64	Swivel	Cast Iron	Porcelain Enamel	Push Button	120 V	20	15 sec.
4ZA65	Swivel	Cast Iron	Porcelain Enamel	Push Button	208/230 V	10/10	15 sec.
1GVL5	Fixed	Cast Iron	Porcelain Enamel	Automatic	120 V	20	15 sec.
3NXE9	Fixed	Steel	Epoxy Enamel	Automatic	120 V	20	15 sec.

Find it at Grainger.

Call or visit your local branch or go to grainger.com/dayton for complete product line information.

