




45-Gallon Manual Closing Doors



Model No.	SC45-MC-Y,-R,-G,-B,-PL
Color	Yellow (-Y), Red (-R), Green (-G), Blue (-B), Platinum (-PL)
Material Specifications	18-Gauge Steel with Reinforced Double-Wall Construction
Verification	Factory-Verified to UL 1275 Flammable Liquid Storage Performance Criteria
OSHA	Yes
NFPA 30	Yes
Door Style	Double Door Manual Close
UPC	033983097231 (Y) 033983097286 (B) 033983097323 (PL) 033983097262 (R) 033983097309 (G)
Dimensions, Exterior	43" W x 18" D x 65" H
Dimensions, Interior	39.8" W x 14.7" D x 60.3" H
Number of Doors	2
Number of Shelves	2
Lock	Keyed Cam Lock
Gallon Capacity	45
Liter Capacity	170 L
Replacement Shelf Model No.	X410275
Shelf Depth	14.2"
Net Weight, lbs.	296
Net Weight, kgs.	134
Adjustable Shelves	Yes
Warranty	10 Yr. Structural- Free After Fire Replacement Guarantee