

# Material Safety Data Sheet

HAZARD WARNINGS	RISK PHRASES	PROTECTIVE CLOTHING
	<b>Lachrymator.</b> Harmful compound, minimize exposure. Irritating to skin, eyes, and the respiratory system. Store under nitrogen.	

## Section I. Chemical Product and Company Identification

Chemical Name	<b>1-Naphthaldehyde (alpha-)</b>		
Catalog Number	N0002	Supplier	TCl America 9211 N. Harbortgate St. Portland OR 1-800-423-8616
Synonym	1-Formylnaphthalene		
Chemical Formula	C <sub>10</sub> H <sub>7</sub> CHO		
CAS Number	66-77-3	In case of Emergency Call	<b>Chemtrec®</b> <b>(800) 424-9300 (U.S.)</b> <b>(703) 527-3887 (International)</b>

## Section II. Composition and Information on Ingredients

Chemical Name	CAS Number	Percent (%)	TLV/PEL	Toxicology Data
1-Naphthaldehyde (alpha-)	66-77-3	Min. 95.0 (T)	Not available.	Mouse LD <sub>50</sub> (unknown) 1100 mg/kg Guinea pig LD <sub>50</sub> (dermal) >20 ml/kg Rat LD <sub>50</sub> (oral) 667mg/kg

## Section III. Hazards Identification

Acute Health Effects	Harmful if ingested or inhaled. Minimize exposure to this material. Severe overexposure can result in injury or death. Severely irritating to the lungs, mucous membranes, and respiratory tract. Always wear an OSHA/MSHA approved respirator when working with this material. Irritating to eyes and skin on contact. Inhalation causes irritation of the lungs and respiratory system. Inflammation of the eye is characterized by redness, watering, and itching. Skin inflammation is characterized by itching, scaling, reddening, or, occasionally, blistering. Follow safe industrial hygiene practices and always wear proper protective equipment when handling this compound.
Chronic Health Effects	<b>CARCINOGENIC EFFECTS</b> : Not available. <b>MUTAGENIC EFFECTS</b> : Not available. <b>TERATOGENIC EFFECTS</b> : Not available. <b>DEVELOPMENTAL TOXICITY</b> Not available. There is no known effect from chronic exposure to this product. Repeated or prolonged exposure to this compound is not known to aggravate existing medical conditions.

## Section IV. First Aid Measures

Eye Contact	Check for and remove any contact lenses. DO NOT use an eye ointment. Flush eyes with running water for a minimum of 15 minutes, occasionally lifting the upper and lower eyelids. Seek medical attention. Treat symptomatically and supportively.
Skin Contact	After contact with skin, wash immediately with plenty of water. Gently and thoroughly wash the contaminated skin with running water and non-abrasive soap. Be particularly careful to clean folds, crevices, creases and groin. Cover the irritated skin with an emollient. Seek medical attention. Treat symptomatically and supportively. Wash any contaminated clothing before reusing.
Inhalation	If the victim is not breathing, perform artificial respiration. Loosen tight clothing such as a collar, tie, belt or waistband. If breathing is difficult, oxygen can be administered. Seek medical attention. Treat symptomatically and supportively.
Ingestion	INDUCE VOMITING by sticking finger in throat. Lower the head so that the vomit will not reenter the mouth and throat. Loosen tight clothing such as a collar, tie, belt, or waistband. If the victim is not breathing, administer artificial respiration. Examine the lips and mouth to ascertain whether the tissues are damaged, a possible indication that the toxic material was ingested; the absence of such signs, however, is not conclusive. Seek immediate medical attention and, if possible, show the chemical label. Treat symptomatically and supportively.

## Section V. Fire and Explosion Data

Flammability	Combustible.	Auto-Ignition	Not available.
Flash Points	112°C (233.6°F).	Flammable Limits	Not available.
Combustion Products	These products are toxic carbon oxides (CO, CO <sub>2</sub> ).		
Fire Hazards	No specific information is available regarding the flammability of this compound in the presence of various materials.		
Explosion Hazards	Risks of explosion of the product in presence of mechanical impact: Not available. Risks of explosion of the product in presence of static discharge: Not available. No additional information is available regarding the risks of explosion.		

Continued on Next Page

Emergency phone number (800) 424-9300

Fire Fighting Media  
and Instructions

66-77-3berNINGS(International)dent<sub>2</sub>, water spray or foam.  
LARGE FIRE: Use water spray, fog or foam. DO NOT use water jet.

### Section VI. Accidental Release Measures

Spill Cleanup  
Instructions

Harmful material. Irritating material. Lachrymatory material.  
Keep away from heat and sources of ignition. Mechanical exhaust required. Stop leak if without risk. Finish cleaning the spill by rinsing any contaminated surfaces with copious amounts of water. Consult federal, state, and/or local authorities for assistance on disposal.

### Section VII. Handling and Storage

Handling and Storage  
Information

HARMFUL. IRRITANT. LACHRYMATOR. STORE UNDER NITROGEN. Keep away from heat and sources of ignition. Mechanical exhaust required. When not in use, tightly seal the container and store in a dry, cool place. Avoid excessive heat and light. DO NOT ingest. Do not breathe gas, fumes, vapor or spray. In case of insufficient ventilation, wear suitable respiratory equipment. If ingested, seek medical advice immediately and show the container or the label. Treat symptomatically and supportively. Avoid contact with skin and eyes.  
Always store away from incompatible compounds such as oxidizing agents, alkalis (bases).

### Section VIII. Exposure Controls/Personal Protection

Engineering Controls

Provide exhaust ventilation or other engineering controls to keep the airborne concentrations of vapors below their respective threshold limit value. Ensure that eyewash station and safety shower is proximal to the work-station location.

Personal Protection

Splash goggles. Lab coat. Vapor respirator. Boots. Gloves. A MSHA/NIOSH approved respirator must be used to avoid inhalation of the product. Suggested protective clothing might not be sufficient; consult a specialist BEFORE handling this product.



Exposure Limits

Not available.

### Section IX. Physical and Chemical Properties

Physical state @ 20°C	Light-yellow liquid.	Solubility	Not available.
Specific Gravity	1.15 (water=1)		
Molecular Weight	156.18	Partition Coefficient	Not available.
Boiling Point	160 to 161 °C (320 to 321.8 °F) @ 15mmHg	Vapor Pressure	Not available.
Melting Point	1 to 2°C (33.8 to 35.6°F)	Vapor Density	>1 (Air = 1)
Refractive Index	Not available.	Volatility	Not available.
Critical Temperature	Not available.	Odor	Not available.
Viscosity	Not available.	Taste	Not available.

### Section X. Stability and Reactivity Data

Stability	This material is stable if stored under proper conditions. (See Section VII for instructions)
Conditions of Instability	Avoid excessive heat and light.
Incompatibilities	Reactive with oxidizing agents, alkalis (bases).

### Section XI. Toxicological Information

RTECS Number	QJ0190000
Routes of Exposure	Eye contact. Inhalation. Ingestion. Skin contact.
Toxicity Data	Mouse LD <sub>50</sub> (unknown) 1100 mg/kg Guinea pig LD <sub>50</sub> (dermal) >20 ml/kg Rat LD <sub>50</sub> (oral) 667mg/kg
Chronic Toxic Effects	<b>CARCINOGENIC EFFECTS</b> : Not available. <b>MUTAGENIC EFFECTS</b> : Not available. <b>TERATOGENIC EFFECTS</b> : Not available. <b>DEVELOPMENTAL TOXICITY</b> Not available. There is no known effect from chronic exposure to this product. Repeated or prolonged exposure to this compound is not known to aggravate existing medical conditions.
Acute Toxic Effects	Harmful if ingested or inhaled. Minimize exposure to this material. Severe overexposure can result in injury or death. Severely irritating to the lungs, mucous membranes, and respiratory tract. Always wear an OSHA/MSHA approved respirator when working with this material. Irritating to eyes and skin on contact. Inhalation causes irritation of the lungs and respiratory system. Inflammation of the eye is characterized by redness, watering, and itching. Skin inflammation is characterized by itching, scaling, reddening, or, occasionally, blistering. Follow safe industrial hygiene practices and always wear proper protective equipment when handling this compound.

Continued on Next Page

Emergency phone number (800) 424-9300

**Section XII. Ecological Information**

Ecotoxicity	Not available.
Environmental Fate	Not available.

**Section XIII. Disposal Considerations**

Waste Disposal	Recycle to process, if possible. Consult your local or regional authorities. You may be able to dissolve or mix material with a combustible solvent and burn in a chemical incinerator equipped with an afterburner and scrubber system. Observe all federal, state, and local regulations when disposing of this substance.
----------------	--

**Section XIV. Transport Information**

DOT Classification	Not a DOT controlled material (United States).
PIN Number	Not applicable.
Proper Shipping Name	Not applicable.
Packing Group (PG)	Not applicable.
DOT Pictograms	

**Section XV. Other Regulatory Information and Pictograms**

TSCA Chemical Inventory (EPA)	This compound is <b>ON</b> the EPA Toxic Substances Control Act (TSCA) inventory list.
WHMIS Classification (Canada)	WHMIS CLASS D-2A: Material causing other toxic effects (VERY TOXIC).
EINECS Number (EEC)	200-633-4
EEC Risk Statements	R36/37/38- Irritating to eyes, respiratory system and skin. R20/21/22- Harmful by inhalation, in contact with skin and if swallowed.
Japanese Regulatory Data	Not available.

**Section XVI. Other Information**

**Version 1.0**  
**Validated on 10/13/1997.**  
**Printed 2/26/2005.**

**Notice to Reader**

TCI laboratory chemicals are for research purposes only and are NOT intended for use as drugs, food additives, household, or pesticides. The information herein is believed to be correct, but does not claim to be all inclusive and should be used only as a guide. Neither the above named supplier nor any of its subsidiaries assumes any liability whatsoever for the accuracy or completeness of the information contained herein. Final determination of suitability of any material is the sole responsibility of the user. All chemical reagents must be handled with the recognition that their chemical, physiological, toxicological, and hazardous properties have not been fully investigated or determined. All chemical reagents should be handled only by individuals who are familiar with their potential hazards and who have been fully trained in proper safety, laboratory, and chemical handling procedures. Although certain hazards are described herein, we can not guarantee that these are the only hazards which exist. Our MSDS sheets are based only on data available at the time of shipping and are subject to change without notice as new information is obtained. Avoid long storage periods since the product is subject to degradation with age and may become more dangerous or hazardous. It is the responsibility of the user to request updated MSDS sheets for products that are stored for extended periods. Disposal of unused product must be undertaken by qualified personnel who are knowledgeable in all applicable regulations and follow all pertinent safety precautions including the use of appropriate protective equipment (e.g. protective goggles, protective clothing, breathing equipment, facial mask, fume hood). For proper handling and disposal, always comply with federal, state, and local regulations.