



TEGERA® 215

Learn more

CUT-RESISTANT GLOVE FOR PRECISION WORK

Cut-resistant glove designed for precision work, combining high protection and great dexterity. Made from full-grain goatskin and Kevlar® fibers, it provides cut resistance (Level C) while offering excellent fingertip sensitivity. Fully lined for comfort, the glove features reinforced index finger and fingertips to ensure precision during delicate tasks.

CHARACTERISTICS

- High level of protection
- Extremely good fingertip sensitivity
- Durable
- Perfect fit

FUNCTIONS

- Reinforced index finger
- Reinforced fingertips

Kevlar®

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.

PREVENTS RISK OF

Cut injuries, Abrasion injuries, Blisters, Grazes, Scratches, lacerations

PRIMARY ENVIRONMENTS OF USE

Cut risk environments, Harsh environments

PRIMARY AREAS OF USE

Assembly, Building and construction, Carpentry, Installation work, HVAC installation, Sheet-metal work, Tiling, Construction, Engineering, Transport work, Metalwork, Glass industry work, Wood industry work, Repair work

PRIMARY INDUSTRIES OF USE

Automotive repair and maintenance, Glass, ceramics and construction materials, Metal manufacturing and fabrication, Transport equipment manufacturing, Machinery and equipment manufacturing, Automotive manufacturing, Transportation and logistics, Electricity and gas supply, Building and construction, Mining and quarrying

TYPE OF WORK

Light weight

SPECIFICATION

TYPE All-round work gloves, Assembly gloves, Cut resistant gloves
CATEGORY Cat. II
PALM MATERIAL Full grain goatskin of top quality
BACK MATERIAL Polyester
LINING Fully lined
LINING MATERIAL KEVLAR® fiber
LENGTH 210-260 mm
DEXTERITY 5
COLOUR Grey
PAIRS PER: BUNDLE/CARTON 12/120
DISPLAY TYPE Thread
FASTENING Elasticated 180°
CUT RESISTANCE (EN ISO 13997) Cut resistance level C
CUT RESISTANCE (EN ISO 13997) TDM: 12.2 N
INNER MATERIAL SPECIFICATION Para-aramid
OUTER MATERIAL SPECIFICATION Leather, Polyester

COMPLIANCE

CE Cat. II
TP TC 019:2011

UKCA Cat. II
EN ISO 21420:2020

EAC
EN 388:2016+A1:2018 2X21C

ANSI A2 CUT

ANSI 4 ABR

FEATURES

Cut protection

SIZE		ARTICLE NUMBER	EAN
7	S	215-7	7392626014077
8	M	215-8	7392626014084
9	L	215-9	7392626014107
10	XL	215-10	7392626014114
11	XXL	215-11	7392626014121
12	3XL	215-12	7392626035508

ejendals
Limavägen 28, SE-793 32 Leksand, Sweden
Phone +46 (0) 247 360 00 | info@ejendals.com | order@ejendals.com

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.