



Post Office Box 97
 Benton Harbor, Michigan
 Ph: 616/926-6171
 Fax: 616/925-8288

PART NUMBER:

STD500

REVISION:

A

Product Specifications

Model Number	Function	RPM	HP	kW	Net Wt.	
					lbs.	kg
1550-600	Pressure	1440	1.0	0,74	33	15
	Pressure	1725	1.5	1,1	33	15
	Vacuum	1440	.50	0,37	33	15
	Vacuum	1725	.75	0,56	33	15

SOUND LEVEL 82 dB(A) MAX.
 NORMAL AMBIENT 1° C. - 40° C.
 RELATIVE HUMIDITY 8% - 100% NON CONDENSING
 ENVIRONMENT CLEAN DUST FREE

NOTES:
 1. TECHNICAL DATA SUBJECT TO CHANGE WITHOUT NOTICE.
 2. DIMENSIONS: METRIC (mm) U.S. IMPERIAL (inches).

DASHED LINE INDICATES INTERMITTENT PERFORMANCE ONLY.

