

Material Safety Data Sheet

HAZARD WARNINGS	RISK PHRASES	PROTECTIVE CLOTHING
	Flammable material; avoid heat and sources of ignition. The health risks of this compound have not been fully determined. Exposure may cause irritation of the skin, eyes, and respiratory system.	

Section I. Chemical Product and Company Identification

Chemical Name	n-Propylcyclohexane		
Catalog Number	P0681	Supplier	TCI America 9211 N. Harbrogate St. Portland OR 1-800-423-8616
Synonym	1-Cyclohexylpropane		
Chemical Formula	C ₆ H ₁₁ (CH ₂) ₂ CH ₃		
CAS Number	1678-92-8	In case of Emergency Call	Chemtrec® (800) 424-9300 (U.S.) (703) 527-3887 (International)

Section II. Composition and Information on Ingredients

Chemical Name	CAS Number	Percent (%)	TLV/PEL	Toxicology Data
n-Propylcyclohexane	1678-92-8	Min. 98.0 (GC)	Not available.	Not available.

Section III. Hazards Identification

Acute Health Effects	No specific information is available in our data base regarding the toxic effects of this material for humans. However, exposure to any chemical should be kept to a minimum. Skin and eye contact may result in irritation. May be harmful if inhaled or ingested. Always follow safe industrial hygiene practices and wear proper protective equipment when handling this compound.
Chronic Health Effects	CARCINOGENIC EFFECTS : Not available. MUTAGENIC EFFECTS : Not available. TERATOGENIC EFFECTS : Not available. DEVELOPMENTAL TOXICITY Not available. There is no known effect from chronic exposure to this product. Repeated or prolonged exposure to this compound is not known to aggravate existing medical conditions.

Section IV. First Aid Measures

Eye Contact	Check for and remove any contact lenses. DO NOT use an eye ointment. Flush eyes with running water for a minimum of 15 minutes, occasionally lifting the upper and lower eyelids. Seek medical attention. Treat symptomatically and supportively.
Skin Contact	After contact with skin, wash immediately with plenty of water. Gently and thoroughly wash the contaminated skin with running water and non-abrasive soap. Be particularly careful to clean folds, crevices, creases and groin. Cover the irritated skin with an emollient. Seek medical attention. Treat symptomatically and supportively. Wash any contaminated clothing before reusing.
Inhalation	Evacuate the victim to a safe area as soon as possible. Loosen tight clothing such as a collar, tie, belt or waistband. If breathing is difficult, administer oxygen. If the victim is not breathing, perform artificial respiration. Seek medical attention. Treat symptomatically and supportively.
Ingestion	INDUCE VOMITING by sticking finger in throat. Lower the head so that the vomit will not reenter the mouth and throat. Loosen tight clothing such as a collar, tie, belt, or waistband. If the victim is not breathing, administer artificial respiration. Examine the lips and mouth to ascertain whether the tissues are damaged, a possible indication that the toxic material was ingested; the absence of such signs, however, is not conclusive. Seek immediate medical attention and, if possible, show the chemical label. Treat symptomatically and supportively.

Section V. Fire and Explosion Data

Flammability	Flammable.	Auto-Ignition	250°C (482°F)
Flash Points	35°C (95°F)	Flammable Limits	LOWER: 0.85%
Combustion Products	These products are toxic carbon oxides (CO, CO ₂).		
Fire Hazards	Reactive with strong oxidizers. Vapors may travel to source of ignition and flash back. Closed containers may explode from heat of a fire. Highly flammable in presence of open flames nad sparks, of heat.		
Explosion Hazards	Risks of explosion of the product in presence of mechanical impact: Not available. Risks of explosion of the product in presence of static discharge: Not available. No additional information is available regarding the risks of explosion.		
Fire Fighting Media and Instructions			

Continued on Next Page**Emergency phone number (800) 424-9300**

Flammable liquid.
 SMALL FIRE: Use DRY chemicals, CO₂, alcohol foam or water spray.
 LARGE FIRE: Use alcohol foam, water spray or fog.

Section VI. Accidental Release Measures

Spill Cleanup Instructions	Flammable liquid. Keep away from heat and sources of ignition. Mechanical exhaust required. Stop leak if without risk. Absorb with DRY earth, sand or other non-combustible material. DO NOT touch spilled material. Prevent entry into sewers, basements or confined areas; dike if needed. Eliminate all sources of ignition. Consult federal, state, and/or local authorities for assistance on disposal.
----------------------------	---

Section VII. Handling and Storage

Handling and Storage Information	FLAMMABLE. Do not breathe gas, fumes, vapor or spray. In case of insufficient ventilation, wear suitable respiratory equipment. If you feel unwell, seek medical attention and show the label when possible. Treat symptomatically and supportively. Avoid contact with skin and eyes. Reactive with strong oxidizers; may be ignited by heat, sparks or flames. Vapors may travel to source of ignition and flash back. Closed containers may explode from heat of a fire. Empty containers may pose a fire risk. Evaporate residue under a fume hood if possible. Ground all equipment containing material. Handle with caution and minimize exposure. Keep away from heat and sources of ignition. Tightly seal container and store in a cool, dry place. Use only non-sparking hand tool when handling this product.
----------------------------------	--

Section VIII. Exposure Controls/Personal Protection

Engineering Controls	Provide exhaust ventilation or other engineering controls to keep the airborne concentrations of vapors below their respective threshold limit value. Ensure that eyewash station and safety shower is proximal to the work-station location.
Personal Protection	Splash goggles. Lab coat. Vapor respirator. Boots. Gloves. A MSHA/NIOSH approved respirator must be used to avoid inhalation of the product. Suggested protective clothing might not be sufficient; consult a specialist BEFORE handling this product.

Exposure Limits Not available.

Section IX. Physical and Chemical Properties

Physical state @ 20°C	Liquid.	Solubility	Not available.
Specific Gravity	0.793		
Molecular Weight	126.24	Partition Coefficient	Not available.
Boiling Point	155°C (311°F)	Vapor Pressure	8.7 mm of Hg @ 37.7°C
Melting Point	Not available.	Vapor Density	Not available.
Refractive Index	Not available.	Volatility	Not available.
Critical Temperature	Not available.	Odor	Not available.
Viscosity	Not available.	Taste	Not available.

Section X. Stability and Reactivity Data

Stability	This material is stable if stored under proper conditions. (See Section VII for instructions)
Conditions of Instability	Avoid excessive heat and light.
Incompatibilities	Reactive with strong oxidizing agents.

Section XI. Toxicological Information

RTECS Number	Not available.
Routes of Exposure	Eye contact. Ingestion. Inhalation. Skin contact.
Toxicity Data	Not available.
Chronic Toxic Effects	CARCINOGENIC EFFECTS : Not available. MUTAGENIC EFFECTS : Not available. TERATOGENIC EFFECTS : Not available. DEVELOPMENTAL TOXICITY Not available. There is no known effect from chronic exposure to this product. Repeated or prolonged exposure to this compound is not known to aggravate existing medical conditions.
Acute Toxic Effects	No specific information is available in our data base regarding the toxic effects of this material for humans. However, exposure to any chemical should be kept to a minimum. Skin and eye contact may result in irritation. May be harmful if inhaled or ingested. Always follow safe industrial hygiene practices and wear proper protective equipment when handling this compound.

Section XII. Ecological Information

Ecotoxicity Not available.

Environmental Fate Not available.

Section XIII. Disposal Considerations

Waste Disposal Recycle to process, if possible. Consult your local or regional authorities. You may be able to dissolve or mix material with a combustible solvent and burn in a chemical incinerator equipped with an afterburner and scrubber system. Observe all federal, state, and local regulations when disposing of this substance.

Section XIV. Transport Information

DOT Classification DOT CLASS 3: Flammable liquid.

PIN Number UN3295

Proper Shipping Name Hydrocarbons, liquid, n.o.s.

Packing Group (PG) III

DOT Pictograms



Section XV. Other Regulatory Information and Pictograms

TSCA Chemical Inventory (EPA)	This product is NOT on the EPA Toxic Substances Control Act (TSCA) inventory. The following notices are required by 40 CFR 720.36 (C) for those products not on the inventory list: (i) These products are supplied solely for use in research and development by or under the supervision of a technically qualified individual as defined in 40 CFR 720.0 et seq. (ii) The health risks of these products have not been fully determined. Any information that is or becomes available will be supplied on an MSDS sheet.
WHMIS Classification (Canada)	WHMIS CLASS B-2: Flammable liquid with a flash point lower than 35°C (100°F).
EINECS Number (EEC)	216-836-6
EEC Risk Statements	R10- Flammable. R18- In use, may form flammable/explosive vapor-air mixture.
Japanese Regulatory Data	Not available.

Section XVI. Other Information

Version 1.0

Validated on 3/18/1999.

Printed 3/18/2005.

Notice to Reader

TCI laboratory chemicals are for research purposes only and are NOT intended for use as drugs, food additives, households, or pesticides. The information herein is believed to be correct, but does not claim to be all inclusive and should be used only as a guide. Neither the above named supplier nor any of its subsidiaries assumes any liability whatsoever for the accuracy or completeness of the information contained herein. Final determination of suitability of any material is the sole responsibility of the user. All chemical reagents must be handled with the recognition that their chemical, physiological, toxicological, and hazardous properties have not been fully investigated or determined. All chemical reagents should be handled only by individuals who are familiar with their potential hazards and who have been fully trained in proper safety, laboratory, and chemical handling procedures. Although certain hazards are described herein, we can not guarantee that these are the only hazards which exist. Our MSDS sheets are based only on data available at the time of shipping and are subject to change without notice as new information is obtained. Avoid long storage periods since the product is subject to degradation with age and may become more dangerous or hazardous. It is the responsibility of the user to request updated MSDS sheets for products that are stored for extended periods. Disposal of unused product must be undertaken by qualified personnel who are knowledgeable in all applicable regulations and follow all pertinent safety precautions including the use of appropriate protective equipment (e.g. protective goggles, protective clothing, breathing equipment, facial mask, fume hood). For proper handling and disposal, always comply with federal, state, and local regulations.