

# Material Safety Data Sheet

HAZARD WARNINGS	RISK PHRASES	PROTECTIVE CLOTHING
 	<p><b>Toxic compound, do not ingest or inhale. Avoid all contact with this material.</b></p> <p><b>Irritating to skin, eyes, and the respiratory system.</b></p> <p><b>Combustible material; avoid heat and sources of ignition.</b></p> <p><b>POSSIBLE CARCINOGEN. MINIMIZE EXPOSURE.</b></p>	   

Section I. Chemical Product and Company Identification	
Chemical Name	<b>(R)-(+)-1-Phenylethyl Alcohol</b>
Catalog Number	P0795
Synonym	(R)-(+)-1-Phenylethanol; (R)-(+)-alpha-Methylbenzyl Alcohol; (R)-(+)-sec-Phenethyl Alcohol
Chemical Formula	C <sub>8</sub> H <sub>10</sub> O
CAS Number	1517-69-7
Supplier	TCI America 9211 N. Harborside St. Portland OR 1-800-423-8616
In case of Emergency Call	<b>Chemtrec®</b> <b>(800) 424-9300 (U.S.)</b> <b>(703) 527-3887 (International)</b>

Section II. Composition and Information on Ingredients				
Chemical Name	CAS Number	Percent (%)	TLV/PEL	Toxicology Data
(R)-(+)-1-Phenylethyl Alcohol	1517-69-7	Min. 98.0 (GC)	This chemical is classified as a possible carcinogen. There is no acceptable exposure limit for a carcinogen.	Not available.

Section III. Hazards Identification	
Acute Health Effects	Toxic if ingested or inhaled. Avoid prolonged contact with this material. Overexposure may result in serious illness or death. Irritating to eyes and skin on contact. Inhalation causes irritation of the lungs and respiratory system. Inflammation of the eye is characterized by redness, watering, and itching. Skin inflammation is characterized by itching, scaling, reddening, or, occasionally, blistering. Follow safe industrial hygiene practices and always wear proper protective equipment when handling this compound.
Chronic Health Effects	<b>CARCINOGENIC EFFECTS</b> : Not available. <b>MUTAGENIC EFFECTS</b> : Not available. <b>TERATOGENIC EFFECTS</b> : Not available. <b>DEVELOPMENTAL TOXICITY</b> : Not available. The substance is toxic to kidneys. Repeated or prolonged exposure to the substance can produce target organs damage. Repeated exposure to an highly toxic material may produce general deterioration of health by an accumulation in one or many human organs.

Section IV. First Aid Measures	
Eye Contact	Check for and remove any contact lenses. In case of contact, immediately flush eyes with plenty of water for at least 15 minutes. Get medical attention.
Skin Contact	In case of contact, immediately flush skin with plenty of water for at least 15 minutes while removing contaminated clothing and shoes. Wash clothing before reuse. Thoroughly clean shoes before reuse. Get medical attention immediately.
Inhalation	If the victim is not breathing, perform mouth-to-mouth resuscitation. Loosen tight clothing such as a collar, tie, belt or waistband. If breathing is difficult, oxygen can be administered. Seek medical attention if respiration problems do not improve.
Ingestion	INDUCE VOMITING by sticking finger in throat. Lower the head so that the vomit will not reenter the mouth and throat. Loosen tight clothing such as a collar, tie, belt or waistband. If the victim is not breathing, perform mouth-to-mouth resuscitation. Examine the lips and mouth to ascertain whether the tissues are damaged, a possible indication that the toxic material was ingested; the absence of such signs, however, is not conclusive.

Section V. Fire and Explosion Data			
Flammability	Combustible.	Auto-Ignition	Not available.
Flash Points	86°C (186.8°F)	Flammable Limits	Not available.
Combustion Products	These products are toxic carbon oxides (CO, CO <sub>2</sub> ).		
Fire Hazards	Not available.		
Explosion Hazards	Risks of explosion of the product in presence of mechanical impact: Not available. Risks of explosion of the product in presence of static discharge: Not available.		
Fire Fighting Media and Instructions	SMALL FIRE: Use DRY chemical powder. LARGE FIRE: Use water spray, fog or foam. DO NOT use water jet. Consult with local fire authorities before attempting large scale fire-fighting operations.		

Printed 2/9/2010.

**Section VI. Accidental Release Measures**

Spill Cleanup Instructions Toxic material. Irritating material. Combustible material. Possibly carcinogenic material. Keep away from heat. Mechanical exhaust required. Stop leak if without risk. DO NOT get water inside container. DO NOT touch spilled material. Use water spray to reduce vapors. Prevent entry into sewers, basements or confined areas; dike if needed. Consult federal, state, and/or local authorities for assistance on disposal.

**Section VII. Handling and Storage**

Handling and Storage Information TOXIC. IRRITANT. COMBUSTIBLE. POSSIBLE CARCINOGEN. Keep locked up.. Keep away from heat. Mechanical exhaust required. Avoid excessive heat and light. DO NOT ingest. Do not breathe gas/fumes/ vapor/spray. Wear suitable protective clothing. If ingested, seek medical advice immediately and show the container or the label. Treat symptomatically and supportively. Always store away from incompatible compounds such as oxidizing agents, acids.

**Section VIII. Exposure Controls/Personal Protection**

Engineering Controls Provide exhaust ventilation or other engineering controls to keep the airborne concentrations of vapors below their respective threshold limit value. Ensure that eyewash station and safety shower is proximal to the work-station location.

Personal Protection Splash goggles. Lab coat. Vapor respirator. Boots. Gloves. A MSHA/NIOSH approved respirator must be used to avoid inhalation of the product. Suggested protective clothing might not be sufficient; consult a specialist BEFORE handling this product.



Exposure Limits This chemical is classified as a possible carcinogen. There is no acceptable exposure limit for a carcinogen.

**Section IX. Physical and Chemical Properties**

Physical state @ 20°C	Liquid. (Clear, colorless.)	Solubility	Not available.
Specific Gravity	1.01 (water=1)		
Molecular Weight	122.16	Partition Coefficient	Not available.
Boiling Point	89°C (192.2°F) @ 10 mmHg	Vapor Pressure	Not available.
Melting Point	11°C (51.8°F)	Vapor Density	Not available.
Refractive Index	1.53	Volatility	Not available.
Critical Temperature	Not available.	Odor	Not available.
Viscosity	Not available.	Taste	Not available.

**Section X. Stability and Reactivity Data**

Stability This material is stable if stored under proper conditions. (See Section VII for instructions)

Conditions of Instability Avoid excessive heat and light.

Incompatibilities Reactive with oxidizing agents, acids.

**Section XI. Toxicological Information**

RTECS Number Not available.

Routes of Exposure Eye Contact. Ingestion. Inhalation.

Toxicity Data Not available.

Chronic Toxic Effects **CARCINOGENIC EFFECTS** : Not available.  
**MUTAGENIC EFFECTS** : Not available.  
**TERATOGENIC EFFECTS** : Not available.  
**DEVELOPMENTAL TOXICITY**: Not available.  
The substance is toxic to kidneys.  
Repeated or prolonged exposure to the substance can produce target organs damage. Repeated exposure to an highly toxic material may produce general deterioration of health by an accumulation in one or many human organs.

Acute Toxic Effects Toxic if ingested or inhaled. Avoid prolonged contact with this material. Overexposure may result in serious illness or death. Irritating to eyes and skin on contact. Inhalation causes irritation of the lungs and respiratory system. Inflammation of the eye is characterized by redness, watering, and itching. Skin inflammation is characterized by itching, scaling, reddening, or, occasionally, blistering.  
Follow safe industrial hygiene practices and always wear proper protective equipment when handling this compound.

**Section XII. Ecological Information**

Ecotoxicity	Not available.
Environmental Fate	Not available.

**Section XIII. Disposal Considerations**

Waste Disposal	Recycle to process, if possible. Consult your local regional authorities. You may be able to dissolve or mix material with a combustible solvent and burn in a chemical incinerator equipped with an afterburner and scrubber system. Observe all federal, state and local regulations when disposing of the substance.
----------------	---

**Section XIV. Transport Information**

DOT Classification	DOT CLASS 6.1: Toxic material
PIN Number	UN2937
Proper Shipping Name	alpha-Methylbenzyl alcohol, liquid
Packing Group (PG)	III
DOT Pictograms	

**Section XV. Other Regulatory Information and Pictograms**

TSCA Chemical Inventory (EPA)	This product is <b>NOT</b> on the EPA Toxic Substances Control Act (TSCA) inventory. The following notices are required by 40 CFR 720.36 (C) for those products not on the inventory list: (i) These products are supplied solely for use in research and development by or under the supervision of a technically qualified individual as defined in 40 CFR 720.0 et sec. (ii) The health risks of these products have not been fully determined. Any information that is or becomes available will be supplied on an MSDS sheet.
WHMIS Classification (Canada)	CLASS B-3: Combustible liquid with a flash point between 37.8°C (100°F) and 93.3°C (200°F). CLASS D-1B: Material causing immediate and serious toxic effects (TOXIC).
EINECS Number (EEC)	Not available.
EEC Risk Statements	R23/24/25- Toxic by inhalation, in contact with skin and if swallowed. R36/37/38- Irritating to eyes, respiratory system and skin. R45- May cause cancer.
Japanese Regulatory Data	ENCS No. 3-1049

**Section XVI. Other Information**

**Version 1.0**  
**Validated on 2/9/2010.**  
**Printed 2/9/2010.**

**Notice to Reader**

TCI laboratory chemicals are for research purposes only and are NOT intended for use as drugs, food additives, households, or pesticides. The information herein is believed to be correct, but does not claim to be all inclusive and should be used only as a guide. Neither the above named supplier nor any of its subsidiaries assumes any liability whatsoever for the accuracy or completeness of the information contained herein. Final determination of suitability of any material is the sole responsibility of the user. All chemical reagents must be handled with the recognition that their chemical, physiological, toxicological, and hazardous properties have not been fully investigated or determined. All chemical reagents should be handled only by individuals who are familiar with their potential hazards and who have been fully trained in proper safety, laboratory, and chemical handling procedures. Although certain hazards are described herein, we can not guarantee that these are the only hazards which exist. Our MSDS sheets are based only on data available at the time of shipping and are subject to change without notice as new information is obtained. Avoid long storage periods since the product is subject to degradation with age and may become more dangerous or hazardous. It is the responsibility of the user to request updated MSDS sheets for products that are stored for extended periods. Disposal of unused product must be undertaken by qualified personnel who are knowledgeable in all applicable regulations and follow all pertinent safety precautions including the use of appropriate protective equipment (e.g. protective goggles, protective clothing, breathing equipment, facial mask, fume hood). For proper handling and disposal, always comply with federal, state, and local regulations.