ABB BALDOR RELIANCE

Customer information packet

M3157

2HP, 1740RPM, 3PH, 60HZ, 56H, 3521M, OPEN, F1, N
Class - None
Division - Not Applicable

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/5/2026 10:23:49 AM

Specifications

Enclosure	ODP
Frame	56H
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	2.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	460.0 V @ 60 HZ
	230.0 V @ 60 HZ
	208.0 V @ 60 HZ
Agency Approvals	CSA
	UR
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	6.700 A @ 208.0 V
	6.140 A @ 230.0 V
	3.070 A @ 460.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	80.0 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Face Code	Standard
Front Shaft Indicator	None

Part Detail

Revision	C
Type	AC
Mech. spec.	35J382
Base	
Status	NLA/A
Elec. spec.	35WGP803
Layout	35LYJ382
Eff. date	01-21-2015
CD Diagram	CD0005
Poles	04
Leads	9#18
Proprietary	False
Created date	07-13-2010

Heater Indicator	No Heater
High Voltage Full Load Amps	3.1 a
Insulation Class	B
Inverter Code	Not Inverter
KVA Code	L
Lifting Lugs	No Lifting Lugs
Locked Bearing Indicator	No Locked Bearing
Motor Lead Exit	Ko Box
Motor Lead Quantity/Wire Size	9 @ 18 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3521M
Mounting Arrangement	F1
Number of Poles	4
Overall Length	11.75 IN
Power Factor	75
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	Standard
Pulley Shaft Indicator	Standard
Rodent Screen	None
Service Factor	1.15
Shaft Diameter	0.625 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	1740 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None

Winding Thermal 2	None

Nameplate

NP1256L									
CAT.NO.	M3157								
SPEC.	35J382P803G1								
HP	2								
VOLTS	208-230/460								
AMP	6.7-6.14/3.07								
RPM	1740								
FRAME	56H	**HZ**	60			**PH**	3		
SER.F.	1.15	**CODE**	L	**DES**	B	**CLASS**	B		
NEMA-NOM-EFF	80	**PF**	75						
RATING	40C AMB-CONT								
CC									
DE	6205	**ODE**	6203						
ENCL	OPEN	**SN**							

Accessories

Part number	Description	Multiplier
35-8764	C FACE KIT	A8
35EP1604A01SP	D-FLANGE KIT	

AC Induction Motor Performance Data
Record # 26939
Typical performance - not guaranteed values

Winding: 35WGP803-R001	**Type:** 3522M	**Enclosure:** OPSB

Nameplate Data				**460 V, 60 Hz: High Voltage Connection**	
Rated Output (HP)			2	**Full Load Torque**	6 LB-FT
Volts			208-230/460	**Start Configuration**	direct on line
Full Load Amps			6.7-6.14/3.07	**Breakdown Torque**	22.59 LB-FT
R.P.M.			1740	**Pull-up Torque**	14.43 LB-FT
Hz	60	**Phase**	3	**Locked-rotor Torque**	17.89 LB-FT
NEMA Design Code	B	**KVA Code**	L	**Starting Current**	23.23 A
Service Factor (S.F.)			1.15	**No-load Current**	2.07 A
NEMA Nom. Eff.	80	**Power Factor**	75	**Line-line Res. @ 25ºC**	8.85 Ω
Rating - Duty			40C AMB-CONT	**Temp. Rise @ Rated Load**	58°C
S.F. Amps				**Temp. Rise @ S.F. Load**	67°C
				Locked-rotor Power Factor	64.8
				Rotor inertia	0.13 LB-FT2

Load Characteristics 460 V, 60 Hz, 2 HP

% of Rated Load	**25**	**50**	**75**	**100**	**125**	**150**	**S.F.**
Power Factor	33	52	65	75	81	85	79
Efficiency	65.5	76.3	80.4	81.4	80.7	79	80.7
Speed	1786	1773	1759	1743	1724	1702	1730
Line amperes	2.12	2.34	2.64	3.07	3.58	4.18	3.38


ABB Motors and Mechanical Inc.

WINDING # 35WGP803


2 HP 3 PH 60 HZ 1740 RPM 460 V 3522M

Typical performance - not guaranteed values.


TORQUES(LB-FT): PO=22.59 PU=14.43 LR=17.89 LRA=23.23




11/5/2026 ACPERF, record # 26939


35LYJ382
510-528 = 11.75
529-535 = 12.63
536-546 = 14.00
2.60
2.12
1.88
.19 KEY
1.38 LONG
NAMEPLATE
Ø .6250
.6245
6 SLOTS
.34 WIDE
3.00
2.75
5.00
1.00
6.50
Ø 6.62
5.62
4.48
6.78
3.50
3.44
THERMAL
(WHEN
REQ'D)
LEAD HOLE
.88 DIA.
2.44
2.44
4.56
3.25
6.50
CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT THE PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION
REV. DESC: ADD THERMAL DIMS AND THERMAL WHEN REQUIRED NOTE
REV: J
VERSION: 06
REVISED: 02:24:53 04/10/2023
TDR: 000001205626
MODEL NO. 35LYJ382
REF: -
BY: USBUFRA
B
BALDOR - RELIANCE®
STD HORZ 56/56H OPEN 35M
SH 1 of 1
35LYJ382

CD0005





NOTES:

1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
2. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
3. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY BE A MULTIPLE OF THOSE SHOWN ABOVE.
4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

CD0005

REV. DESC: REVISE TO SHOW OPTIONAL COLORS			BALDOR ELECTRIC Co.
REV. LTR: E	BY: JLP	REVISED: 01/19/99 10:15	TDR: 0171435
CD0005		FILE: AAA00005140	MDL: –
		MTL: –	3PH, DV, 9 LEADS