



SAFETY DATA SHEET

1. Identification

Product identifier LOR10Series
Other means of identification Not available.
Recommended use Inkjet printing
Recommended restrictions None known.
Company identification HP Inc.
1501 Page Mill Road
Palo Alto, CA 94304-1112
United States
Telephone 650-857-5020

HP Inc. health effects line
(Toll-free within the US) 1-800-457-4209
(Direct) 1-760-710-0048
HP Inc. Customer Care Line
(Toll-free within the US) 1-800-474-6836
(Direct) 1-208-323-2551
Email: hpcustomer.inquiries@hp.com

2. Hazard(s) identification

Physical hazards Not classified.
Health hazards Not classified.
Environmental hazards Not classified.
OSHA defined hazards Not classified.

Label elements

Hazard symbol None.
Signal word None.
Hazard statement Not available.

Precautionary statement

Prevention Not available.
Response Not available.
Storage Not available.
Disposal Not available.

Hazard(s) not otherwise classified (HNOC) Complete toxicity data are not available for this specific formulation.

Potential routes of overexposure to this product are skin and eye contact. Inhalation of vapor and ingestion are not expected to be significant routes of exposure for this product under normal use conditions.

None of the components present in this formulation at concentrations equal to or greater than 0.1% are listed by EU, MAK, IARC, NTP or OSHA.

Supplemental information This product is not classified as hazardous according to OSHA CFR 1910.1200 (HazCom 2012).

3. Composition/information on ingredients

Mixtures

| Chemical name | Common name and synonyms | CAS number | % |
|-----------------|--------------------------|-------------|-------|
| Water | | 7732-18-5 | 70-85 |
| 2-pyrrolidone | | 616-45-5 | <10 |
| Magenta pigment | | Proprietary | <5 |

Composition comments This ink supply contains an aqueous ink formulation. This product has been evaluated using criteria specified in 29 CFR 1910.1200 (Hazard Communication Standard).

4. First-aid measures

Inhalation Move to fresh air. If symptoms persist, get medical attention.

Skin contact Wash affected areas thoroughly with mild soap and water. Get medical attention if irritation develops or persists.

Eye contact Do not rub eyes. Immediately flush with large amounts of clean, warm water (low pressure) for at least 15 minutes or until particles are removed. If irritation persists get medical attention.

Ingestion If ingestion of a large amount does occur, seek medical attention.

Most important symptoms/effects, acute and delayed Not available.

5. Fire-fighting measures

Suitable extinguishing media Dry chemical, CO₂, water spray or regular foam.

Unsuitable extinguishing media None known.

Specific hazards arising from the chemical Not applicable.

Special protective equipment and precautions for firefighters Not available.

Specific methods None established.

6. Accidental release measures

Personal precautions, protective equipment and emergency procedures Wear appropriate personal protective equipment.

Methods and materials for containment and cleaning up Dike the spilled material, where this is possible. Absorb with inert absorbent such as dry clay, sand or diatomaceous earth, commercial sorbents, or recover using pumps.

Environmental precautions Do not let product enter drains. Do not flush into surface water or sanitary sewer system.

7. Handling and storage

Precautions for safe handling Avoid contact with skin, eyes and clothing.

Conditions for safe storage, including any incompatibilities Keep out of the reach of children. Keep away from excessive heat or cold.

8. Exposure controls/personal protection

Occupational exposure limits No exposure limits noted for ingredient(s).

Biological limit values No biological exposure limits noted for the ingredient(s).

Exposure guidelines Exposure limits have not been established for this product.

Appropriate engineering controls Use in a well ventilated area.

Individual protection measures, such as personal protective equipment

- Eye/face protection** Not available.
- Skin protection**
 - Hand protection** Not available.
 - Other** Not available.
- Respiratory protection** Not available.
- Thermal hazards** Not available.

General hygiene considerations Handle in accordance with good industrial hygiene and safety practice.

9. Physical and chemical properties

Appearance

Material name: LOR10Series
12735 Version #: 01 Issue date: 12-May-2016

| | |
|---|---|
| Physical state | Not available. |
| Color | Magenta |
| Odor | Not available. |
| Odor threshold | Not available. |
| pH | 9 - 9.5 |
| Melting point/freezing point | Not available. |
| Initial boiling point and boiling range | Not available. |
| Flash point | > 230.0 °F (> 110.0 °C) Pensky-Martens Closed Cup |
| Evaporation rate | Not available. |
| Flammability (solid, gas) | Not available. |
| Upper/lower flammability or explosive limits | |
| Flammability limit - lower (%) | Not available. |
| Flammability limit - upper (%) | Not available. |
| Explosive limit - lower (%) | Not available. |
| Explosive limit - upper (%) | Not available. |
| Vapor pressure | Not available. |
| Solubility(ies) | |
| Solubility (water) | Not available. |
| Partition coefficient (n-octanol/water) | Not available. |
| Auto-ignition temperature | Not available. |
| Decomposition temperature | Not available. |
| Viscosity | Not available. |
| Other information | For other VOC regulatory data/information see Section 15. |
| VOC (Weight %) | 204 g/l estimated |

10. Stability and reactivity

| | |
|---|---|
| Reactivity | Not available. |
| Chemical stability | Stable under recommended storage conditions. |
| Possibility of hazardous reactions | Will not occur. |
| Conditions to avoid | Not available. |
| Incompatible materials | Incompatible with strong bases and oxidizing agents. |
| Hazardous decomposition products | Upon decomposition, this product may yield gaseous nitrogen oxides, carbon monoxide, carbon dioxide and/or low molecular weight hydrocarbons. |

11. Toxicological information

| | |
|---|---|
| Symptoms related to the physical, chemical and toxicological characteristics | Not available. |
| Information on toxicological effects | |
| Acute toxicity | Based on available data, the classification criteria are not met. |
| Skin corrosion/irritation | Based on available data, the classification criteria are not met. |
| Serious eye damage/eye irritation | Based on available data, the classification criteria are not met. |
| Respiratory or skin sensitization | |
| Respiratory sensitization | Based on available data, the classification criteria are not met. |
| Skin sensitization | Based on available data, the classification criteria are not met. |

| | |
|---|---|
| Germ cell mutagenicity | Based on available data, the classification criteria are not met. |
| Carcinogenicity | Based on available data, the classification criteria are not met. |
| Reproductive toxicity | Based on available data, the classification criteria are not met. |
| Specific target organ toxicity - single exposure | Based on available data, the classification criteria are not met. |
| Specific target organ toxicity - repeated exposure | Based on available data, the classification criteria are not met. |
| Aspiration hazard | Based on available data, the classification criteria are not met. |
| Further information | Complete toxicity data are not available for this specific formulation Refer to Section 2 for potential health effects and Section 4 for first aid measures. |

| Components | Species | Test Results |
|------------------------------|------------|--------------|
| 2-pyrrolidone (CAS 616-45-5) | | |
| Acute | | |
| <i>Oral</i> | | |
| LD50 | Guinea pig | 6500 mg/kg |
| | Rat | 6500 mg/kg |

12. Ecological information

Aquatic toxicity No information available.

Ecotoxicity

| Components | Species | Test Results |
|------------------------------|--|----------------------|
| 2-pyrrolidone (CAS 616-45-5) | | |
| Aquatic | | |
| Crustacea | EC50 Water flea (<i>Daphnia pulex</i>) | 13.21 mg/l, 48 hours |

Persistence and degradability Not available.

Bioaccumulative potential Not available.

Partition coefficient n-octanol / water (log Kow)
2-pyrrolidone -0.85

Mobility in soil Not available.

Other adverse effects Not available.

13. Disposal considerations

Disposal instructions Do not allow this material to drain into sewers/water supplies.
Dispose of waste material according to Local, State, Federal, and Provincial Environmental Regulations.

HP's Planet Partners (trademark) supplies recycling program enables simple, convenient recycling of HP original inkjet and LaserJet supplies. For more information and to determine if this service is available in your location, please visit <http://www.hp.com/recycle>.

14. Transport information

DOT

Not regulated as dangerous goods.

IATA

Not regulated as dangerous goods.

IMDG

Not regulated as dangerous goods.

ADR

Not regulated as dangerous goods.

Further information Not a dangerous good under DOT, IATA, ADR, IMDG, or RID.

15. Regulatory information

US federal regulations US TSCA 12(b): Does not contain listed chemicals.

TSCA Section 12(b) Export Notification (40 CFR 707, Subpt. D)

Not regulated.

CERCLA Hazardous Substance List (40 CFR 302.4)

Not listed.

SARA 304 Emergency release notification

Not regulated.

OSHA Specifically Regulated Substances (29 CFR 1910.1001-1050)

Not listed.

Superfund Amendments and Reauthorization Act of 1986 (SARA)

Hazard categories Immediate Hazard - No
 Delayed Hazard - No
 Fire Hazard - No
 Pressure Hazard - No
 Reactivity Hazard - No

SARA 302 Extremely hazardous substance

Not listed.

SARA 311/312 No
Hazardous chemical

Other federal regulations

Safe Drinking Water Act (SDWA) Not regulated.

US state regulations**US. Massachusetts RTK - Substance List**

2-pyrrolidone (CAS 616-45-5)

US. New Jersey Worker and Community Right-to-Know Act

Not listed.

US. Pennsylvania Worker and Community Right-to-Know Law

2-pyrrolidone (CAS 616-45-5)

US. Rhode Island RTK

Not regulated.

US. California Proposition 65

Not Listed.

Other information VOC content (less water, less exempt compounds) = 694 g/L (U.S. requirement, not for emissions)

VOC data based on formulation (Organic compounds minus solids)

Regulatory information All chemical substances in this HP product have been notified or are exempt from notification under chemical substances notification laws in the following countries: US (TSCA), EU (EINECS/ELINCS), Switzerland, Canada (DSL/NDL), Australia, Japan, Philippines, South Korea, New Zealand, and China.

16. Other information, including date of preparation or last revision

Issue date 12-May-2016

Version # 01

Disclaimer This Safety Data Sheet document is provided without charge to customers of HP. Data is the most current known to HP at the time of preparation of this document and is believed to be accurate. It should not be construed as guaranteeing specific properties of the products as described or suitability for a particular application. This document was prepared to the requirements of the jurisdiction specified in Section 1 above and may not meet regulatory requirements in other countries.

Revision Information 1. Product and Company Identification: Alternate Trade Names

Manufacturer information HP Inc.
 1501 Page Mill Road
 Palo Alto, CA 94304-1112 US
 Direct 1-650-857-5020

Explanation of abbreviations

| | |
|---------------|---|
| ACGIH | American Conference of Governmental Industrial Hygienists |
| CAS | Chemical Abstracts Service |
| CERCLA | Comprehensive Environmental Response Compensation and Liability Act |
| CFR | Code of Federal Regulations |
| COC | Cleveland Open Cup |
| DOT | Department of Transportation |
| EPCRA | Emergency Planning and Community Right-to-Know Act (aka SARA) |
| IARC | International Agency for Research on Cancer |
| NIOSH | National Institute for Occupational Safety and Health |
| NTP | National Toxicology Program |
| OSHA | Occupational Safety and Health Administration |
| PEL | Permissible Exposure Limit |
| RCRA | Resource Conservation and Recovery Act |
| REC | Recommended |
| REL | Recommended Exposure Limit |
| SARA | Superfund Amendments and Reauthorization Act of 1986 |
| STEL | Short-Term Exposure Limit |
| TCLP | Toxicity Characteristics Leaching Procedure |
| TLV | Threshold Limit Value |
| TSCA | Toxic Substances Control Act |
| VOC | Volatile Organic Compounds |