



Outstanding Quality Products
Competitive Prices
Superior Service

MILES HYDRO STOP LEAK

Hydraulic Fluid with Leak Stop

MILES HYDRO STOP LEAK is high performance inherently biodegradable hydraulic fluid, formulated for hydraulic systems prone to leakage. Its advanced additives help reduce hydraulic fluid leakage from seals. MILES HYDRO STOP LEAK also provides enhanced lubricity and a very long fluid life.

ATTRIBUTES

- Reduces hydraulic fluid leakage from seals
- Excellent protection against wear, rust and corrosion
- Excellent demulsibility
- Excellent oxidative stability
- High viscosity index
- Excellent carbon and varnish control
- Very low volatility
- Non-Toxic / Non-Hazardous

TYPICAL PROPERTIES

	HYDRO STOP LEAK-22	HYDRO STOP LEAK-32	HYDRO STOP LEAK-46	HYDRO STOP LEAK-68	HYDRO STOP LEAK-100
Lubrication Properties					
Grade	22	32	46	68	100
Viscosity cSt @ 40 °C	22.4	32.0	46.1	67.3	102
Oxidation Stability	10000+	10000+	10000+	10000+	10000+
Color (D1500)	<.5	<.5	<.5	<.5	<.5
Flash Point °F	390	418	432	448	512
Pour Point °F	-50	-42	-39	-34	-27
Copper Corrosion	1a	1a	1a	1a	1a
Rust Test	Pass	Pass	Pass	Pass	Pass
Foam Sequence 1	0/0	0/0	0/0	0/0	0/0
Pump Wear Test (Vickers 35VQ25)	Pass	Pass	Pass	Pass	Pass
Denison Demulsibility, 130 °F, 30 min	Meets 40/40/0	Meets 40/40/0	Meets 40/40/0	Meets 40/40/0	Meets 40/40/0