

MAX1350 S

 1420 x 440 x H168 mm
55.90 x 17.32 x 6.61 inch

 1350 x 370 x H150 mm
53.14 x 14.56 x 5.90 inch

 45 + 105 mm
1.77 + 4.13 inch

 9,60 kg / 21.16 lb


 -51 / 90 °C / -59.8 / 194° F

 Capacità / Capacity
75 lt



 Stampaggio: ad iniezione
Process: Injection molding

 Materiale / Materials
POLIPROPILENE/POLYPROPYLENE
NYLON (Serrature / Latches)
Assale Ruote in ACCIAIO INOX /
Stainless steel wheel pins
POLIURETANO/POLYURETHANE
(Spugna / foam)



VIDEO S & HDS



- Guarnizione ermetica / Watertight seal around lid
- Valvola automatica di pressurizzazione
Automatic pressure release valve
- Sistema di impilabilità / Stackable interlocking system
- Resistenza agli urti / Thick body material
- Chiusure di sicurezza a doppio step / Easy to open double throw latches
- Manico morbido ad alta ergonomia / Load tested soft grip handle
- Pareti spesse ANTIURTO / Thick body material
- Punti di fissaggio per varie applicazioni / Extra fixing points
- Cerniera lungo tutto il profilo della valigia / Fully length hinges
- Perni in nylon ANTI corrosione / Nylon pins corrosion free

Shipping & Logistic info

1 pz. per cartone
1 pc. x carton



11,25 Kg per cartone
24.80 lb gross weight



IP67
RATING

MIL SPECS

DEF STAN 81-41
STANAG 4280
MIL STD 810G



CUSTOM LABEL
ETICHETTA CUSTOM



CUSTOMIZED
FOAM INLAY
INTERNI IN SPUGNA
FUSTELLATA



LASER MARKING
OR ENGRAVING
INCISIONE O
MARCATURA LASER



CUSTOM COLOUR
COLORI CUSTOM