

Ultratorch® UT-100 & UT-100-TC

Butane-powered soldering iron, flameless heat tool and torch



UT-100-TC

Ultratorch Professional Kit:

Includes heat tool, 3 soldering tips, flameless hot air and open flame torch tips, hot knife, solder, wire cutter, needle nose pliers and cap in a rugged storage/carrying case



70-01-02 tip

70-01-55

70-35

70-07TU

70-01-52

UT-100

Ultratorch



Solder



Flameless Heat



Torch

- Triple function soldering iron, flameless heat tool and brazing torch
- Features oxygen-free, copper based Ultratip® soldering tips, with thick iron and chrome plating for long life and high thermal conductivity
- Cordless and completely portable, ready-to-use in 30 seconds
- Adjustable temperature control
- Soldering temperature up to 932°F, ideal for use with today's lead-free solder
- Hot air temperature up to 1202°F, perfect for Solderseal™ environmental "heat and seal" connectors
- Torch temperatures up to 2372°F/1260°C
- Sturdy metal tank with fuel viewing window holds enough fuel for 2 hours of operation
- Refill with Master Ultratane Butane for best performance (page 28)
- Use to pinpoint heat, remove surface mount components, repair vinyl, heat shrink tubing, solder and desolder, spot dry, torch materials and more
- Optional accessories available and interchangeable between UT-100 & UT100Si (See page 20)



MODEL NO.	DESCRIPTION
UT-100-TC	Includes Ultratorch, three Ultratip soldering tips: 70-01-02, 70-01-05, 70-01-11, hot air tip: 70-01-52, shrink attachment: 70-01-55, hot knife: 70-01-16, torch ejector 70-07TU, open end wrench, ejector, sponge, cap, solder, wire cutter and needle nose pliers packed in a rugged plastic carrying case
UT-100	Includes Ultratorch, Ultratip soldering tip: 70-01-02, hot air tip: 70-01-52, shrink attachment: 70-01-55, torch ejector 70-07TU, open end wrench, ejector, sponge and steel case

See page 20 for more tips & accessories

Specifications

- Approx. Soldering Tip Temp.: 392° - 932°F (200° - 500°C)
- Approx. Hot Air Tip Temp.: 1112°F (600°C) ■ Approx. Torch Tip Temp. 2372°F (1260°C) ■ Equivalent to Electric Iron: 20 to 80 Watt ■ Approx. Operating Time: 120 min. ■ Fuel Tank Capacity: 1 fl. oz. (28 cc)
- Tool dimensions: 9.5" L (242mm) ■ Tool Net Weight: 3.7 oz.
- UT-100 Shipping Weight: 1 lb. ■ UT-100-TC Shipping Weight: 3 lbs.
- Shipped Empty

NOTE: Users should independently evaluate the suitability of the product for their application.