

XLERATOR® HAND DRYER



ORIGINAL. PATENTED. STILL THE BEST.

10-15

SECOND
proven dry time*

80%

LESS ENERGY
than conventional dryers

95%

COST SAVINGS
versus paper towels



XLERATOR® HAND DRYER



MODELS: **XL - BW** **W** **GR** **C** **SB** **SI** **SP** OPTIONS: **-1.1N** (Noise Reduction Nozzle) **-H** (HEPA Filter) **-VOLTAGE** (See Chart)



XL-BW

White Thermoset Resin (BMC)

FEATURES & BENEFITS

- ✓ 10-15 Second Dry Time*
- ✓ 5-Year Limited Warranty
- ✓ 80% Less Energy Than Conventional Hand Dryers
- ✓ GreenSpec® Listed and Helps Qualify for several LEED® credits
- ✓ 95% Cost Savings Vs. Paper Towels
- ✓ A Hygienic Hand Drying Solution
- ✓ Virtually Maintenance Free
- ✓ Over a Decade of Proven Performance

OPTIONS

- ✓ **HEPA Filtration System:** Filters 99.97% of bacteria and particles at 0.3 microns from the air stream.
- ✓ **1.1 Noise Reduction Nozzle:** Lowers decibel level 9 dB by reducing air deflection noise but increases dry time by approximately 3 seconds.

ONLINE INFORMATION

- ▶ Product Videos
- 📊 3 Part Specifications
- 💰 Cost Savings & Carbon Footprint Calculator
- 👁️ CAD/BIM Images
- 📊 Life Cycle Assessment Study
- 📄 AIA/GBCI CEU Courses
- 📄 Case Studies
- 📄 Technical Data Sheet



XL-W

White Epoxy Painted



XL-GR

Graphite Textured Painted



XL-SP**

Custom Special Paint



XL-SI***

Custom Special Image



XL-C

Chrome Plated



XL-SB

Brushed Stainless Steel

DIMENSIONS

Width 11 3/4" (298 mm) **Height** 12 11/16" (322 mm) **Depth** 6 11/16" (170 mm)

WEIGHT

XL-BW: 15 lbs. (6.8 kgs.) **XL-SB:** 16 lbs. (7.26 kgs.) **XL-W, GR, C, SI, SP:** 17 lbs. (7.71 kgs.)

ELECTRICAL

Units are Single Phase 1500 Watts and available as specified in:

| | | | |
|----------|--------|----------|--------|
| 110-120V | 12.5 A | 60 Hz | cUL US |
| 208V | 7 A | 50/60 Hz | cUL US |
| 220-240V | 6.5 A | 50/60 Hz | cUL US |
| 277V | 5.5 A | 60 Hz | cUL US |
| 230V | 6.5 A | 50 Hz | CE |

ACTIVATION

Automatic Sensor Operated

MOUNTING

Surface Mounted

SUGGESTED MOUNTING HEIGHTS

Men 45" (114 cm) **Women** 43" (109 cm) **Handicapped** 37" (94 cm)

Note: Heights measured from floor to bottom of dryer.

ACCESSORIES

- ✓ Sound and Speed Control
- ✓ Anti-Microbial Wall Guards
- ✓ XChanger Paper Towel Dispenser Retrofit Kit
- ✓ ADA-Compliant Recess Kit

Width 16 3/8" (416 mm) **Height** 26" (660 mm)
Depth 3 3/8" (86 mm) **Weight** 11 lbs. (4.99 kgs.)



Part # 40502



RoHS



* Dry time based on third party testing performed by SGS International on standard XLERATOR hand dryer with 0.8 nozzle to 0.2g or less of residual moisture.

** Special Paint powder-coated covers are available in many colors and textures.

*** Exclusive digital image technology allows for the addition of company, school or team logos with any color, design or a 'green message'.



TIME TO THROW IN THE TOWEL®
EXCEL DRYER INC