



Dishwasher Detergent Pods

Material Safety Data Sheet

Revision date: 23/03/2017 According to Regulation (EC) No. 1907/2006
Updated Date: 27/07/2026

SECTION 1. Identification of the substance/preparation and company

Product Name: DISHWASHER DETERGENT PODS
Supplier: World Amenities, Inc.
Address: 8960 Carroll Way, Suite E, San Diego, CA 92121, USA
Telephone: 1-858-880-SOAP / Fax: 858-428-3330

SECTION 2. Hazards identifications

- 2.1 Hazard Classification of substance or mixture (GHS): Acute toxicity, oral category 4

Serious eye damage/eye irritation category 2A Sensitisation, respiratory category 1

Hazardous to the aquatic environment, long-term hazard category 2

- 2.2 Pictograms:

[GHS hazard pictograms: Exclamation mark, Environmental hazard, Health hazard]

- 2.3 Signal word:

Danger

- 2.4 Hazard description:

H302: Harmful if swallowed

H319: Causes serious eye irritation

H334: May cause allergy or asthma symptoms or breathing difficulties if inhaled

H411: Toxic to aquatic life with long lasting effects

- 2.5 Precautionary description:

P261: Avoid breathing dust/fume/gas/mist/vapours/spray.

P264: Wash ... thoroughly after handling.

P270: Do not eat, drink or smoke when using this product.

P273: Avoid release to the environment.

P280: Wear eye protection/face protection.

P284: [In case of inadequate ventilation] wear respiratory protection.

SECTION 3. Composition / information on ingredients

The difference between the single product and mixture: Mixture

INCI Name	CAS No.	%	Function
C12-14 Alketh-9	68439-50-9	10-30	Cleansing
Laureth-9	9002-92-0	10-20	Surfactant
Aqua (Water)	7732-18-5	1-25	Solvent
Dodecylbenzene Sulfonic Acid	27176-87-0	1-20	Cleansing
Sodium Laureth Sulfate	68585-34-2	1-15	Cleansing
Sorbitol	50-70-4	1-10	Humectant
Ethanolamine	141-43-5	1-10	Buffering
Propylene Glycol	57-55-6	1-10	Solvent
PEG-400	25322-68-3	1-10	Binding
Fragrance	N/A	0.3	Perfuming
BHT	128-37-0	0.01-2	Antioxidant
Phenoxyethanol	122-99-6	0.1-2	Preservative
Linalool	78-70-6	Allergen	Perfuming-Allergen

SECTION 4. First aid measures

General advice: Immediate medical attention is required. Show this safety data sheet (MSDS) to the doctor in attendance.

- 4.1 Following eye contact:

Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. Seek medical attention immediately.

- 4.2 Following skin contact:

Wash skin with water. Immediately consult a physician if feeling uncomfortable.

- 4.3 Following inhalation:

Move victim into fresh air. If breathing is difficult, give oxygen. If not breathing, give cardiopulmonary resuscitation and consult a physician immediately.

- 4.4 Following ingestion:

If it is ingested, rinse the mouth with water. Seek medical attention immediately.

SECTION 5. Firefighting measures

- 5.1 Special hazards arising from the substance or mixture: Not considered to be a fire hazard. Not easily ignited by fire.
- 5.2 Extinguishing Media:

Dry powder, Chemical foam, Carbon dioxide, water mist.

- 5.3 Advice for firefighters:

As in any fire, wear self-contained breathing apparatus (MSHA/NIOSH approved or equivalent) and full

protective gear.

Extinguish fire in a safe distance with enough protection

Prevent fire extinguishing water from contaminating surface water or the ground water system.

- 5.4 Hazardous combustion products: No data available.

SECTION 6. Accidental release measures

- 6.1 Personal precautions, protective equipment and emergency procedures: Do not let this product come into direct contact with eyes.

Ensure adequate ventilation. Clear all fire sources.

Evacuate personnel to safe areas. Keep people away from upwind of spill/leak. Wear appropriate protection (SEE SECTION 8).

- 6.2 Environmental precautions:

If the product contaminates lakes, rivers, inform appropriate authorities in accordance with local regulations.

- 6.3 Cleaning method:

Remove by liquid absorbing material (e.g. kieselguhr). Adhered or collected material should be promptly disposed of. Disposal of discarded waste/pollutants refers to SECTION 13.

SECTION 7. Safe handling and storage

- 7.1 Handling Notes:

Keep away from fire and heat.

Keep indoor ventilation or local exhaust device.

When handling, load and unload with care to prevent damage to packaging and containers. This product is not edible and should be kept out of the reach of children and pets.

Do not let this product come into direct contact with eyes. Do not touch the beads with wet hands.

Avoid moisture.

Do not touch water.

- 7.2 Storage Notes:

Keep away from fire and heat. Store in a cool, ventilated place.

Pay attention to sealed storage to avoid moisture. Do not touch water.

Stored in compatible containers. Keep storage containers sealed.

Do not store with food containers or incompatible materials (see section 10.2)

SECTION 8. Exposure controls / personal protection

- 8.1 Occupational Exposure Limit: No information found

- 8.2 Engineering Control:

Provide adequate ventilation. Where reasonably practicable, this should be achieved by the use of local exhaust ventilation and good general extraction. If these are not sufficient to maintain concentrations of particulates and solvent vapour below the OEL, suitable respiratory protection must be worn.

Ensure that eyewash stations and safety showers are proximal to the work-station location.

- 8.3 Respiratory Protection:

No special protection is required under normal conditions. Wear a filter mask when necessary.

- 8.4 Eyes Protection:

No special protection is required under normal conditions. Wear protective glasses when necessary.

- 8.5 Hands Protection:

No special protection is required under normal conditions. Wear protective gloves when necessary.

- 8.6 Sanitary Measure:

Forbid smoking, eating and drinking in working places. Washing hands after handling products.

SECTION 9. Physical and chemical properties

Appearance and Color	Solid contains liquid
Odour	Weak odor
PH value	7.5
Flammability	Non flammable
Flash point (°C, Closed cup)	No Data
Boiling point(°C)	No Data
Freezing point (°C)	No Data
Density(g/cm³)	No Data
Relative steam density (air = 1)	No Data
Vapor pressure(MPa)	No Data
Octanol/water partition coefficient	No Data
Viscosity (mPa/s)	No Data
Evaporation rate (kg/s)	No Data
UEL %(V/V)	No Data
LEL %(V/V)	No Data

Auto-ignition temperature(°C): No Data Decomposition

temperature(°C): No Data

Solubility: Soluble in water

SECTION 10. Stability and reactivity

- 10.1 Stability:

Stable under recommended storage and handling conditions (See section 7).

- 10.2 Material for avoiding: Strong oxide, acid and alkali.

- 10.3 Contact conditions for avoiding:

Water, Fire, Moisture, High temperature.

- 10.4 Hazardous decomposition products: No data available.

SECTION 11. Toxicological information

- 11.1 Acute toxicity:

No information found.

- 11.2 Skin corrosion/irritation: No information found.

- 11.3 Serious eye damage/irritation: Causes serious eye irritation

- 11.4 Respiratory or skin sensitisation:

May cause allergy or asthma symptoms or breathing difficulties if inhaled

- 11.5 Germ cell mutagenicity: No information found.

- 11.6 Carcinogenicity: No information found.

- 11.7 Reproductive toxicity: No information found.

- 11.8 STOT-single exposure: No information found.

- 11.9 STOT-repeated exposure: No information found.

- 11.10 Aspiration hazard.: No information found.

SECTION 12. Ecological information

- 12.1 Ecotoxicity:

According to the environmental protection laws, this product can't be discarded in those places which would affect soil and underground water.

- 12.2 Persistence and degradability: No data available.

- 12.3 Bioaccumulative potential: No data available.

- 12.4 Mobility in soil: No data available.

- 12.5 Other adverse effects: No data available

SECTION 13. Disposal considerations

- 13.1 Handling method for waste:

Handling waste according to the local regulations. Contact specific waste disposal company or companies recommended by local laws.

- 13.2 Handling method for uncleaned packaging: According to official regulations.

SECTION 14. Transport information

IMDG, ICAO/IATA, ADR/RID 14.1 UN NO.: 3082

IMDG, ICAO/IATA, ADR/RID 14.2 Class: 9

IMDG, ICAO/IATA, ADR/RID 14.3 Packaging group: III IMDG, ICAO/IATA, ADR/RID 14.4 Technical name:

ENVIRONMENTALLY HAZARDOUS SUBSTANCE, LIQUID, N.O.S.

IMDG, ICAO/IATA, ADR/RID 14.5 Label: [Hazard labels]

14.6 Attention Notes: Gentle with, prevent collision drag and dump. Prohibition with antioxidant and chemical mixed stowage, transit should prevent sun, fire, rain and high temperature.

SECTION 15. Regulatory information

Hazardous chemicals catalog

International maritime dangerous goods code Dangerous Goods

Number Of United Nations

Technical Instructions for the Safe Transport of Dangerous Goods by Air Classification and code of dangerous goods

Occupational Safety and Health Act (OSHA)

The principle of classification of transport packaging groups of dangerous goods Globally

Harmonized System of Classification and Labelling of Chemicals

In accordance with all local laws.

SECTION 16. Other information

Disclaimer

The information in this Material Safety Data Sheet was obtained from sources which we believe are reliable. However, the information is provided without any warranty, express or implied, regarding its correctness. The conditions or methods of handling, storage, use or disposal of the product are beyond our control and may be beyond our knowledge. For this and other reasons, we do not assume responsibility and expressly disclaim liability for loss, damage or expense arising out of or in any way connected with the handling, storage, use or disposal of the product. This MSDS was prepared and is to be used only for this product. This information is furnished upon condition that the person receiving it shall make his own determination of the suitability of the material for his particular purpose.