ABB BALDOR RELIANCE

Customer information packet

L1317-50

2/1.5KW, 2910RPM, 1PH, 50HZ, 56, 3536LC, OPEN
Class - None
Division - Not Applicable

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/5/2026 9:02:16 AM

Specifications

Enclosure	OPEN
Frame	56
Frame Material	Steel
Frequency	50.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Cap Start, Cap Run
Output @ Frequency	1.500 KW @ 50 HZ
Phase	1
Synchronous Speed @ Frequency	3000 RPM @ 50 HZ
Voltage @ Frequency	220.0 V @ 50 HZ
Agency Approvals	CE
	CURUS
	UKCA
	WEEE
	C UR US
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	8.100 A @ 220.0 V
Design Code	-
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	84.0 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Shaft Indicator	None
Heater Indicator	No Heater
High Voltage Full Load Amps	8.1 a

Part Detail

Revision	F
Type	AC
Mech. spec.	35M497
Base	
Status	PRD/A
Elec. spec.	35WGG773
Layout	35LYM497
Eff. date	04-20-2026
CD Diagram	CD0055
Poles	02
Leads	4#14 A PH,2#16 B PH
Proprietary	False
Created date	05-25-2023

Insulation Class	F
Inverter Code	Not Inverter
IP Rating	NONE
KVA Code	J
Lifting Lugs	No Lifting Lugs
Locked Bearing Indicator	No Locked Bearing
Motor Lead Quantity/Wire Size	4 @ 14 AWG, A PH
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3536LC
Mounting Arrangement	F1
Number of Poles	2
Overall Length	14.32 IN
Power Factor	98
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	Standard
Pulley Shaft Indicator	Standard
Rodent Screen	None
RoHS Status	ROHS COMPLIANT
Service Factor	1.15
Shaft Diameter	0.625 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	2910 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP1372L									
CAT.NO.	L1317-50								
SPEC.	35M497G773G1								
HP	2/1.5KW								
VOLTS	110/220								
AMP	17/8.5								
R.P.M. (1/MIN)	2910								
FRAME	56		**HZ**	50			**PH**	1	
SER.F.	1.15	**CODE**	J	**DES**	-	**CL**	F		
NEMA-NOM-EFF	84	**PF**	95						
RATING	40C AMB-S1 CONT								
CC			IP22 KG27 IC01						
DE	6205		**ODE**	6203					
ENCL	OPEN	**SN**							
	IE2 85.1(75%) 82.7(50%)								

Accessories

Part number	Description	Multiplier
35-8764	C FACE KIT	A8
35EP1604A01SP	D-FLANGE KIT	

AC Induction Motor Performance Data
Record # 101571
Typical performance - not guaranteed values


Winding: 35WGG773-R001	**Type:** 3536LC	**Enclosure:** OPEN


Nameplate Data			
Rated Output (KW)			1.5
Volts			110/220
Full Load Amps			17/8.5
R.P.M.			2910
Hz	50	**Phase**	1
NEMA Design Code	-	**KVA Code**	J
Service Factor (S.F.)			1.15
NEMA Nom. Eff.	84	**Power Factor**	95
Rating - Duty			40C AMB-CONT
S.F. Amps			

110 V, 50 Hz: High Voltage Connection	
Full Load Torque	3.63 LB-FT
Start Configuration	direct on line
Breakdown Torque	10.3 LB-FT
Pull-up Torque	7.4 LB-FT
Locked-rotor Torque	10 LB-FT
Starting Current	132 A
No-load Current	4.86 A
Line-line Res. @ 25ºC	0.23 Ω A Ph 0.634 Ω B Ph
Temp. Rise @ Rated Load	30°C
Temp. Rise @ S.F. Load	37°C
Locked-rotor Power Factor	85.3
Rotor inertia	0.0774 lb-ft²


Load Characteristics 110 V, 50 Hz, 1.5 KW

% of Rated Load	**25**	**50**	**75**	**100**	**125**	**150**	**S.F.**
Power Factor	77	90	93	95	96	95	96
Efficiency	71.9	82.7	85.1	85.1	83.6	81.4	84.2
Speed	2976	2957	2934	2910	2883	2850	2894
Line amperes	6.19	9.21	12.92	16.92	21.34	26.45	19.6


ABB Motors and Mechanical Inc.
WINDING # 35WGG773
1.5 KW 1 PH 50 HZ 2910 RPM 110 V 3536LC
Typical performance - not guaranteed values.
TORQUES(LB-FT): PO=10.3 PU=7.4 LR=10 LRA=132
TORQUE
RPM
WATTS
AMPS
EFF
PF
%EFF %PF
TORQUE (LB-FT)
RPM
WATTS
AMPS
PERCENT OF RATED OUTPUT (1.5 KW)
11/5/2026 ACPERF, record # 101571


35LYM497
510-528 = 12.07
529-535 = 12.94
536-546 = 14.32
2.60
2.44
1.88
.19 KEY
1.38 LONG
NAMEPLATE
Ø .6250
.6245
4 SLOTS
.34 WIDE
.66
3.00
2.75
4.32
6.62
5.61
4.11
2.18
6.78
3.50
3.44
THERMAL
(WHEN
REQ'D)
LEAD HOLE
.88 DIA.
2.47
2.47
4.55
3.31
6.62
CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT BALDOR'S PRODUCT WILL PERFORM SUITABLY IN THE INTEDED APPLICATION.
REV. DESC: ADD THERMAL DIMS AND THERMAL WHEN REQUIRED NOTE
REV: E
VERSION: 05
REVISED: 07:55:50 04/04/2023
TDR: 000001205626
MODEL NO: 35LYM497
REF: -
BY: USBUFRA
Material: -
B
BALDOR - RELIANCE®
STD HORZ 56 OPEN 35LC
SH 1 of 1
35LYM497

CD0055



	LINE A	LINE B	JOIN
HIGH STD	1	4,5	2,3,8
HIGH OPP	1	4,8	2,3,5
LOW STD	1,3,8	2,4,5	–
LOW OPP	1,3,5	2,4,8	–

NOTES:

1. STANDARD ROTATION IS CCW FACING END OPPOSITE SHAFT EXTENSION.
2. OPTIONAL THERMOSTAT IS PROVIDED WHEN SPECIFIED.
3. MULTIPLE CAPACITORS ARE CONNECTED IN PARALLEL UNLESS OTHERWISE SPECIFIED.
4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

CD0055

REV. DESC: REVISE TO SHOW OPTIONAL COLORS			BALDOR ELECTRIC Co.
REV. LTR: D	BY: JLP	REVISED: 04/08/99 1:17	TDR: 0178636
CD0055		FILE: AAA00007414	MDL: –
		MTL: –	TYPE LC, DV, REV, 6 LEADS