



**Airflow
You
Trust**

Confined Space Ventilators • Dehumidification

Dehumidifier



Product Description

Choose the AMERIC® AMD-100A-115 —the quietest, highest-performing compact dehumidifier your techs will reach for first. Perfectly sized for everyday jobs, the AMD-100A-115 is built with AMERIC durability to handle years of demanding use. It removes more water than any other unit in its class and features grain-depression monitoring, drying-progress graphs, quick-access humidistat controls, and more.



Features and Benefits

- Offers quick, convenient access to humidistat settings, job hours, maintenance alerts, and more.
- Spill-proof pump basin contains any residual water after the final purge.
- Exceptionally durable, designed to roll up stairs with ease and stack neatly for storage.

Key Specs

Model Number	AMD-100A-115
Brand	Americ®
Type	Low Grain Refrigerant
Dimensions (L x W x H)	18.5" x 17.5" x 30"
Tested Water Removal AHAM (80°F, 60%RH)	100 Pints/ Day
Full Saturation (90F, 90%RH)	219 Pints/Day
Process Air Rating	380 CFM
Maximum Operating Humidity	90%
Minimum Operating Humidity	10%

Handle	Steel, Fold Down
Power 115 Volt	6.4 Amp
Defrost Type	Fan Defrost
Controls	Electronic Touchpad
Refridgerant	R32
Housing	Rotomolded Polyethylene
Safety	CSA (TBD)
Noise Level	≤ 58 dB