



## GRC58

by Burndy  
Catalog ID: GRC58

Prop 65 Notice

Mechanical Ground Rod Clamp, For Cable to Rod, High Strength, 10 AWG (Sol)- 1 AWG (Str), 5/8" Drive Rod, 3/8" Stud.

Features: High Copper Alloy Ground Connector For Joining A Range Of Cable To Copper Clad, Galvanized Steel, And Stainless Steel Ground Rods, Slips Over End Of Rod, One-Wrench Installation, UL467 Listed For Direct Burial In Earth And Concrete, Ground Rod Size: 5/8 IN, Stud/bolt Size: 3/8 IN, Width: 0.95 IN, Length: 0.63 IN, Height: 2.19 IN

## Product Details

### General

Application	For Joining A Range Of Cable To Copper Clad, Galvanized Steel, And Stainless Steel Ground Rods, Direct Burial Applications In Earth And Concrete
Installation Torque Recommended in-lb	170 in-lb
Material	Copper Alloy
Plated	N
Plating Type	Unplated
Sub Brand	MECHANICAL CONNECTOR
Type	GRC, High Strength
UPC	781810230961
UPC 12 Digit	7818102309611

### Dimensions

Dimension - B Length inch	0.57 in
Dimension - Height inch	2.18 in
Dimension - Length Side B inch	0.63 in
Dimension - Width inch	0.95 in
Dimension - Width mm	24 mm

### Conductor Related

Conductor - Copper Solid Size Range	10 AWG
Conductor - Copper Str Size Range	12 AWG-1 AWG
Conductor - Rod Size	5/8 in
Conductor Size	#10 AWG Sol - #1 AWG Str
Conductor Type	<ul style="list-style-type: none"> <li>Rod-Size</li> <li>CU C Solid-Size</li> </ul>

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes

Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	RUS
Standards - Industry Standards Met	RUS
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Minimum Pack Quantity	1
-----------------------	---

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)