

## 64261



### Product features and benefits

- Precise filament alignment with patented quartz pinch technology
- OSRAM HLX lamps provide 10% higher luminous efficacy over standard halogen
- Instant on and nearly constant luminous flux over the life of the lamp
- Dimmable

### Areas of application

- Microscopy
- Laboratory & Analysis
- UV Curing
- Fiber Illumination
- Surgical & Dental Overhead
- Club & Disco

## Product datasheet

### Technical data

#### General product information

Product Number	54247
Product Name	64261 12V 40/CS 1/SKU
Ordering Abbreviation	64261
Brand Name	OSRAM
General Description	30 Watt, tungsten halogen, low voltage without reflector
Application	Projector
LIF Code	M/130

#### Electrical data

Nominal Wattage	30 W
Nominal Voltage	12 V
Type of Current	AC

#### Light technical data

Luminous Flux	750 lm
Light Center Length - LCL (in)	1.17 in
Light Center Length - LCL (mm)	30 mm
Color Rendering Index	100
Average Rated Life	50 h

#### Physical attributes


Base	G6.35 Bipin
Bulb Shape	T3.25
Maximum Overall Length (in)	1.716 in
Maximum Overall Length (mm)	44 mm
Length l (in)	1.716 in
Length l (mm)	44 mm
Diameter d (in)	0.472 in
Diameter d (mm)	12.00 mm
Distance a (in)	1.170 in
Distance a (mm)	30 mm
Filament Dimensions Length (in)	0.0510 in
Filament Dimensions Length (mm)	1.3 mm
Filament Dimensions Width (in)	0.101 in
Filament Dimensions Width (mm)	2.6 mm

## Product datasheet

Reflector Coating	12.00
-------------------	-------

### Additional product data

Operating Position	Any
Class	C (gas)
Lamp Type	SINGLE END



s180

### Packaging Information

Product number	EAN/UPC	Packaging	Quantity	Outside dimensions l x w x h	Gross weight
54247	4050300220529	Folding box (SKU)	1		
54247	4050300890364	Shipping box (Case)	40	5.7 in x 4.2 in x 4.8 in	0.5 lb

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

### Disclaimer

OSRAM does not accept liability for errors, changes and omissions.