

MAXX Floor Stripper

Page 1 of 2

CLASSIFICATION

Powerful, ultra-concentrated floor finish stripper

PRODUCT DESCRIPTION

- Powerful, ultra-concentrated floor finish stripper
- Effectively removes MAXX Durable Floor Finish
- Butyl-free formula for the toughest floor stripping needs
- Low odor
- For use on VCT, vinyl and terrazzo floors

USE

FOR INDUSTRIAL USE ONLY - NOT FOR HOUSEHOLD USE

Use on vinyl and vinyl asbestos floor tiles, terrazzo and concrete floors. Before use on asphalt tile, test use-dilution in a hidden area to ensure bleaching, bleeding or softening does not occur. DO NOT use on linoleum, rubber, marble or wood floors.

DIRECTIONS FOR USE (For Removing MAXX Durable):

1. Apply solution liberally with mop and allow solution to dwell for 20 minutes (5-7 coats) or 30 minutes (7+ coats). Do not allow solution to dry – add more as needed.
2. Scrub thoroughly with a high productivity floor pad.
3. Pick up with wet vacuum, auto scrubber or mop.
4. Ensure removal of residue by rinsing floor thoroughly with clean water or Ecolab neutralizer.
5. Pick up with wet vacuum, auto scrubber or mop.
6. Rinse floor with clean water and allow floor to dry completely before applying Ecolab floor finish.

MAXX Durable DILUTIONS: 1:4 Heavy Build

DIRECTIONS FOR USE (Removing Conventional Finishes):

1. Apply solution liberally with mop and allow solution to dwell for 10 minutes (allow 15 minutes for heavy buildup). Do not allow solution to dry – add more as needed.
2. Scrub thoroughly with black pad or stripping brush.
3. Pick up with wet vacuum, auto scrubber or mop.
4. Ensure removal of residue by rinsing floor thoroughly with clean water or Ecolab neutralizer.
5. Pick up with wet vacuum, auto scrubber or mop.
6. Rinse floor with clean water and allow floor to dry completely before applying Ecolab floor finish.

CONVENTIONAL DILUTIONS:

1:8 Heavy build-up (10+ coats) / highly burnished finishes
1:10 – 1:15 Medium build-up
1:16 – 1:24 Light build-up

Consult your Ecolab Specialist or call 1-800-35 CLEAN (352-5326) for specific use directions, service, or additional information.

PHYSICAL AND CHEMICAL PROPERTIES

Physical State Liquid
Color Clear, Amber
Odor Sweet
pH 13.5 - 14.0 (100%)

Ingredients:

Water	7732-18-5
Benzyl alcohol	100-51-6
Monoethanolamine	141-43-5
Sodium dodecylbenzene sulfonate	25155-30-0
9,12-octadecadienoic acid (z,z)-, sodium salt	822-17-3
Sodium hydroxide	1310-73-2

% P Formula ingredients contain no phosphorus

PACKAGING / PRODUCT NUMBERS

Size Available	Product Number
9.46 L (2.5 US GAL)	6101130