

Business Essential


Satellite Pro C40-K / C50-K

The Perfect Balance Between Performance and Portability

Experience seamless performance and portability with the ultraportable Satellite Pro C40/C50 series. This ultra-slim, narrow-bezel laptop is designed for stylish, efficient multitasking, featuring the latest Intel® Core processors (Series 1) and Windows 11 Pro.



<i>Satellite Pro C40-K</i>		<i>Satellite Pro C50-K</i>	
Thin & Sleek 18.75mm	From 1.36kg*	Thin & Sleek 18.95mm	From 1.54kg*



Powered by the latest Intel Core™ processors, up to 32GB of memory and 1TB of storage



Choice of HD and FHD Anti-glare displays with narrow bezels for a comfortable viewing experience



HD webcam with camera shutter and AI-enhanced audio capabilities



Fingerprint reader for boosted security



Full ports connectivity with 4 USB ports, HDMI, and built-in LAN for collaboration anywhere



Anti-Bacterial coating to keep you safe



Lay-flat 180° hinge



Intel® Core™ 7 processor

Why Dynabook?

Over three decades of business innovation

Dynabook is the world's laptop pioneer, with an unrivaled track record of helping businesses succeed with leading-edge mobile solutions.

Dynabook controls the entire process

For unmatched quality and reliability, our Satellite Pro series PCs are designed, engineered and manufactured at Dynabook facilities. The same goes for our image development services.

Quality, reliability, performance. You have our assurance

Dynabook's extremely rigorous pre-production testing process for our business-class mobile computers has dramatically lowered annual field failure rates.

Product Highlights



A Valuable Mix of Power and Efficiency

Offering the latest Intel Core™ processors (Series 1), up to 32GB of memory and up to 1TB storage, the Satellite Pro laptops offer accelerated performance for effortless task management and browsing.



Maintains A Cleaner Work Surface

With an EPA-approved IONPURE IPL coating, Satellite Pro™ laptop chassis inhibits microbial growth, ensuring a cleaner work environment for usersm whether in classrooms, offices, or shared workspaces.



Collaboration Comes Naturally

Featuring a privacy shutter webcam, dual microphones, and stereo speakers, Satellite Pro laptops enhance collaboration, enabling users to engage in clear and productive video conferences and virtual meetings.



Security Taken Seriously

Built to withstand a variety of threats, Satellite Pro laptops incorporate firmware TPM (fTPM) 2.0 technology and a security lock slot, providing peace of mind against unauthorized access and data breaches.




Ports for Versatile Connectivity

Designed with a comprehensive selection of ports, including HDMI, Gigabit LAN, USB-C, USB-A, and a microSD card slot for seamless, clutter-free connections with peripherals and accessories.



Proven Reliability

Satellite Pro laptops are backed by proven reliability and come standard with Dynabook Limited Warranty with the option of Carry-in or On-site service.



Specifications

	<i>Satellite Pro C40-K</i>	<i>Satellite Pro C50-K</i>
PROCESSOR	Intel® Core™ 3 Processor 100U (1.2GHz, up to 4.7GHz, 6 Cores (2P+4E), 10MB Cache) Intel® Core™ 5 processor 120U (1.4GHz upto 5.0GHz, 10 Cores (2P+8E), 12MB Cache) Intel® Core™ 7 Processor 150U (1.8GHz, up to 5.4GHz, 10 Cores (2P+8E), 12MB Cache)	
OPERATING SYSTEM	Windows 11 Pro	
GRAPHICS	Up to Intel® Iris® Xe Graphics	
SYSTEM MEMORY	Choice of 8GB / 16GB DDR4 (3,200 MHz) up to a maximum of 32GB (two fully configurable slots)	
DISPLAY	14" Full HD Anti-Glare (250NIT) IPS display, resolution 1,920 x 1,080	15.6" Full HD Anti-Glare (250NIT) IPS display, resolution 1,920 x 1,080
HARD DISK*	Choice of 256GB, 512GB Gen 3 PCIe NVMe Solid State Drive or 1TB Gen 4 PCIe NVMe Solid State Drive	
INPUT DEVICES	ClickPad with antibacterial coating	
COMMUNICATIONS	Intel® Wi-Fi 6 Dual Band Wireless LAN (802.11ax), Bluetooth® 5.2	
BUILT-IN CAMERA / MICROPHONE	HD webcam with shutter slider and LED indicator. Infrared camera with Face Authentication (optional). Dual Mic supports beam forming and AI-powered noise reduction technology	
SOUND SYSTEM	Stereo speakers	
KEYBOARD	Frameless matte black tiled keyboard with antibacterial coating. Dedicated conference call function keys	Frameless matte black tiled keyboard with numeric keypad, antibacterial coating. Dedicated conference call function keys
INTERFACES	3x USB 3.2 Type-A, 1x USB 3.2 Type-C™ Gen 2 (supporting power delivery, data transfer and display), HDMI-out, RJ-45, headphone/microphone combo, MicroSD card reader	
BATTERY TYPE	3-cell, 45Whr Lithium-Ion Polymer (not user replaceable). Quick charge technology (30 minutes charge = 4 hours of battery). Battery management eco utility for conservation of the battery lifespan	
POWER RATING	45W 100-240V/50-60Hz Universal AC Adaptor	
SECURITY FEATURES	Firmware Trusted Platform Module (fTPM) 2.0, Fingerprint Reader (optional), Infrared (IR) camera for Face Authentication (optional), Camera shutter slider, Security lock slot	
PROTECTION FEATURES	180-degree hinge, Antibacterial paint coating (chassis, keyboard and Clickpad), Slim bezels (83% screen-to-body ratio)	
PHYSICAL DIMENSIONS	323.9 x 211.8 x 18.75mm	358.9 x 230.5 x 18.95mm
WEIGHT	Starting from 1.35kg	Starting from 1.52kg
WARRANTY*	1-year Local limited warranty (carry-in), 1-year battery	

* Actual product features and specifications depend on model and local availability. For more information, please visit <http://asia.dynabook.com>
+ Dynabook's standard limited warranty terms and limitations apply. For more details, please visit <https://asia.dynabook.com/warranty/laptop/>

Optional Accessories

- Dynabook Business Backpack (up to 16")
- Dynabook USB-C™ Dock (Support up to 3 displays)
- Additional dynabook Universal USB Type C™ PD AC Adaptor

