

162 iS PH/S VDE Insulated screwdriver with reduced blade diameter for PlusMinus screws (Phillips/slotted), # 1 x 80 mm



EAN:	4013288160201	Size:	178x33x33 mm
Part number:	05006455001	Weight:	54 g
Article number:	162 iS PH/S	Country of origin:	CZ
		Customs tariff number:	82054000

- Insulated blades for secure work at 1,000 volts
- Smooth hard zones for high speed turning, soft grip zones for high torque transfer
- Handle markings simplify finding and sorting of tools
- Hexagonal anti-roll feature against rolling away
- Reduced shaft diameter; combination profile Phillips/slotted

Reduced blade diameter with integrated insulation protection so that even low-lying screw and spring elements can be accessed and actuated. Combination profile - slotted and Phillips particularly for jobs on terminal blocks, fuse boxes, switches and relays. Kraftform Plus handle for pleasant, ergonomic working that makes blisters and calluses a thing of the past. Hard gripping zones for high working speeds whereas soft zones ensure high torque transfer. The anti-roll feature prevents any bothersome rolling away at the workplace.



VDE
TOOL



EXTRA
SLIM



KRAFTFORM
ERGONOMICS



ANTI
ROLL-OFF

Web link

<https://www.wera.de/en/05006455001>

Wera - 162 iS PH/S
05006455001 - 4013288160201

Wera Werkzeuge GmbH
Korzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de


162 iS PH/S VDE Insulated screwdriver with reduced blade diameter for PlusMinus screws (Phillips/slotted), # 1 x 80 mm



VDE-insulated screwdriver with reduced blade diameter



The individual testing at 10,000 volts, in accordance with IEC 60900, ensures safe working with loads up to 1,000 volts.



Reduced blade diameter with integrated protective insulation, allows sunken screws and spring elements to be accessed and actuated, individually tested as per IEC 60900.

Individually tested



The individual testing at 10,000 volts, in accordance with IEC 60900, ensures safe working with loads up to 1,000 volts.

Impact strength test



Impact strength tested at -40°C, guaranteeing safety even under extreme conditions.

Multicomponent Kraftform handle



Wera produces the Kraftform handle out of several materials with different properties. A resistant plastic is used for the core which ensures that the blade is held securely even under high strain. A softer material is used for the coloured soft zones, which provides high frictional resistance and allows the transfer of high forces - resulting in less required screwdriving effort. The red sections with their hard surfaces prevent any "sticking" of the hand to the handle, making rapid repositioning of the hand possible.

Prevents hand injuries



The outstanding design of the Kraftform handle that fits perfectly into the hand prevents hand injuries such as blisters and calluses.

Rapid hand repositioning



The hard materials used for the handle ensure rapid hand repositioning without any danger of the skin "sticking" to the handle. The surrounding hard zones with large diameters glide like wheels through the hand.

Identification marking



The screw profile and tip size identification markings on the handle make it easier to find the right screwdriver in the tool case, or at the workplace.

Web link
<https://www.wera.de/en/05006455001>

Wera - 162 iS PH/S
 05006455001 - 4013288160201

Wera Werkzeuge GmbH
 Korzter Straße 21-25
 D-42349 Wuppertal
 Tel: +49 (0)2 02 / 40 45-0
 E-Mail: info@wera.de

162 iS PH/S VDE Insulated screwdriver with reduced blade diameter for PlusMinus screws (Phillips/slotted), # 1 x 80 mm



Further versions in this product family:



mm



mm



inch

05006455001	# 1	80	98	3 1/8"
05006456001	# 2	100	105	4"

Web link

<https://www.wera.de/en/05006455001>

Wera - 162 iS PH/S

05006455001 - 4013288160201

Wera Werkzeuge GmbH

Korzter Straße 21-25

D-42349 Wuppertal

Tel: +49 (0)2 02 / 40 45-0

E-Mail: info@wera.de