ABB BALDOR RELIANCE

Customer information packet

EJMM2333T-5

15HP, 1765RPM, 3PH, 60HZ, 254JM, 0944M, TEFC, F
Class - None
Division - Not Applicable

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/5/2026 10:17:46 AM

Specifications

Enclosure	TEFC
Frame	254JM
Frame Material	Iron
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	15.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	575.0 V @ 60 HZ
Agency Approvals	UR
	CSA
	CSA EEV
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	14.600 A @ 575.0 V
Design Code	A
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	92.4 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Face Code	Standard
Front Shaft Indicator	None
Heater Indicator	No Heater
High Voltage Full Load Amps	14.6 a
Insulation Class	F

Part Detail

Revision	U
Type	AC
Mech. spec.	09P14
Base	
Status	PRD/A
Elec. spec.	09WGT124
Layout	09LYP014
Eff. date	04-16-2024
CD Diagram	CD0006
Poles	04
Leads	3#12
Proprietary	False
Created date	08-18-2015

Inverter Code	Inverter Ready
KVA Code	H
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Motor Lead Exit	Ko Box
Motor Lead Quantity/Wire Size	3 @ 12 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	0944M
Mounting Arrangement	F1
Number of Poles	4
Overall Length	25.30 IN
Power Factor	83
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	C-Face
Pulley Shaft Indicator	Tapped & Key
Rodent Screen	None
Service Factor	1.15
Shaft Diameter	1.750 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	Shaft Slinger
Speed	1765 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP3441L									
CAT.NO.	EJMM2333T-5								
SPEC.	09P014T124G2								
HP	15								
VOLTS	575								
AMP	14.6								
RPM	1765								
FRAME	254JM	**HZ**	60				**PH**	3	
SER.F.	1.15	**CODE**	H	**DES**	A	**CL**	F		
NEMA-NOM-EFF	92.4	**PF**	83						
RATING	40C AMB-CONT								
CC	010A								
DE	6309	**ODE**	6208						
ENCL	TEFC	**SN**							
VPWM INVERTER READY									
CT6-60H(10:1)VT3-60H(20:1									
	SFA 16.7								

AC Induction Motor Performance Data
Record # 47378
Typical performance - not guaranteed values

Winding: 09WGT124-R001	**Type:** 0944M	**Enclosure:** TEFC

Nameplate Data				**575 V, 60 Hz: Single Voltage Motor**	
Rated Output (HP)			15	**Full Load Torque**	44.5 LB-FT
Volts			575	**Start Configuration**	direct on line
Full Load Amps			14.6	**Breakdown Torque**	153 LB-FT
R.P.M.			1765	**Pull-up Torque**	69.5 LB-FT
Hz	60	**Phase**	3	**Locked-rotor Torque**	86.5 LB-FT
NEMA Design Code	A	**KVA Code**	H	**Starting Current**	102 A
Service Factor (S.F.)			1.15	**No-load Current**	6.05 A
NEMA Nom. Eff.	92.4	**Power Factor**	83	**Line-line Res. @ 25ºC**	0.874 Ω
Rating - Duty			40C AMB-CONT	**Temp. Rise @ Rated Load**	54°C
S.F. Amps				**Temp. Rise @ S.F. Load**	66°C
				Locked-rotor Power Factor	33.1
				Rotor inertia	1.92 lb-ft²

Load Characteristics 575 V, 60 Hz, 15 HP

% of Rated Load	**25**	**50**	**75**	**100**	**125**	**150**	**S.F.**
Power Factor	45	69	78	83	85	87	86
Efficiency	88.1	92.3	92.6	92.4	91.5	90.5	92.2
Speed	1791	1783	1774	1765	1755	1743	1769
Line amperes	6.9	8.8	11.6	14.6	18.1	21.5	16.3


ABB Motors and Mechanical Inc.


WINDING # 09WGT124

15 HP 3 PH 60 HZ 1765 RPM 575 V 0944M

Typical performance - not guaranteed values.


TORQUES(LB-FT): PO=153 PU=69.5 LR=86.5 LRA=102





09LYP014
(920 - 956)
(920 - 960 4,6,8 PL ONLY)
25.36
10.11
5.250±.031
CHECK W/GAUGE T-9041
3.000±.02
.625±.02
.25
.25 KEY
2.50 LONG
Ø8.500
8.497
Ø 1.2495
1.2490
Ø 1.750
1.748
Ø9.09
.50-13 (CL.3B)
R.H. TAP
1.12 DEEP
SLINGER
8 HOLES
Ø.53
AUTO DRAIN
(EA. END)
8.25
8.25
.75
10.00
4.75
11.50
12.94
10.19
6.62
2.70
45°
45°
12.88
6.25
6.19
LEAD
HOLE
Ø1.75
4 HOLES
.50-13 TAP
ON Ø7.25 B.C.
5.00
5.00
8.18
5.75
11.50
R.054
.043
Ø 1.3750
1.3745
Ø 1.202
1.196
UNDERCUT DETAIL
CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT THE PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION
REV. DESC: 09SF1107A02 WAS '1112A01;09CB3003 WAS '3002
REV: Y
VERSION: 13
REVISED: 03:12:03 04/30/2021
TDR: 000001166578
MODEL NO. 09LYP014
REF: -
BY: ENFRAJ0
B
BALDOR - RELIANCE®
HORZ TEFC 254-6JM
09LYP014


CD0006

TYPICAL WYE–CONNECTED MOTOR





TYPICAL DELTA–CONNECTED MOTOR



NOTES:

1. THREE LEAD MOTOR MAY BE EITHER WYE CONNECTED OR DELTA CONNECTED.
2. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
3. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
4. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY VARY.
5. LEAD COLORS ARE OPTIONAL. LEADS MUST BE NUMBERED AS SHOWN.

CD0006

REV. DESC: ADD CLASS CONN00000007		
REV. LTR: E	VERSION: 01	TDR: 000001099922
FILE: \AAA\00005\141	REVISED: 10:24:49 02/19/2019	BY: ENBRIR0
MTL: –		

BALDOR - RELIANCE®

3PH, SV, 3 LEADS, WYE OR DELTA CONNECTED

SH 1 of 1