



SAFETY DATA SHEET

1. Identification

Product identifier Liquid Wrench White Lithium Grease

Other means of identification

SDS number L616
Part No. L616, L616/4
Tariff code 2710.19.4000

Recommended use Grease

Recommended restrictions None known.

Manufacturer/Importer/Supplier/Distributor information

Manufacturer

Company name RSC Chemical Solutions
Address 600 Radiator Road
Indian Trail, NC 28079
United States
Telephone Customer Service: (704) 821-7643
Technical: (704) 821-7643
Website www.rscbrands.com
E-mail sds@rscbrands.com
Emergency phone number Emergency Telephone: (303) 623-5716
Emergency Contact: RMPDC (877) 740-5015

2. Hazard(s) identification

Physical hazards Flammable aerosols Classification not possible

Health hazards Acute toxicity, oral Category 4
Skin corrosion/irritation Category 2
Serious eye damage/eye irritation Category 2A
Specific target organ toxicity, single exposure Category 3 narcotic effects
Aspiration hazard Category 1

Environmental hazards Not classified.

OSHA defined hazards Not classified.

Label elements



Signal word Danger

Hazard statement Contains gas under pressure; may explode if heated. Harmful if swallowed. May be fatal if swallowed and enters airways. Causes skin irritation. Causes serious eye irritation. May cause drowsiness or dizziness.

Precautionary statement

Prevention Avoid breathing gas. Wash thoroughly after handling. Do not eat, drink or smoke when using this product. Use only outdoors or in a well-ventilated area. Wear eye protection/face protection. Wear protective gloves.

Response If swallowed: Immediately call a poison center/doctor. Rinse mouth. Do NOT induce vomiting. If on skin: Wash with plenty of water. If inhaled: Remove person to fresh air and keep comfortable for breathing. If in eyes: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. Call a poison center/doctor if you feel unwell. If skin irritation occurs: Get medical advice/attention. If eye irritation persists: Get medical advice/attention. Take off contaminated clothing and wash before reuse.

Storage Store in a well-ventilated place. Keep container tightly closed. Store locked up.

Disposal	Dispose of contents/container in accordance with local/regional/national/international regulations.
Hazard(s) not otherwise classified (HNOC)	Combustible.
Supplemental information	54.97% of the mixture consists of component(s) of unknown acute oral toxicity. % of the mixture consists of component(s) of unknown acute dermal toxicity. 26.73, 15% of the mixture consists of component(s) of unknown acute hazards to the aquatic environment. 26.73, 15% of the mixture consists of component(s) of unknown long-term hazards to the aquatic environment. NOTE: This product is a consumer product and is labeled in accordance with the US Consumer Product Safety Commission regulations which take precedence over OSHA Hazard Communication labeling. The container label may not include the OSHA label elements listed in this document. Always carefully review the entire SDS and the product label prior to use in the workplace.

3. Composition/information on ingredients

Mixtures

Chemical name	Common name and synonyms	CAS number	%
2-(2-butoxyéthoxy) Éthanol		112-34-5	20 - < 30
Distillates (petroleum), Hydrotreated Light	Hydrotreated light distillates (petroleum)	64742-47-8	20 - < 30
Stoddard Solvent And/or Solvent Naphtha (petroleum), Medium Aliphatic And/or Hydrotreated Naphtha, Heavy	(8052-41-3 and/or 64742-88-7 and /or 64742-48-9)	Trade Secret	20 - < 30
Distillates (petroleum), Hydrotreated Heavy Naphthenic		64742-52-5	10 - < 20
Carbon Dioxide		124-38-9	1 - < 3
Corrosion Inhibitor		Mixture	1 - < 3
Zinc Oxide		1314-13-2	< 0.3
Other components below reportable levels			3 - < 5

*Designates that a specific chemical identity and/or percentage of composition has been withheld as a trade secret.

4. First-aid measures

Inhalation	Remove victim to fresh air and keep at rest in a position comfortable for breathing. Call a POISON CENTER or doctor/physician if you feel unwell.
Skin contact	Remove contaminated clothing. Wash with plenty of soap and water. If skin irritation occurs: Get medical advice/attention. Wash contaminated clothing before reuse.
Eye contact	Immediately flush eyes with plenty of water for at least 15 minutes. Remove contact lenses, if present and easy to do. Continue rinsing. Get medical attention if irritation develops and persists.
Ingestion	Call a physician or poison control center immediately. Rinse mouth. Do not induce vomiting. If vomiting occurs, keep head low so that stomach content doesn't get into the lungs.
Most important symptoms/effects, acute and delayed	Aspiration may cause pulmonary edema and pneumonitis. May cause drowsiness and dizziness. Headache. Nausea, vomiting. Severe eye irritation. Symptoms may include stinging, tearing, redness, swelling, and blurred vision. Skin irritation. May cause redness and pain.
Indication of immediate medical attention and special treatment needed	Provide general supportive measures and treat symptomatically. Keep victim warm. Keep victim under observation. Symptoms may be delayed.
General information	Ensure that medical personnel are aware of the material(s) involved, and take precautions to protect themselves. Show this safety data sheet to the doctor in attendance.

5. Fire-fighting measures

Suitable extinguishing media	Alcohol resistant foam. Powder. Dry chemicals. Carbon dioxide (CO2).
Unsuitable extinguishing media	Do not use water jet as an extinguisher, as this will spread the fire.
Specific hazards arising from the chemical	During fire, gases hazardous to health may be formed.
Special protective equipment and precautions for firefighters	Self-contained breathing apparatus and full protective clothing must be worn in case of fire.
Fire fighting equipment/instructions	Cool containers exposed to heat with water spray and remove container, if no risk is involved. Containers should be cooled with water to prevent vapor pressure build up.

Specific methods	Use standard firefighting procedures and consider the hazards of other involved materials.
General fire hazards	Combustible. No unusual fire or explosion hazards noted.

6. Accidental release measures

Personal precautions, protective equipment and emergency procedures	Keep unnecessary personnel away. Keep people away from and upwind of spill/leak. Wear appropriate protective equipment and clothing during clean-up. Avoid breathing gas. Do not touch damaged containers or spilled material unless wearing appropriate protective clothing. Ensure adequate ventilation. Local authorities should be advised if significant spillages cannot be contained. For personal protection, see section 8 of the SDS.
Methods and materials for containment and cleaning up	Refer to attached safety data sheets and/or instructions for use. Stop leak if you can do so without risk. Move the cylinder to a safe and open area if the leak is irreparable. Use water spray to reduce vapors or divert vapor cloud drift. Isolate area until gas has dispersed. Keep combustibles (wood, paper, oil, etc.) away from spilled material. The product is immiscible with water and will spread on the water surface. Absorb in vermiculite, dry sand or earth and place into containers. Following product recovery, flush area with water. Small Spills: Wipe up with absorbent material (e.g. cloth, fleece). Clean surface thoroughly to remove residual contamination. For waste disposal, see section 13 of the SDS.
Environmental precautions	Avoid discharge into drains, water courses or onto the ground.

7. Handling and storage

Precautions for safe handling	Pressurized container: Do not pierce or burn, even after use. Do not use if spray button is missing or defective. Do not spray on a naked flame or any other incandescent material. Do not smoke while using or until sprayed surface is thoroughly dry. Do not cut, weld, solder, drill, grind, or expose containers to heat, flame, sparks, or other sources of ignition. Ground and bond containers when transferring material. Do not re-use empty containers. Do not taste or swallow. Avoid breathing gas. Avoid contact with eyes, skin, and clothing. Avoid prolonged or repeated contact with skin. Avoid prolonged exposure. When using, do not eat, drink or smoke. Use only in well-ventilated areas. Wear appropriate personal protective equipment. Wash hands thoroughly after handling. Observe good industrial hygiene practices.
Conditions for safe storage, including any incompatibilities	Level 2 Aerosol. Store locked up. Contents under pressure. Do not expose to heat or store at temperatures above 120°F/49°C as can may burst. Do not puncture, incinerate or crush. Do not handle or store near an open flame, heat or other sources of ignition. Store in tightly closed container. Keep out of the reach of children. Store away from incompatible materials (see Section 10 of the SDS).

8. Exposure controls/personal protection

Occupational exposure limits

The following constituents are the only constituents of the product which have a PEL, TLV or other recommended exposure limit. At this time, the other constituents have no known exposure limits.

US. OSHA Table Z-1 Limits for Air Contaminants (29 CFR 1910.1000)

Components	Type	Value	Form
Carbon Dioxide (CAS 124-38-9)	PEL	9000 mg/m3	
		5000 ppm	
Distillates (petroleum), Hydrotreated Heavy Naphthenic (CAS 64742-52-5)	PEL	5 mg/m3	Mist.
		2000 mg/m3	
		500 ppm	
Distillates (petroleum), Hydrotreated Light (CAS 64742-47-8)	PEL	400 mg/m3	
		100 ppm	
Zinc Oxide (CAS 1314-13-2)	PEL	5 mg/m3	Respirable fraction.
		5 mg/m3	Fume.
		15 mg/m3	Total dust.

US. ACGIH Threshold Limit Values

Components	Type	Value	Form
2-(2-butoxyéthoxy) Éthanol (CAS 112-34-5)	TWA	10 ppm	Inhalable fraction and vapor.
Carbon Dioxide (CAS 124-38-9)	STEL	30000 ppm	
	TWA	5000 ppm	
Distillates (petroleum), Hydrotreated Heavy Naphthenic (CAS 64742-52-5)	TWA	5 mg/m3	Inhalable fraction.
Zinc Oxide (CAS 1314-13-2)	STEL	10 mg/m3	Respirable fraction.
	TWA	2 mg/m3	Respirable fraction.

US. NIOSH: Pocket Guide to Chemical Hazards

Components	Type	Value	Form
Carbon Dioxide (CAS 124-38-9)	STEL	54000 mg/m3	
		30000 ppm	
	TWA	9000 mg/m3	
		5000 ppm	
Distillates (petroleum), Hydrotreated Heavy Naphthenic (CAS 64742-52-5)	Ceiling	1800 mg/m3	
	STEL	10 mg/m3	Mist.
Zinc Oxide (CAS 1314-13-2)	Ceiling	15 mg/m3	Dust.
	STEL	10 mg/m3	Fume.
	TWA	5 mg/m3	Fume.
		5 mg/m3	Dust.

Biological limit values

No biological exposure limits noted for the ingredient(s).

Appropriate engineering controls

Good general ventilation (typically 10 air changes per hour) should be used. Ventilation rates should be matched to conditions. If applicable, use process enclosures, local exhaust ventilation, or other engineering controls to maintain airborne levels below recommended exposure limits. If exposure limits have not been established, maintain airborne levels to an acceptable level. Provide eyewash station and safety shower.

Individual protection measures, such as personal protective equipment**Eye/face protection**

Face shield is recommended. Wear safety glasses with side shields (or goggles). Applicable for industrial settings only.

Skin protection**Hand protection**

Wear appropriate chemical resistant gloves. Applicable for industrial settings only.

Other

Wear appropriate chemical resistant clothing. Applicable for industrial settings only.

Respiratory protection

If permissible levels are exceeded use NIOSH mechanical filter / organic vapor cartridge or an air-supplied respirator. Chemical respirator with organic vapor cartridge and full facepiece if threshold limits are exceeded. Dust & vapor respirator. Applicable for industrial settings only.

Thermal hazards

Wear appropriate thermal protective clothing, when necessary.

General hygiene considerations

When using do not smoke. Keep away from food and drink. Always observe good personal hygiene measures, such as washing after handling the material and before eating, drinking, and/or smoking. Routinely wash work clothing and protective equipment to remove contaminants.

9. Physical and chemical properties**Appearance****Physical state**

Gas.

Form

Aerosol.

Color

Not available.

Odor	Not available.
Odor threshold	Not available.
pH	Not available.
Melting point/freezing point	-90.58 °F (-68.1 °C) estimated
Initial boiling point and boiling range	314.6 °F (157 °C) estimated
Flash point	104.0 °F (40.0 °C) estimated
Evaporation rate	Not available.
Flammability (solid, gas)	Not available.

Upper/lower flammability or explosive limits

Flammability limit - lower (%)	0.7 % estimated
Flammability limit - upper (%)	5 % estimated
Explosive limit - lower (%)	Not available.
Explosive limit - upper (%)	Not available.
Vapor pressure	0.174 hPa estimated
Vapor density	Not available.
Relative density	Not available.
Solubility(ies)	
Solubility (water)	Insoluble
Partition coefficient (n-octanol/water)	Not available.
Auto-ignition temperature	229 °F (109.44 °C) estimated
Decomposition temperature	Not available.
Viscosity	< 200 cps

Other information

Density	7.33 lbs/gal estimated
Explosive properties	Not explosive.
Flame extension	None
Flammability (flash back)	No
Heat of combustion (NFPA 30B)	24.97 kJ/g estimated
Oxidizing properties	Not oxidizing.
Percent volatile	24.43 % estimated
Specific gravity	0.88 estimated
VOC	0 % w/w

10. Stability and reactivity

Reactivity	The product is stable and non-reactive under normal conditions of use, storage and transport.
Chemical stability	Material is stable under normal conditions.
Possibility of hazardous reactions	No dangerous reaction known under conditions of normal use.
Conditions to avoid	Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. Avoid temperatures exceeding the flash point. Contact with incompatible materials.
Incompatible materials	Strong oxidizing agents.
Hazardous decomposition products	No hazardous decomposition products are known.

11. Toxicological information

Information on likely routes of exposure

Inhalation	May cause drowsiness and dizziness. Headache. Nausea, vomiting. Prolonged inhalation may be harmful.
-------------------	--

Skin contact	Causes skin irritation.	
Eye contact	Causes serious eye irritation.	
Ingestion	Harmful if swallowed. Droplets of the product aspirated into the lungs through ingestion or vomiting may cause a serious chemical pneumonia.	
Symptoms related to the physical, chemical and toxicological characteristics	Aspiration may cause pulmonary edema and pneumonitis. May cause drowsiness and dizziness. Headache. Nausea, vomiting. Severe eye irritation. Symptoms may include stinging, tearing, redness, swelling, and blurred vision. Skin irritation. May cause redness and pain.	
Information on toxicological effects		
Acute toxicity	May be fatal if swallowed and enters airways.	
Components	Species	Test Results
2-(2-butoxyéthoxy) Éthanol (CAS 112-34-5)		
<u>Acute</u>		
Dermal		
LD50	Rabbit	2700 mg/kg
Oral		
LD50	Rat	4500 mg/kg
Stoddard Solvent And/or Solvent Naphtha (petroleum), Medium Aliphatic And/or Hydrotreated Naphtha, Heavy		
<u>Acute</u>		
Dermal		
<i>Liquid</i> LD50	Rabbit	> 2000 mg/kg
Oral		
<i>Liquid</i> LD50	Rat	> 5000 mg/kg
Zinc Oxide (CAS 1314-13-2)		
<u>Acute</u>		
Inhalation		
LC50	Mouse	> 5.7 mg/l, 4 Hours
Oral		
LD50	Rat	> 5 g/kg
Skin corrosion/irritation	Causes skin irritation.	
Serious eye damage/eye irritation	Causes serious eye irritation.	
Respiratory or skin sensitization		
Respiratory sensitization	Not a respiratory sensitizer.	
Skin sensitization	This product is not expected to cause skin sensitization.	
Germ cell mutagenicity	No data available to indicate product or any components present at greater than 0.1% are mutagenic or genotoxic.	
Carcinogenicity	Risk of cancer cannot be excluded with prolonged exposure.	
IARC Monographs. Overall Evaluation of Carcinogenicity		
Not listed.		
OSHA Specifically Regulated Substances (29 CFR 1910.1001-1052)		
Not regulated.		
US. National Toxicology Program (NTP) Report on Carcinogens		
Not listed.		
Reproductive toxicity	This product is not expected to cause reproductive or developmental effects.	
Specific target organ toxicity - single exposure	May cause drowsiness and dizziness.	
Specific target organ toxicity - repeated exposure	Not classified.	
Aspiration hazard	May be fatal if swallowed and enters airways.	
Chronic effects	Prolonged inhalation may be harmful. Prolonged exposure may cause chronic effects.	

12. Ecological information

Ecotoxicity The product is not classified as environmentally hazardous. However, this does not exclude the possibility that large or frequent spills can have a harmful or damaging effect on the environment.

Components	Species	Test Results
2-(2-butoxyéthoxy) Éthanol (CAS 112-34-5)		
Aquatic		
Fish	LC50	Bluegill (<i>Lepomis macrochirus</i>) 1300 mg/l, 96 hours
Distillates (petroleum), Hydrotreated Light (CAS 64742-47-8)		
Aquatic		
Crustacea	EC50	Water flea (<i>Daphnia pulex</i>) 2.7 - 5.1 mg/l, 48 hours
Fish	LC50	Rainbow trout, donaldson trout (Oncorhynchus mykiss) 2.9 mg/l, 96 hours
Zinc Oxide (CAS 1314-13-2)		
Aquatic		
Fish	LC50	Fathead minnow (<i>Pimephales promelas</i>) 2246 mg/l, 96 hours

Persistence and degradability No data is available on the degradability of any ingredients in the mixture.

Bioaccumulative potential

Partition coefficient n-octanol / water (log Kow)

2-(2-butoxyéthoxy) Éthanol 0.56

Mobility in soil No data available.

Other adverse effects No other adverse environmental effects (e.g. ozone depletion, photochemical ozone creation potential, endocrine disruption, global warming potential) are expected from this component.

13. Disposal considerations

Disposal instructions	Collect and reclaim or dispose in sealed containers at licensed waste disposal site. Contents under pressure. Do not puncture, incinerate or crush. Incinerate the material under controlled conditions in an approved incinerator. If discarded, this product is considered a RCRA ignitable waste, D001. Dispose of contents/container in accordance with local/regional/national/international regulations.
Local disposal regulations	Dispose in accordance with all applicable regulations.
Hazardous waste code	D001: Waste Flammable material with a flash point <140 F The waste code should be assigned in discussion between the user, the producer and the waste disposal company.
Waste from residues / unused products	Dispose of in accordance with local regulations. Empty containers or liners may retain some product residues. This material and its container must be disposed of in a safe manner (see: Disposal instructions).
Contaminated packaging	Since emptied containers may retain product residue, follow label warnings even after container is emptied. Empty containers should be taken to an approved waste handling site for recycling or disposal. Do not re-use empty containers.

14. Transport information

DOT

UN number	Not available.
UN proper shipping name	Consumer Commodity
Transport hazard class(es)	
Class	ORM-D
Subsidiary risk	-
Packing group	Not available.
Environmental hazards	
Marine pollutant	No
Special precautions for user	Read safety instructions, SDS and emergency procedures before handling.
Packaging exceptions	306
Packaging non bulk	302, 304
Packaging bulk	302, 314, 315

IATA

UN number	UN1950
UN proper shipping name	Aerosols, non-flammable

Transport hazard class(es)**Class** 2.2**Subsidiary risk** -**Packing group** Not available.**Environmental hazards** No**Special precautions for user** Read safety instructions, SDS and emergency procedures before handling.**IMDG****UN number** UN1950**UN proper shipping name** Aerosols**Transport hazard class(es)****Class** 2.2**Subsidiary risk** -**Packing group** Not available.**Environmental hazards****Marine pollutant** No**EmS** F-D, S-U**Special precautions for user** Read safety instructions, SDS and emergency procedures before handling.**Transport in bulk according to** Not applicable.**Annex II of MARPOL 73/78 and****the IBC Code****IATA; IMDG****15. Regulatory information****US federal regulations** This product is a "Hazardous Chemical" as defined by the OSHA Hazard Communication Standard, 29 CFR 1910.1200.**TSCA Section 12(b) Export Notification (40 CFR 707, Subpt. D)**

Not regulated.

CERCLA Hazardous Substance List (40 CFR 302.4)

2-(2-butoxyéthoxy) Éthanol (CAS 112-34-5) Listed.

Zinc Oxide (CAS 1314-13-2) Listed.

SARA 304 Emergency release notification

Not regulated.

OSHA Specifically Regulated Substances (29 CFR 1910.1001-1052)

Not regulated.

Superfund Amendments and Reauthorization Act of 1986 (SARA)**SARA 302 Extremely hazardous substance**

Not listed.

SARA 311/312 Hazardous chemical No (Exempt)**SARA 313 (TRI reporting)**

Chemical name	CAS number	% by wt.
2-(2-butoxyéthoxy) Éthanol	112-34-5	20 - < 30

Other federal regulations**Clean Air Act (CAA) Section 112 Hazardous Air Pollutants (HAPs) List**

2-(2-butoxyéthoxy) Éthanol (CAS 112-34-5)

Clean Air Act (CAA) Section 112(r) Accidental Release Prevention (40 CFR 68.130)

Not regulated.

US state regulations

California Proposition 65



WARNING: This product can expose you to Titanium Dioxide, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov.

California Proposition 65 - CRT: Listed date/Carcinogenic substance

Titanium Dioxide (CAS 13463-67-7)

Listed: September 2, 2011

US. California. Candidate Chemicals List. Safer Consumer Products Regulations (Cal. Code Regs, tit. 22, 69502.3, subd. (a))

2-(2-butoxyéthoxy) Éthanol (CAS 112-34-5)

Distillates (petroleum), Hydrotreated Heavy Naphthenic (CAS 64742-52-5)

International Inventories

Country(s) or region	Inventory name	On inventory (yes/no)*
Australia	Australian Inventory of Chemical Substances (AICS)	Yes
Canada	Domestic Substances List (DSL)	Yes
Canada	Non-Domestic Substances List (NDSL)	No
China	Inventory of Existing Chemical Substances in China (IECSC)	Yes
Europe	European Inventory of Existing Commercial Chemical Substances (EINECS)	No
Europe	European List of Notified Chemical Substances (ELINCS)	No
Japan	Inventory of Existing and New Chemical Substances (ENCS)	No
Korea	Existing Chemicals List (ECL)	Yes
New Zealand	New Zealand Inventory	Yes
Philippines	Philippine Inventory of Chemicals and Chemical Substances (PICCS)	Yes
Taiwan	Taiwan Chemical Substance Inventory (TCSI)	No
United States & Puerto Rico	Toxic Substances Control Act (TSCA) Inventory	Yes

*A "Yes" indicates that all components of this product comply with the inventory requirements administered by the governing country(s)

A "No" indicates that one or more components of the product are not listed or exempt from listing on the inventory administered by the governing country(s).

16. Other information, including date of preparation or last revision

Issue date	04-29-2015
Revision date	02-12-2019
Version #	06
HMIS® ratings	Health: 3* Flammability: 1 Physical hazard: 0
NFPA ratings	Health: 2 Flammability: 1 Instability: 0
NFPA ratings	



Disclaimer

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text.

Revision information

This document has undergone significant changes and should be reviewed in its entirety.