

DIGITAL TORQUE WRENCH

PCE-TWT 10N



Specification

Torque

Measuring range up to 0,001 ... 10 Nm

Resolution 0,001 Nm

Accuracy clockwise: $\pm 2\%$ FS, counterclockwise: $\pm 2.5\%$ FS

Torque

Measuring range up to 0,001 ... 7,38 lbf ft

Resolution 0,001 lbf ft

Accuracy clockwise: $\pm 2\%$ FS, counterclockwise: $\pm 2.5\%$ FS

Torque

Measuring range up to 0,01 ... 88,5 lbf in

Resolution 0,01 lbf in

Accuracy clockwise: $\pm 2\%$ FS, counterclockwise: $\pm 2.5\%$ FS

Torque

Measuring range up to 0,01 ... 102 kgfcm

Resolution 0,01 kgfcm

Accuracy clockwise: $\pm 2\%$ FS, counterclockwise: $\pm 2.5\%$ FS

General technical data

Measuring functions peak, Real-time value, Default value

Units Nm, kgfcm, lbfft, lbf in

Connections 1/4 inch

Storage medium Internal memory

Storage capacity 999 Values

Automatic power-off 3 min.

Alarm Acoustic, optical

Alarm settings 0.3 ... 10 Nm

Protection class (device) IP52

Power supply 2x AAA batteries

Battery/battery 2 x 1,5 V AAA Battery (1,5V) , Alkali-Manganese

Battery capacity 1200 mAh

Operating conditions -10 ... 60 °C , 10 ... 90 %RH

Storage conditions -20 ... 70 °C , 10 ... 90 %RH

Dimensions (L x W x H) 235 x 48 x 38 mm

Weight 385 g