

TOP FEATURES

5^{YR}
WARRANTY

5
CCT

30K
35K
40K
50K
65K

(WATT)
SELECTION

50W
40W
30W

SELECT
5500/4500/3500
LUMENS

DIMMABLE
0-10V

LED
BACKLIT
TECHNOLOGY

DAMP
RATED

120-277
VOLT

115°
BEAM
ANGLE

HIGH
BRIGHTNESS

50K
HOURS

CERTIFICATIONS



SPECIFICATIONS

2X4 FOOT LED

50 / 40 / 30 WATT SELECTABLE | WHITE | DROP-IN BACK-LIT PANEL

NW-SM-2X4-30.40.50W-5CCT

Effortless Installation - High quality internal driver, lightweight led flat panel light can be quickly & easily installed as a surface mount, flush mount and suspended mount without a mounting kit. Distinct hook design makes installation easy and secures when attaching to suspended grid ceilings and troffer fixtures.

TECHNICAL SPECS

VOLTAGE	AC 120-277V
WATTAGE	50W 40W 30W
POWER FACTOR	>0.9
LUMENS	5500 4500 3500
CRI	80
EQUIVALENCY	(4) 32W T8
DIMMABLE	0-10V
BEAM ANGLE	115°
EFFICACY (LM/W)	N/A
COLOR TEMPERATURE	5CCT COLOR FIELD SELECTABLE 3000K 3500K 4000K 5000K 6500K
OPERATING TEMPERATURE	-20~40°C
IP RATING	IP44
MOISTURE RATING	DAMP LOCATION

LIFETIME PERFORMANCE

WARRANTY	5 YEAR WARRANTY
LIFETIME HOURS	50,000 HOURS

CONSTRUCTION

HOUSING MATERIAL	SPCC IRON BACK COVER + PS DIFFUSER
TRIM MATERIAL	DIE-CAST ALUMINUM
PRODUCT WEIGHT	3.7 KG
PRODUCT DIMENSIONS	47.8 IN. X 23.7 IN. X 1.3 IN
LENS DIMENSIONS	45.7 IN. X 21.7 IN. X .04 IN
LENS MATERIAL	PS



SELECTABLE
WATTAGE & LUMENS

TECHNICAL

2X4 FOOT LED | 50 40 30 W SELECTABLE | WHITE | DROP-IN BACK-LIT PANEL

NW-SM-2X4-30.40.50W-5CCT

EDGE

1.33 IN
33 MM



23.7 IN • 603 MM

EXTERIOR DIMENSIONS

45.7 IN
1161 MM





47.8 IN
1214 MM

LENS DIMENSIONS

21.7 IN • 552 MM

110°

AVERAGE
BEAM ANGLE




LUMINOUS INTENSITY DISTRIBUTION DIAGRAM

5500 LUMENS AT 50W

IN STORE DISPLAY



MULTI-PACK BOX



PALLET