

Garant
Circular mill, Steel, Type: 18

Order data

Order number	217250 18
GTIN	4045197571908
Item class	21Q

Description
Note:

The actual groove depth $S_{\max}$ is calculated as follows: $(D-d_1) / 2$.

Technical description

Overhang L_1	25 mm
maximum cutting depth $S_{\max}$	6.5 mm
Shank $\varnothing D_s$ h6	12 mm
Internal $\varnothing d_1$	9 mm
Set of insert screws	219818 (8IP; 1.2 Nm)
Shank type	Weldon
smallest hole $\varnothing D$	14 - 22 mm
Overall length L_{tot}	71.5 mm
for insert type	P16
Through-coolant	yes
Thread depth	20.9 mm
Material of milling tool	Steel
Tool exchange	PowerCard
Type of product	Circular mills

Accessories

Set of insert screws10-piece	219818
------------------------------	--------