



SAFETY DATA SHEET

1. Identification

Important information	*** This Safety Data Sheet is only authorised for use by HP for HP Original products. Any unauthorised use of this Safety Data Sheet is strictly prohibited and may result in legal action being taken by HP. ***
Product identifier	W1760A
Other means of identification	None.
Recommended use	This product is a toner mixture that is used in printing systems.
Recommended restrictions	None known.
Manufacturer/Importer/Supplier/Distributor information	HP Inc. 1501 Page Mill Road Palo Alto, CA 94304-1112 United States
Telephone	650-857-1501
HP Inc. health effects line (Toll-free within the US)	1-800-457-4209
(Direct)	1-760-710-0048
HP Inc. Customer Care Line	
(Toll-free within the US)	1-800-474-6836
(Direct)	1-208-323-2551
Email:	sustainability@hp.com

2. Hazard(s) identification

Physical hazards	Not classified.
Health hazards	Not classified.
Environmental hazards	Not classified.
OSHA defined hazards	Not classified.
Label elements	
Hazard symbol	None.
Signal word	None.
Hazard statement	Not available.
Precautionary statement	
Prevention	Not available.
Response	Not available.
Storage	Not available.
Disposal	Not available.
Hazard(s) not otherwise classified (HNOC)	Carbon black is classified by the IARC as a Group 2B carcinogen (the substance is possibly carcinogenic to humans). Carbon black in this preparation, due to its bound form, does not present this carcinogenic risk. None of the other ingredients in this preparation are classified as carcinogens according to ACGIH, EU, IARC, MAK, NTP or OSHA.
Supplemental information	This product is not classified as hazardous according to OSHA CFR 1910.1200 (HazCom 2012).

3. Composition/information on ingredients

Mixtures

Chemical name	Common name and synonyms	CAS number	%
Polyester resin	Polyester resin	Proprietary	<80

Material name: W1760A

15528 Version #: 05 Revision date: 17-Mar-2025 Issue date: 02-Aug-2021

SDS US

1 / 8

Chemical name	Common name and synonyms	CAS number	%
Black Pigment		Proprietary	<15
Paraffin Wax		Proprietary	<15
Silica		Proprietary	<5

4. First-aid measures

Inhalation	Move person to fresh air immediately. If irritation persists, consult a physician.
Skin contact	Wash affected areas thoroughly with mild soap and water. Get medical attention if irritation develops or persists.
Eye contact	Do not rub eyes. Immediately flush with large amounts of clean, warm water (low pressure) for at least 15 minutes or until particles are removed. If irritation persists, consult a physician.
Ingestion	Rinse mouth with water. Drink one to two glasses of water. DO NOT induce vomiting. Get medical attention immediately.
Most important symptoms/effects, acute and delayed	Difficulty in breathing. Coughing.

5. Fire-fighting measures

Suitable extinguishing media	Water spray, dry chemical, carbon dioxide.
Unsuitable extinguishing media	None known.
Specific hazards arising from the chemical	Like most organic material in powder form, toner can form explosive dust-air mixtures when finely dispersed in air.
Special protective equipment and precautions for firefighters	Wear self-contained breathing apparatus and protective clothing. Wear full set of protective equipment including chemical goggles and gloves.
Fire fighting equipment/instructions	If fire occurs in the printer, treat as an electrical fire.
Specific methods	None established.

6. Accidental release measures

Personal precautions, protective equipment and emergency procedures	Avoid inhalation of dust. Wash thoroughly after dealing with a spillage. See Section 8 of the SDS for Personal Protective Equipment. Ensure adequate ventilation. Remove victim immediately from source of exposure. Emergency personnel should wear self-contained breathing apparatus.
Methods and materials for containment and cleaning up	Slowly vacuum or sweep the material into a bag or other sealed container. Clean remainder with a damp cloth or vacuum cleaner. If a vacuum is used, the motor must be rated as dust explosion-proof. Fine powder can form explosive dust-air mixtures. Dispose of in compliance with federal, state, and local regulations.
Environmental precautions	Avoid spreading dust or contaminated materials. Avoid discharge into drains, water courses or onto the ground.

7. Handling and storage

Precautions for safe handling	Use local exhaust ventilation. Take precautionary measures against static discharges. Use only in well-ventilated areas. Ground and bond containers when transferring material. Avoid inhalation of dust and contact with skin and eyes. Keep away from excessive heat, sparks, and open flames.
Conditions for safe storage, including any incompatibilities	Keep out of the reach of children. Wash hands after handling. When using, do not eat, drink or smoke. Remove contaminated clothing and wash the skin thoroughly with soap and water after work. Keep tightly closed and dry. Store at room temperature.

8. Exposure controls/personal protection

Occupational exposure limits

US. OSHA Table Z-1 Limits for Air Contaminants (29 CFR 1910.1000)

Components	Type	Value
Black Pigment	PEL	3.5 mg/m ³

US. OSHA Table Z-3 (29 CFR 1910.1000)

Components	Type	Value	Form
Black Pigment	TWA	5 mg/m ³	Respirable fraction.
		15 mg/m ³	Total dust.
		50 mppcf	Total dust.

US. OSHA Table Z-3 (29 CFR 1910.1000)

Components	Type	Value	Form
		15 mppcf	Respirable fraction.

US. ACGIH Threshold Limit Values

Components	Type	Value	Form
Black Pigment	TWA	3 mg/m ³	Inhalable fraction.
Paraffin Wax	TWA	2 mg/m ³	Fume.

US. NIOSH. Immediately Dangerous to Life or Health (IDLH) Values, as amended

Components	Type	Value
Black Pigment	IDLH	1750 mg/m ³

US. NIOSH: Pocket Guide to Chemical Hazards

Components	Type	Value	Form
Black Pigment	TWA	0.1 mg/m ³	
Paraffin Wax	TWA	2 mg/m ³	Fume.

Biological limit values	No biological exposure limits noted for the ingredient(s).
Exposure guidelines	USA OSHA (TWA/PEL): 15 mg/m ³ (Total Dust) 5 mg/m ³ (Respirable Fraction) ACGIH (TWA/TLV): 10 mg/m ³ (Inhalable Particulate) 3 mg/m ³ (Respirable Particulate)
Appropriate engineering controls	Use in a well ventilated area.
Individual protection measures, such as personal protective equipment	
Eye/face protection	Wear safety glasses with side shields (or goggles).
Skin protection	
Hand protection	Rubber gloves are recommended. Wash hands after handling.
Other	Protection suit must be worn.
Respiratory protection	No personal respiratory protective equipment required under normal conditions of use.
Thermal hazards	Not available.
General hygiene considerations	Keep away from food, drink and animal feeding stuffs. Wash hands before breaks and immediately after handling the product.

9. Physical and chemical properties

Appearance	Fine powder
Physical state	Solid.
Form	solid
Color	Black.
Odor	Odorless
Odor threshold	No information available
pH	Not applicable
Melting point/freezing point	No information available
Initial boiling point and boiling range	Not applicable
Flash point	Not applicable
Evaporation rate	Not available.
Flammability (solid, gas)	Not available.
Upper/lower flammability or explosive limits	
Explosive limit - lower (%)	Not flammable
Explosive limit - upper (%)	Not available.
Vapor density	Not applicable

Vapor density	Not applicable
Solubility(ies)	
Solubility (water)	Insoluble in water. Partially soluble in toluene, chloroform and tetrahydrofuran
Partition coefficient (n-octanol/water)	Not available.
Auto-ignition temperature	No data available
Decomposition temperature	>392 °F (>200 °C)
Viscosity	Not applicable
Other information	Not available.
Oxidizing properties	No information available.
Specific gravity	1.2 g/ml

10. Stability and reactivity

Reactivity	Not available.
Chemical stability	Stable under normal storage conditions.
Possibility of hazardous reactions	Not available.
Conditions to avoid	Heat, sparks, flames. Sunlight. Avoid dust close to ignition sources.
Incompatible materials	This product may react with strong oxidizing agents. This product may react with strong acids.
Hazardous decomposition products	Carbon monoxide and carbon dioxide. Hydrogen.

11. Toxicological information

Information on likely routes of exposure

Inhalation	Under normal conditions of intended use, this material is not expected to be an inhalation hazard.
Skin contact	Contact with skin may result in mild irritation.
Eye contact	Contact with eyes may result in mild irritation.
Ingestion	Ingestion is not a likely route of exposure.

Symptoms related to the physical, chemical and toxicological characteristics Not available.

Information on toxicological effects

Acute toxicity Based on available data, the classification criteria are not met. LD50/oral/rat >5000 mg/kg

Components	Species	Test Results
Black Pigment		
<u>Acute</u>		
Oral		
LD50	Rat	> 10000 mg/kg

Skin corrosion/irritation Based on available data, the classification criteria are not met. Not a known irritant. (OECD 404)

Serious eye damage/eye irritation Based on available data, the classification criteria are not met. Not a known irritant. (OECD 405)

Respiratory or skin sensitization

Respiratory sensitization Based on available data, the classification criteria are not met.

Skin sensitization Based on available data, the classification criteria are not met.

Germ cell mutagenicity Negative, does not indicate mutagenic potential (Ames Test: Salmonella typhimurium)
Based on available data, the classification criteria are not met.

Carcinogenicity Based on available data, the classification criteria are not met.

Carbon black is classified as a carcinogen by the IARC (possibly carcinogenic to humans, Group 2B) and by the State of California under Proposition 65. In their evaluations of carbon black, both organizations indicate that exposure to carbon black, per se, does not occur when it remains bound within a product matrix, specifically, rubber, ink, or paint. Carbon black is present only in a bound form in this preparation.

IARC Monographs. Overall Evaluation of Carcinogenicity

Black Pigment (CAS Proprietary)

2B Possibly carcinogenic to humans.

OSHA Specifically Regulated Substances (29 CFR 1910.1001-1053)

Not listed.

US. National Toxicology Program (NTP) Report on Carcinogens

Black Pigment (CAS Proprietary)

Known To Be Human Carcinogen.

Reproductive toxicity	Based on available data, the classification criteria are not met.
Specific target organ toxicity - single exposure	Based on available data, the classification criteria are not met.
Specific target organ toxicity - repeated exposure	Based on available data, the classification criteria are not met.
Aspiration hazard	Based on available data, the classification criteria are not met.
Further information	Complete toxicity data are not available for this specific formulation Refer to Section 2 for potential health effects and Section 4 for first aid measures.

In a study in rats (H.Muhle) by chronic inhalation exposure to a typical toner, a mild to moderate degree of lung fibrosis was observed in 92% of the rats in the concentration(16mg/m3) exposure group, and a minimal to mild degree of fibrosis was noted in 22% of the animals in the middle (4mg/m3) exposure group. But no pulmonary changes was reported in the lowest (1mg/m3) exposure group, the most relevant level to potential human exposures.

12. Ecological information

Ecotoxicity	Not available.
Persistence and degradability	Not available.
Bioaccumulative potential	Not available.
Mobility in soil	Not available.
Other adverse effects	Not available.

13. Disposal considerations

Disposal instructions	Dispose of in compliance with federal, state, and local regulations. Do not shred toner cartridge, unless dust-explosion prevention measures are taken. Do not put toner container into fire; heated toner may cause severe burns. Do not incinerate. Do not allow this material to drain into sewers/water supplies. HP's Planet Partners (trademark) supplies recycling program enables simple, convenient recycling of HP original inkjet and LaserJet supplies. For more information and to determine if this service is available in your location, please visit http://www.hp.com/recycle .
------------------------------	--

14. Transport information

DOT

UN number	Not available.
UN proper shipping name	Not Regulated
Transport hazard class(es)	
Class	Not available.
Subsidiary risk	-
Packing group	Not available.
Environmental hazards	
Marine pollutant	No
Special precautions for user	Not available.

IATA

UN number	Not available.
UN proper shipping name	Not Regulated
Transport hazard class(es)	
Class	Not available.
Subsidiary risk	-
Packing group	Not available.
Environmental hazards	No
Special precautions for user	Not available.

IMDG

UN number	Not available.
------------------	----------------

UN proper shipping name Not Regulated
Transport hazard class(es)
Class Not available.
Subsidiary risk -
Packing group Not available.
Transport hazard class(es)
Marine pollutant No
EmS Not available.
Special precautions for user Not available.

ADR

UN number Not available.
UN proper shipping name Not Regulated
Transport hazard class(es)
Class Not available.
Subsidiary risk -
Hazard No. (ADR) Not available.
Tunnel restriction code Not available.
Packing group Not available.
Environmental hazards No
Special precautions for user Not available.

Further information Not a dangerous good under DOT, IATA, ADR, IMDG, or RID.

15. Regulatory information

US federal regulations US EPA TSCA Inventory: All chemical substances in this product comply with all rules or orders under TSCA.

Toxic Substances Control Act (TSCA)

TSCA Section 12(b) Export Notification (40 CFR 707, Subpt. D)

Not regulated.

CERCLA Hazardous Substance List (40 CFR 302.4)

Not listed.

SARA 304 Emergency release notification

Not regulated.

OSHA Specifically Regulated Substances (29 CFR 1910.1001-1053)

Not listed.

Superfund Amendments and Reauthorization Act of 1986 (SARA)

SARA 302 Extremely hazardous substance

Not listed.

SARA 311/312 Hazardous chemical No

Other federal regulations

Clean Air Act (CAA) Section 112 Hazardous Air Pollutants (HAPs) List

No intentionally added HAP substances.

Clean Air Act (CAA) Section 112(r) Accidental Release Prevention (40 CFR 68.130)

Not regulated.

Safe Drinking Water Act (SDWA) Not regulated.

US state regulations

California Proposition 65

California Proposition 65 - CRT: Listed date/Carcinogenic substance

Black Pigment (CAS Proprietary)

Listed: February 21, 2003

Clean Air Act (CAA) No intentionally added HAP substances.

16. Other information, including date of preparation or last revision

Issue date 02-Aug-2021

Revision date 17-Mar-2025

Version #

05

Other information

This SDS was prepared in accordance with USA OSHA Hazard Communications regulation (29 CFR 1910.1200).

Disclaimer

This [Material] Safety Data Sheet is provided without charge to customers of Hewlett-Packard Company. Data is the most current known to Hewlett-Packard Company at the time of preparation of this (M)SDS and is believed to be accurate. It should not be construed as guaranteeing specific properties of the products as described or suitability for a particular application. This Safety Data Sheet document is provided without charge to customers of HP. Data is the most current known to HP at the time of preparation of this document and is believed to be accurate. It should not be construed as guaranteeing specific properties of the products as described or suitability for a particular application. This document was prepared to the requirements of the jurisdiction specified in Section 1 above and may not meet regulatory requirements in other countries.

This safety data sheet is meant to convey information about HP inks (toners) provided in HP Original ink (toner) supplies. If our Safety Data Sheet has been provided to you with a refilled, remanufactured, compatible or other non-HP Original supply please be aware that the information contained herein was not meant to convey information about such products and there could be considerable differences from information in this document and the safety information for the product you purchased. Please contact the seller of the refilled, remanufactured or compatible supplies for applicable information, including information on personal protective equipment, exposure risks and safe handling guidance. HP does not accept refilled, remanufactured or compatible supplies in our recycling programs.

Revision information

1. Product and Company Identification: Alternate Trade Names

Explanation of abbreviations

ACGIH	American Conference of Governmental Industrial Hygienists
Acute Tox.	Acute toxicity
Aquatic Acute	Short-term (acute) aquatic hazard
Aquatic Chronic	Long-term (chronic) aquatic hazard
Asp. Tox.	Aspiration hazard
Carc.	Carcinogenicity
CAS	Chemical Abstracts Service
CERCLA	Comprehensive Environmental Response Compensation and Liability Act
CFR	Code of Federal Regulations
COC	Cleveland Open Cup
DOT	Department of Transportation
EPCRA	Emergency Planning and Community Right-to-Know Act (aka SARA)
Eye Dam.	Serious eye damage
Eye Irrit.	Eye Irritation
Flam. Liq.	Flammable liquids
Flam. Sol.	Flammable solids
Lact.	Effects on or via lactation
Muta.	Germ cell mutagenicity
IARC	International Agency for Research on Cancer
NIOSH	National Institute for Occupational Safety and Health
NTP	National Toxicology Program
OSHA	Occupational Safety and Health Administration
Ox. Liq.	Oxidising liquids
Ozone	Hazardous to the ozone layer
PEL	Permissible Exposure Limit
Press. Gas	Gases under pressure
RCRA	Resource Conservation and Recovery Act
REC	Recommended
REL	Recommended Exposure Limit
Repr.	Reproductive toxicity
Resp. Sens.	Respiratory sensitization
SARA	Superfund Amendments and Reauthorization Act of 1986
Skin Corr.	Skin corrosion
Skin Irrit.	Skin irritation
Skin Sens.	Skin sensitization
STEL	Short-Term Exposure Limit
STOT RE	Specific target organ toxicity - repeated exposure
STOT SE	Specific target organ toxicity - single exposure
TCLP	Toxicity Characteristics Leaching Procedure
TLV	Threshold Limit Value
TSCA	Toxic Substances Control Act