

6 OUTLET SURGE PROTECTOR POWER STRIP WITH 6 FT EXTENSION CORD



ELECTRICAL AND STRUCTURAL CHARACTERISTICS.

Cord / Cable:
 - Type: *SJT 14AWGX3C (14 AWG=2,08 mm² 3 conductors), 300V, min.60°C.*
 - Length: 6 ft. (1.83 m)
Ways: 6 x *NEMA 5-15R (2 P + Ground Polarized)*
On/Off Switch
Plug: *NEMA 5-15P (2 P + Ground Polarized).*
Current: 15 A
Voltage: 125V AC
Frequency : 60 Hz
Maximum Power : 1875W
Surge Protection : 250 Joules
Fast fixing wall: 1 keyhole on the back

MATERIALS

Aluminum Alloy
Plastic Parts: *Polypropylene*
Contacts: Copper
Cord Insulation jacket: *Thermoplastic (PVC)*

APPLIED STANDARD

UL Std.1363 and 1449
CSA STD.C22.2 No.308 and 269.3

DIMENSIONS

1.57" x 2.09" x 16.14" (4 x 5.31 x 41 cm)

DIELECTRIC STRENGTH / RIGIDEZ DIELECTRICA

125V AC

