BEST SANITIZERS INC.™

Complete, Confident, Compliant.

TECH SHEET

BSI-500

High-Foaming Heavy-Duty Caustic Cleaner

A high-foaming, heavy-duty caustic cleaner and degreaser. Contains a powerful mixture of surfactants and chelating agents for use in difficult cleaning applications. BSI-500 is a strong alkaline cleaner, designed for stainless steel or black iron surfaces. Product may be used cold, but best results are usually obtained at temperatures between 100 - 120 degrees. May be used in all departments of meat, poultry and general food processing plants.

Recommended for use: to clean ovens, utensils, equipment, walls, and floors

DILUTION RATIO: 2 to 12 ounces per gallon of hot water (adjust as needed)

REORDER: BSI5001, BSI5002, BSI5003, BSI5004

CONFIGURATIONS:

- 4 x 1 Gallon Bottles
- 5 Gallon Pail
- 55 Gallon Drum
- 275 Gallon Tote

COMPATIBLE EQUIPMENT:

MD20001, MD20001-75, MD20003, MD20006, MD20008, MD20009, MD20010-15, USP20068, USP20084-89, SS20003, MD20016, MD20018, USP20218, USP20220, USP20221, USP20109, USP20082, USP20083

CHEMTREC EMERGENCY PHONE:

1-800-424-9300

Read SDS before using this product.



Food Safety is Our Priority

www.bestsanitizers.com | 888.225.3267