

Cut resistant level C, nitrile-dipped and touchscreen functionality.

TEGERA® 804

Learn more

ATEX GLOVE FOR USE IN EXPLOSIVE AREAS

An ATEX glove for use in ATEX-protected work environments. Cut resistant level C using TEGERA® CRF-Technology and ESD-approved. The glove has touchscreen functionality, ensuring seamless transition between duties without having to remove the glove. Made of thin 18 gg fibre for dexterity and 3/4 nitrile-dipped for extra grip and protection in oily and wet environments.

CHARACTERISTICS

- Flexible
- Durable
- Good grip
- Comfortable

FUNCTIONS

- Withstands contact heat up to 100°C
- For touchscreen
- Latex-free
- Oil and grease resistant
- ESD
- Antistatic/ATEX
- Conforms with IEC 61340-5-1 (ESD)
- Thin

CRF®

ORIGINAL EXCELLENT dermatest 2019 dermatest-guarantee.de

OEKO TEX® STANDARD 100 SE 14-214 RISE

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.

PREVENTS RISK OF

Cut injuries, Scratches, lacerations, Contact with dirt, Contact with oil and fat, Antistatic

PRIMARY ENVIRONMENTS OF USE

Cut risk environments, Oily and greasy environments, Dirty environments, Harsh environments, Environments with explosive risks

PRIMARY AREAS OF USE

Assembly, Construction, Electronics work, Engineering, Installation work

PRIMARY INDUSTRIES OF USE

Automotive manufacturing, Automotive repair and maintenance, Basic metals manufacturing, Electrical equipment manufacturing, Machinery and equipment manufacturing, Metal manufacturing and fabrication, Mining and quarrying, Oil and gas extraction, Transport equipment manufacturing

TYPE OF WORK

Medium weight

SPECIFICATION

TYPE Cut resistant gloves, Heat protection gloves, ESD gloves
CATEGORY Cat. II
KNITTING GAUGE (GG) 18
LINING MATERIAL Carbon, CRF® Technology, Glass fibre thread, HPPE, Polyester, Spandex
LENGTH 220-270 mm
DEXTERITY 5
GRIP DESIGN Sandy finish
COLOUR Black
PAIRS PER: BUNDLE/CARTON 6/120
DISPLAY TYPE Bulk pack
DIPPING 3/4 dipped
DIPPING MATERIAL Nitrile
CUFF STYLE Knitwrist cuff
CUFF MATERIAL Textile
CUT RESISTANCE (EN ISO 13997) Cut resistance level C
CUT RESISTANCE (EN ISO 13997) TDM: 13.2 N
INNER MATERIAL SPECIFICATION HPPE (High performance polyethylene), Polyester, Glass fibre thread, Elastane, Carbon thread
OUTER MATERIAL SPECIFICATION Nitrile

COMPLIANCE

CE Cat. II

EAC TP TC 019:2011

EN ISO 21420:2020

EN 388:2016+A1:2018 3X41C

EN 407:2020 (No flame protection) X1XXXX

IEC 61340-5-1:2016 R < 1.0 x 10⁹ Ω

EN 16350:2014 R < 1,0 x 10⁸ Ω

ANSI A3 CUT

ANSI 4 ABR

ANSI 3 PUN

Contact heat rating valid for palm area only

FEATURES

Cut protection

For touchscreen

SIZE		ARTICLE NUMBER	EAN
6	XS	804-6	7340118395807
7	S	804-7	7340118395890
8	M	804-8	7340118395982
9	L	804-9	7340118396071
10	XL	804-10	7340118396163
11	XXL	804-11	7340118396255

ejendals
Limavägen 28, SE-793 32 Leksand, Sweden
Phone +46 (0) 247 360 00 | info@ejendals.com | order@ejendals.com

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.