





## TEGERA® INFINITY 8805

Learn more

## SUPER SOFT, PALM DIPPED, CUT B GLOVE

Dexterous cut resistant glove, level B, with touchscreen function. Ultra-light thanks to 18 gg knitted with CRF® cut resistant technology. Palm dipped with super soft nitrile foam that provides excellent grip on dry surfaces. Reinforced thumb crotch for improved longevity. Suitable for precision work. Breathable materials for all day comfort. Protection against contact heat up to 100°C/212°F. Wide range of sizes means a perfectly fitting glove for everyone. Skin friendly with Derma-test and Oeko-Tex certificate.

### CHARACTERISTICS

- Good fingertip sensitivity
- Flexible
- Durable
- Good grip
- Extra comfortable

### FUNCTIONS

- Withstands contact heat up to 100°C
- Approved for handling foodstuffs
- For touchscreen
- Reinforcement between index finger and thumb
- Thin

CRF®

ORIGINAL EXCELLENT dermatest 2019 dermatest-guarantee.de

OEKO TEX® STANDARD 100 SE 14-214 RISE



*All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.*

## PREVENTS RISK OF

Cut injuries, Abrasion injuries, Blisters, Grazes, Scratches, lacerations, Contact with dirt, Drying out, Chapping

## PRIMARY ENVIRONMENTS OF USE

Cut risk environments, Dry environments, Moist environments, Dirty environments

## PRIMARY AREAS OF USE

Fine assembly, Assembly, Machine operating, Building and construction, Carpentry, Painting, Installation work, HVAC installation, Sheet-metal work, Engineering, Transport work, Machine driving, Warehouse work, Airport work, Metalwork, Glass industry work, Repair work, Paper industry work, Service work, Shop work

## PRIMARY INDUSTRIES OF USE

Agriculture, forestry and fishing, Automotive manufacturing, Automotive repair and maintenance, Basic metals manufacturing, Building and construction, Electrical equipment manufacturing, Electricity and gas supply, Facility management services, Glass, ceramics and construction materials, Machinery and equipment manufacturing, Metal manufacturing and fabrication, Mining and quarrying, Public safety, security and defence, Pulp and paper, Retail and wholesale, Transport equipment manufacturing, Transportation and logistics, Warehousing

## TYPE OF WORK

Light weight

## SPECIFICATION

**TYPE** Cut resistant gloves, Heat protection gloves
**CATEGORY** Cat. II
**COLLECTION** Infinity
**KNITTING GAUGE (GG)** 18
**LINING MATERIAL** Carbon, CRF® Technology, HPPE, Nylon, Stainless steel fibre yarn
**LENGTH** 210-270 mm
**DEXTERITY** 5
**GRIP DESIGN** Foam grip pattern
**COLOUR** Grey
**PAIRS PER: BUNDLE/CARTON** 6/120
**DISPLAY TYPE** Bulk pack
**DIPPING** Palm-dipped
**DIPPING MATERIAL** Nitrile foam, Waterbased PU
**CUFF STYLE** Knitwrist cuff
**CUFF MATERIAL** Textile
**CUT RESISTANCE (EN ISO 13997)** Cut resistance level B
**CUT RESISTANCE (EN ISO 13997) TDM:** 9 N
**INNER MATERIAL SPECIFICATION** Nylon, HPPE (High performance polyethylene), Stainless steel fibre yarn, Carbon thread
**OUTER MATERIAL SPECIFICATION** Nitrile

## COMPLIANCE

CE Cat. II
TP TC 019:2011

UKCA Cat. II
EN ISO 21420:2020

EAC

EN 388:2016+A1:2018 4X42B

EN 407:2020 (No flame protection) X1XXXX

ANSI A2 CUT

ANSI 3 ABR

**Contact heat rating valid for palm area only**

## FEATURES

Cut protection

For touchscreen

| SIZE | | ARTICLE NUMBER | EAN |
|---|---|---|---|
| 5 | XXS | 8805-5 | 7340118328089 |
| 6 | XS | 8805-6 | 7340118319322 |
| 7 | S | 8805-7 | 7340118319339 |
| 8 | M | 8805-8 | 7340118319346 |
| 9 | L | 8805-9 | 7340118319353 |
| 10 | XL | 8805-10 | 7340118319308 |
| 11 | XXL | 8805-11 | 7340118319315 |

ejendals
Limavägen 28, SE-793 32 Leksand, Sweden
Phone +46 (0) 247 360 00 | info@ejendals.com | order@ejendals.com



*All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.*