



TEGERA® 431

Learn more

HIGH DURABILITY WITH GOOD GRIP

A versatile cut protection glove with CRF® technology and high durability as it has a double dipped palm in nitrile. Sandy finish provides good grip in damp and slightly oily environments. Withstands contact heat up to 100 °C/212 °F. Suitable for assembly work and metal work, among other things.

CHARACTERISTICS

- Very durable
- Good grip

FUNCTIONS

- Withstands contact heat up to 100°C
- Oil and grease resistant palm

CRF®

OEKO TEX® STANDARD 100 SE 14-214 RISE

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.

PREVENTS RISK OF

Cut injuries, Scratches, lacerations, Contact with dirt, Contact with oil and fat

PRIMARY ENVIRONMENTS OF USE

Cut risk environments, Dry environments, Oily and greasy environments, Dirty environments

PRIMARY AREAS OF USE

Assembly, Machine operating, Building and construction, Engineering, Transport work, Metalwork

PRIMARY INDUSTRIES OF USE

Agriculture, forestry and fishing, Automotive manufacturing, Automotive repair and maintenance, Basic metals manufacturing, Building and construction, Electrical equipment manufacturing, Machinery and equipment manufacturing, Metal manufacturing and fabrication, Mining and quarrying, Transport equipment manufacturing

TYPE OF WORK

Medium weight

SPECIFICATION

TYPE Cut resistant gloves, Heat protection gloves
CATEGORY Cat. II
KNITTING GAUGE (GG) 13
LINING MATERIAL CRF® Technology, HPPE, Nylon, Spandex
LENGTH 210-280 mm
DEXTERITY 5
GRIP DESIGN Sandy finish
COLOUR Grey
PAIRS PER: BUNDLE/CARTON 12/60
DISPLAY TYPE Bulk pack
DIPPING Palm-dipped
DIPPING MATERIAL Nitrile, Nitrile foam
CUFF STYLE Knitwrist cuff
CUFF MATERIAL Textile
CUT RESISTANCE (EN ISO 13997) Cut resistance level B
CUT RESISTANCE (EN ISO 13997) TDM: 5.4 N
INNER MATERIAL SPECIFICATION HPPE (High performance polyethylene), Nylon, Elastane
OUTER MATERIAL SPECIFICATION Nitrile

COMPLIANCE

CE Cat. II
TP TC 019:2011

UKCA Cat. II
EN ISO 21420:2020

EAC

EN 388:2016+A1:2018 4X43B

EN 407:2020 (No flame protection) X1XXXX

ANSI A1 CUT

ANSI 3 ABR

Contact heat rating valid for palm area only

FEATURES

Cut protection

SIZE		ARTICLE NUMBER	EAN
5	XXS	431-5	7340118355870
6	XS	431-6	7340118322438
7	S	431-7	7340118322445
8	M	431-8	7340118322452
9	L	431-9	7340118322469
10	XL	431-10	7340118322407
11	XXL	431-11	7340118322414
12	3XL	431-12	7340118322421

ejendals
Limavägen 28, SE-793 32 Leksand, Sweden
Phone +46 (0) 247 360 00 | info@ejendals.com | order@ejendals.com

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.