ABB BALDOR RELIANCE

Customer information packet

VHECP4107T

25HP, 3520RPM, 3PH, 60HZ, 284HP, 0954M, TEFC
Class - None
Division - Not Applicable

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/5/2026 10:17:11 AM

Specifications

Enclosure	TEFC
Frame	284HP
Frame Material	Iron
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	25.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	3600 RPM @ 60 HZ
Voltage @ Frequency	460.0 V @ 60 HZ
	230.0 V @ 60 HZ
Agency Approvals	CSA
	CSA EEV
	UR
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	No Mounting
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	56.000 A @ 230.0 V
	64.000 A @ 208.0 V
	28.000 A @ 460.0 V
Design Code	A
Drip Cover	Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	92.4 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Face Code	Standard
Front Shaft Indicator	None

Part Detail

Revision	AL
Type	AC
Mech. spec.	09G614
Base	
Status	PRD/A
Elec. spec.	09WGY357
Layout	09LYG614
Eff. date	06-16-2026
CD Diagram	CD0180
Poles	02
Leads	9#10
Proprietary	False
Created date	01-01-0001

Heater Indicator	No Heater
High Voltage Full Load Amps	28.0 a
Insulation Class	F
Inverter Code	Inverter Ready
KVA Code	J
Lifting Lugs	Vertical Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Motor Lead Exit	Ko Box
Motor Lead Quantity/Wire Size	9 @ 10 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	0950M
Mounting Arrangement	F1
Number of Poles	2
Overall Length	25.72 IN
Power Factor	91
Product Family	Super-E Chemical Processing
Pulley End Bearing Type	Ball
Pulley Face Code	P-Base
Pulley Shaft Indicator	P-Base Groove & Key
Rodent Screen	None
Service Factor	1.15
Shaft Diameter	1.125 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	Shaft Slinger
Speed	3530 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None

Winding Thermal 2	None

Nameplate

NP1260								
CAT.NO.	VHECP4107T							
SPEC.	09G614Y357							
HP	25							
VOLTS	230/460							
AMP	56/28							
RPM	3530							
FRAME	284HP	**HZ**	60		**PH**	3		
SER.F.	1.15	**CODE**	J	**DES**	A	**CL**	F	
NEMA-NOM-EFF	92.4	**PF**	91					
RATING	40C AMB-CONT							
CC	010A							
DE	6311	**ODE**	6208					
ENCL	TEFC	**SN**						

AC Induction Motor Performance Data
Record # 1971
Typical performance - not guaranteed values

Winding: 09WGY357-R001	**Type:** 0950M	**Enclosure:** TEFC

Nameplate Data				**460 V, 60 Hz: High Voltage Connection**	
Rated Output (HP)			25	**Full Load Torque**	37.2 LB-FT
Volts			230/460	**Start Configuration**	direct on line
Full Load Amps			56/28	**Breakdown Torque**	139 LB-FT
R.P.M.			3530	**Pull-up Torque**	67.2 LB-FT
Hz	60	**Phase**	3	**Locked-rotor Torque**	78.3 LB-FT
NEMA Design Code	A	**KVA Code**	J	**Starting Current**	236 A
Service Factor (S.F.)			1.15	**No-load Current**	7.8 A
NEMA Nom. Eff.	92.4	**Power Factor**	91	**Line-line Res. @ 25ºC**	0.286 Ω
Rating - Duty			40C AMB-CONT	**Temp. Rise @ Rated Load**	64°C
S.F. Amps				**Temp. Rise @ S.F. Load**	78°C
				Locked-rotor Power Factor	27.3
				Rotor inertia	1.28 LB-FT2

Load Characteristics 460 V, 60 Hz, 25 HP

% of Rated Load	**25**	**50**	**75**	**100**	**125**	**150**	**S.F.**
Power Factor	62	82	89	91	92	92	92
Efficiency	89.9	93	93.5	93.2	92.6	91.7	92.8
Speed	3583	3566	3549	3531	3512	3492	3520
Line amperes	10.45	15.33	21.15	27.5	34.3	41.5	31.6


ABB Motors and Mechanical Inc.


WINDING # 09WGY357

25 HP 3 PH 60 HZ 3530 RPM 460 V 0950M


Typical performance - not guaranteed values.


TORQUES(LB-FT): PO=139 PU=67.2 LR=78.3 LRA=236





09LYG614
(920 - 956) = 26.11
10.84
2.746±.031
3.75
NAMEPLATE
2.03
.750
.745
.68
.378
.376
Ø13.25
.25 KEY
1.13 LONG
Ø1.1250
1.1245
Ø9.87
(MAX)
Ø8.253
8.250
Ø.875
.870
.25
SEAL DETAIL
.31-18 TAP
GND LOC.
13.05
9.99
11.19
6.70
2.70
45°
45°
DRAIN
HOLE
LEAD HOLE
2.00 N.P.T.
DRAIN
HOLE
4 HOLES
Ø.44 ON
Ø9.12 B.C.
8.75
HW4600E45
SEAL DETAIL
CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT THE PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION
REV. DESC: LOAD DRAWING TO SOLIDWORKS
REV: F
VERSION: 06
REVISED: 07:56:00 02/12/2020
TDR: 000001132140
MODEL NO. 09LYG614
REF: -
BY: ENALEM0
B
BALDOR - RELIANCE®
VERT TEFC 284-6HP ECP W/6311 BRG
09LYG614

CD0180







NOTES:

1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
2. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
3. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY BE A MULTIPLE OF THOSE SHOWN ABOVE.
4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

CD0180

REV. DESC: ADD CLASS CONN00000007		
REV. LTR: D	VERSION: 01	TDR: 000001099922
FILE: \AAA\00005\148	REVISED: 10:25:29 02/19/2019	BY: ENBRIR0
MTL: –		

BALDOR - RELIANCE®

3PH, DV, 9 LEADS, DELTA CONNECTION

SH 1 of 1