

ULTRASONIC FLOW METER

PCE-TDS 200 SL



- » **Measuring range ± 32 m/s**
- » **USB-C interface for data transfer**
- » **Optional software for analysing the measured values**
- » **Reproducibility ± 0.5 % of measured value**
- » **Heat quantity measurement**
- » **Data memory for 10 million measuring points**
- » **individually adjustable alarm limits**
- » **optionally with ISO or DAkkS calibration certificate**

The ultrasonic flow meter has a measuring range of ± 32 m/s. With an accuracy of ± 1.5 % f.s. for a pipe diameter of DN ≥ 50 , ± 3.5 % f.s. for a pipe diameter of DN < 50 and a reproducibility of ± 0.5 % f.s., the ultrasonic flow meter is a particularly precise measuring device. An installation aid is available for installing the sensors of the ultrasonic flow meter. The installation aid graphically displays the signal quality of the ultrasonic flow meter. In addition, it is graphically displayed whether the sensors of the ultrasonic flow meter are positioned at the correct distance from each other. To carry out flow measurements with the ultrasonic flow meter, the flow velocity, the volume flow and the volume are displayed after entering the pipe and medium specifications. The ultrasonic flow meter displays the measured values in a wide range of units. For example: m^3 , l, gal, igl, mgl, cf, bal, lb and ob.

During a measurement, it is possible to record the measured values via the data logger function of the ultrasonic flow meter. Start and stop conditions and the storage interval can be set from 1 second to 12 hours for the ultrasonic flow meter. A memory point of the ultrasonic flow meter contains all measured values once. The measured values are stored on the 32 GB built-in memory of the ultrasonic flow meter.

Specification

Speed	
Measurement range up to	-32 ... +32 m/s

Resolution	0.001 m/s
------------	-----------

Accuracy	DN >50 mm: ±1.5 % of Rd for velocities >0.3 m/s / DN <50 mm: ±3.5 % of Rd for velocities >0.3 m/s
----------	---

Ultrasonic sensor	
-------------------	--

Designation	PCE-TDS 200 S SENSOR
-------------	----------------------

Pipe diameter	DN 15 ... 100 mm / Ø 20 ... 108 mm
---------------	------------------------------------

Dimension	45 x 30 x 30 mm
-----------	-----------------

Battery type	Ultrasound
--------------	------------

Frequency	1 MHz
-----------	-------

Operating temperature	-30 ... 160 °C
-----------------------	----------------

Sensor cable length	5 m
---------------------	-----

Ultrasonic sensor	
-------------------	--

Designation	PCE-TDS 200 L SENSOR
-------------	----------------------

Pipe diameter	DN 300 ... 6000 mm / Ø 300 ... 6000 mm
---------------	--

Dimension	91 x 52 x 44 mm
-----------	-----------------

Battery type	Ultrasound
--------------	------------

Frequency	1 MHz
-----------	-------

Temperature	-30 ... 160 °C
-------------	----------------

Sensor cable length	5 m
---------------------	-----

General technical data	
Measuring functions	Flow velocity, Volume flow, Volume

Units	metric, imperial
-------	------------------

Units additional information	Dimensions: mm, in Flow velocity: m/s, ft/s Volume flow: m ³ , l, gal, igl, mgl, cf, bal, ib, ob Volume: m ³ , l, gal, igl, mgl, cf, bal, ib, ob Time specification: seconds, minutes, hours, days
------------------------------	--

Display size	2,8 Inch
--------------	----------

Storage medium	Internal memory
----------------	-----------------

Storage capacity	32 GB
------------------	-------

Storage interval from	1 s
-----------------------	-----

Storage interval to	12 h
---------------------	------

Interface	USB-C
-----------	-------

Pipe material	Steel, Cast iron, Stainless steel, Aluminium, Brass, Copper, PVC, Iron, Nickel, Titanium, Zinc, Acrylic, Polyethylene, Polypropylene, Nylon, User-defined (manual entry of the transversal sound velocity of the pipe material)
---------------	---

Pipe material additional information	Inner lining of the pipe: - No lining - Epoxy resin - Rubber - Mortar - Polystyrene - Polyethylene - Polytetrafluoroethylene - Polyurethane - Polypropylene - Customised (manual entry of the longitudinal sound velocity of the inner lining of the pipe)
--------------------------------------	--

Measured medium	Water, Seawater, Oil, Crude oil, Methanol, Ethanol, Diesel, Petrol, Petroleum, User-defined (manual entry of the sound velocity of the medium)
-----------------	--

Operating time	10 h
----------------	------

Automatic power-off from...to	1 ... 15 min.
-------------------------------	---------------

Automatic power-off can be deactivated	Yes
--	-----

Measuring method	Z, V, N, W
------------------	------------

Alarm	optical, Acoustic
-------	-------------------

Alarm modes	Undercut, overflow, within, beyond
-------------	------------------------------------

Reproducibility	±0.5 %
-----------------	--------

Menu language	Turkish, English, Polish, Spanish, German, Chinese, Russian, Japanese, French, Danish, Italian, Dutch, Portuguese
---------------	---

Protection class (device)	IP52
---------------------------	------

Power supply	USB 5 VDC, 500 mA
--------------	-------------------

Connector type	Device-europlug
----------------	-----------------

Capacity	2500 mAh
----------	----------

Operating conditions	-20 ... 65 °C, 10 ... 95 % RH
----------------------	-------------------------------

Storage conditions	-20 ... 65 °C, 10 ... 95 % RH
--------------------	-------------------------------

Dimensions (L x W x H)	165 x 85 x 32 mm
--------------------------	------------------

Weight	263,5 g
--------	---------