ABB BALDOR RELIANCE

Customer information packet

CFSWDNM3558T-E

2HP, 1760RPM, 3PH, 60HZ, 145TC, 3546M, TENV, F1
Class - None
Division - Not Applicable

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/5/2026 12:50:04 PM

Specifications

Enclosure	TENV
Frame	145TC
Frame Material	Stainless Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	2.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	460.0 V @ 60 HZ
	230.0 V @ 60 HZ
Agency Approvals	CSA EEV
	CURUSEEV
	NEMA PREMIUM
	NEMA_PREMIUM
	WEEE
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	5.600 A @ 208.0 V
	5.300 A @ 230.0 V
	2.650 A @ 460.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	86.5 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK

Part Detail

Revision	B
Type	AC
Mech. spec.	35E4742
Base	
Status	PRD/A
Elec. spec.	35WGZ811
Layout	35LYE4742
Eff. date	10-01-2024
CD Diagram	CD0005
Poles	04
Leads	9#18 Y
Proprietary	False
Created date	03-11-2022

Front Shaft Indicator	None
Heater Indicator	No Heater
High Voltage Full Load Amps	2.7 a
Insulation Class	H
Inverter Code	Inverter Duty
KVA Code	L
Lifting Lugs	No Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Max Speed	2700 rpm
Motor Finish	UNPAINTED
Motor Lead Quantity/Wire Size	9 @ 18 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3546M
Mounting Arrangement	F1
Number of Poles	4
Overall Length	15.09 IN
Power Factor	80
Product Family	WD All SS Encapsulated
Pulley End Bearing Type	Sealed Bearing
Pulley Face Code	C-Face
Pulley Shaft Indicator	Standard
Rodent Screen	None
Service Factor	1.15
Shaft Diameter	0.875 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	1760 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor

Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP4427AAA01												
CAT #	CFSWDNM3558T-E			**WT**	63	**LBS**						
SPEC	35E4742Z811G1			**ENCL**	TENV							
SER #				**CC**	010A	**IP**	69					
HP	2			**MAG CUR**	2.7/1.35							
VOLTS	230/460					**NEMA NOM. EFF**	86.5					
AMPS	5.3/2.65					**PF**	80					
RATING	40C AMB-CONT											
RPM	1760				**MAX RPM**	2700						
FRAME	145TC	**HZ**	60	**CODE**	L	**CLASS**	H					
SER.F.	1.15	**SF AMP**	6/3			**PH**	3	**DES**	B			
DE	6205			**ODE**	6205							
LUBRICATION	POLYREX EM											
ID LOGO	**INVERTER TYPE**			**VPWM**		**CHP**	60	**TO**	90		1.5:1	
ID LOGO	**WK2**	0.332	**CT**	15	**TO**	60		4:1				
ID LOGO	**SL HZ**	1.33	**VT**	3	**TO**	60		20:1				
						QR						
YR												

AC Induction Motor Performance Data
Record # 87105
Preliminary Data Sheet

Winding: 35WGZ811-R001	**Type:** 3546M	**Enclosure:** TENV

Nameplate Data				**460 V, 60 Hz: High Voltage Connection**	
Rated Output (HP)			2	**Full Load Torque**	6 LB-FT
Volts			230/460	**Start Configuration**	direct on line
Full Load Amps			5.3/2.65	**Breakdown Torque**	27.78 LB-FT
R.P.M.			1760	**Pull-up Torque**	16.81 LB-FT
Hz	60	**Phase**	3	**Locked-rotor Torque**	21.79 LB-FT
NEMA Design Code	B	**KVA Code**	L	**Starting Current**	25.07 A
Service Factor (S.F.)			1.15	**No-load Current**	1.36 A
NEMA Nom. Eff.	86.5	**Power Factor**	80	**Line-line Res. @ 25ºC**	7.86 Ω
Rating - Duty			40C AMB-CONT	**Temp. Rise @ Rated Load**	100°C
S.F. Amps			6/3	**Temp. Rise @ S.F. Load**	122°C
				Locked-rotor Power Factor	51.7
				Rotor inertia	0.332 lb-ft²

Load Characteristics 460 V, 60 Hz, 2 HP

% of Rated Load	**25**	**50**	**75**	**100**	**125**	**150**	**S.F.**
Power Factor	39	61	73	80	85	87	83
Efficiency	83.3	88.6	89.2	88.7	87.5	86	88
Speed	1790	1781	1771	1760	1748	1735	1753
Line amperes	1.5	1.78	2.17	2.65	3.18	3.77	2.97


ABB Motors and Mechanical Inc.

WINDING # 35WGZ811


2 HP 3 PH 60 HZ 1760 RPM 460 V 3546M

Typical performance - not guaranteed values.

TORQUES(LB-FT): PO=27.78 PU=16.81 LR=21.79 LRA=25.07



35LYE4742



PULLEY END DETAIL

CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT THE PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION


REV. DESC: ADD DIM TO AXIAL SEAL LOCATION			
REV: F	VERSION: 06	REVISED: 12:58:55 07/23/2026	TDR: 000001276312
35LYE4742	MODEL NO. 35LYE4742		REF: -
	BY: USALMAZ		


BALDOR - RELIANCE®

STD HORZ 143/5TC TENV 35M WD11/12

35LYE4742

CD0005





NOTES:

1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
2. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
3. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY BE A MULTIPLE OF THOSE SHOWN ABOVE.
4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

CD0005

REV. DESC: REVISE TO SHOW OPTIONAL COLORS			BALDOR ELECTRIC Co.
REV. LTR: E	BY: JLP	REVISED: 01/19/99 10:15	TDR: 0171435
CD0005		FILE: AAA00005140	MDL: –
		MTL: –	3PH, DV, 9 LEADS