

1. IDENTIFICATION

Product Name	Tide Professional Coldwater Laundry Detergent
Product Code(s)	5-05
Product Identifier	PA00216163_PROF_NG
Product Type:	Finished Product - Professional Use Only
Recommended Use	Detergent.
Synonyms	97202566
Details of the supplier of the safety data sheet	Procter & Gamble Professional 1 P&G Plaza Cincinnati, Ohio 45202 Procter & Gamble Inc. P.O. Box 355, Station A Toronto, ON M5W 1C5 1-800-332-7787
E-mail Address	pgsds.im@pg.com
Emergency Telephone	Transportation (24 HR) CHEMTREC - 1-800-424-9300 (U.S./ Canada) or 1-703-527-3887 Mexico toll free in country: 800-681-9531

2. HAZARD IDENTIFICATION

This product is classified under 29CFR 1910.1200(d) and the Canadian Hazardous Products Regulation as follows:.

Hazard Category

Acute toxicity - Oral
Eye Damage / Irritation
Flammable Liquids
Signal Word

Category 4
Category 2B
Category 4
WARNING

Hazard Statements

Causes eye irritation
Harmful if swallowed
Combustible liquid

Hazard pictograms



Precautionary Statements

Wash hands thoroughly after handling
Do not eat, drink or smoke when using this product
Keep away from heat/sparks/open flames/hot surfaces. — No smoking
Keep container tightly closed

Precautionary Statements - Response

IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing
If eye irritation persists: Get medical advice/attention
IF SWALLOWED:
Rinse with plenty of water
Drink 1 or 2 glasses of water
Call a POISON CENTER or doctor/physician if you feel unwell
In case of fire: Use water, CO2, dry chemical, or foam for extinction

Precautionary Statements - Storage Store in a well-ventilated place. Keep cool

Precautionary Statements - Disposal Dispose of contents/container in accordance with local regulation

3. COMPOSITION/INFORMATION ON INGREDIENTS

Ingredients are listed according to 29CFR 1910.1200 Appendix D and the Canadian Hazardous Products Regulation

Chemical Name	Synonyms	Trade Secret	CAS-No	Weight-%
Benzenesulfonic acid, mono-C10-16-alkyl derivs., sodium salts	Benzenesulfonic acid, mono-C10-16-alkyl derivs., sodium salts	No	68081-81-2	5 - 10
Poly(oxy-1,2-ethanediyl), alpha-sulfo-omega-hydroxy-, C10-16-alkyl ethers, sodium salts	Poly(oxy-1,2-ethanediyl), alpha-sulfo-omega-hydroxy-, C10-16-alkyl ethers, sodium salts	No	68585-34-2	5 - 10
Alcohols, C14-15, ethoxylated	Alcohols, C14-15, ethoxylated	No	68951-67-7	1 - 5
Propylene glycol	Propylene Glycol	No	57-55-6	1 - 5
Dodecanoic acid, sodium salt (1:1)	Dodecanoic acid, sodium salt (1:1)	No	629-25-4	1 - 5
Disodium tetraborate pentahydrate	Boron sodium oxide (B4Na2O7), pentahydrate	No	12179-04-3	0.5 - 1.5
Glycine, N,N-bis[2-[bis(carboxymethyl)amino]ethyl]-, sodium salt (1:5)	Glycine, N,N-bis[2-[bis(carboxymethyl)amino]ethyl]-, sodium salt (1:5)	No	140-01-2	0.1 - 1.0

Additional information

Actual substance concentrations fall within the ranges stated. Maximum values do not necessarily represent the values present in the formula.

4. FIRST AID MEASURES

First aid measures for different exposure routes

Eye contact

Rinse with plenty of water. Get medical attention immediately if irritation persists.

Skin contact

Rinse with plenty of water. Get medical attention if irritation develops and persists.

Ingestion

Rinse mouth. Drink 1 or 2 glasses of water. Do NOT induce vomiting. Get medical attention immediately if symptoms occur.

Inhalation

Move to fresh air. If symptoms persist, call a physician.

Most important symptoms/effects, acute and delayed None under normal use conditions.

F. Indication of immediate medical attention and special treatment needed, if necessary

Notes to Physician Treat symptomatically.

5. FIRE-FIGHTING MEASURES

Suitable extinguishing media	In case of fire: Use water, CO2, dry chemical, or foam for extinction.
Unsuitable Extinguishing Media	Do not use a solid water stream as it may scatter and spread fire.
Special hazard	Fumes may catch fire.
Special protective equipment for fire-fighters	As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.
Specific hazards arising from the chemical	None.

6. ACCIDENTAL RELEASE MEASURES

Personal precautions, protective equipment and emergency procedures

Personal precautions	Use personal protective equipment. Do not get in eyes, on skin, or on clothing.
Advice for emergency responders	Use personal protective equipment as required.
Environmental precautions	Should not be released into the environment

Methods and materials for containment and cleaning up

Methods for containment	Absorb with earth, sand or other non-combustible material and transfer to containers for later disposal.
Methods for cleaning up	Contain spillage, and then collect with non-combustible absorbent material, (e.g. sand, earth, diatomaceous earth, vermiculite) and place in container for disposal according to local / national regulations (see section 13).

7. HANDLING AND STORAGE

Precautions for safe handling

Advice on safe handling	Keep away from open flames, hot surfaces and sources of ignition. Use personal protective equipment as required. Keep container closed when not in use. Never return spills in original containers for re-use. Keep out of the reach of children.
--------------------------------	---

Conditions for safe storage, including any incompatibilities

Storage Conditions	Keep containers tightly closed in a dry, cool and well-ventilated place. Store in a cool/low-temperature, well-ventilated, dry place away from heat and ignition sources.
Incompatible products	None known.

8. EXPOSURE CONTROLS/PERSONAL PROTECTION

Control parameters

Exposure Guidelines

Chemical Name	CAS-No	ACGIH TLV	OSHA PEL	Mexico PEL
Disodium tetraborate pentahydrate	12179-04-3	STEL: 6 mg/m ³ inhalable particulate matter TWA: 2 mg/m ³ inhalable particulate matter	(vacated) TWA: 10 mg/m ³	Mexico: TWA 1 mg/m ³

Chemical Name	CAS-No	Alberta	Quebec	Ontario TWAEV	British Columbia
Propylene glycol	57-55-6			TWA: 10 mg/m ³ TWA: 50 ppm TWA: 155 mg/m ³	
Disodium tetraborate pentahydrate	12179-04-3	TWA: 1 mg/m ³ STEL: 3 ppm	TWA: 1 mg/m ³	TWA: 2 mg/m ³ STEL: 6 mg/m ³	TWA: 2 mg/m ³ STEL: 6 mg/m ³

No relevant exposure guidelines for other ingredients

Exposure controls

Engineering Measures

Distribution, Workplace and Household Settings:

Ensure adequate ventilation

Product Manufacturing Plant (needed at Product-Producing Plant ONLY):

Where reasonably practicable this should be achieved by the use of local exhaust ventilation and good general extraction

Personal Protective Equipment

Eye Protection

Distribution, Workplace and Household Settings:

No special protective equipment required

Product Manufacturing Plant (needed at Product-Producing Plant ONLY):

Use appropriate eye protection

Hand Protection

Distribution, Workplace and Household Settings:

No special protective equipment required

Product Manufacturing Plant (needed at Product-Producing Plant ONLY):

Protective gloves

Skin and Body Protection

Distribution, Workplace and Household Settings:

No special protective equipment required

Product Manufacturing Plant (needed at Product-Producing Plant ONLY):

Wear suitable protective clothing

Respiratory Protection

Distribution, Workplace and Household Settings:

No special protective equipment required

Product Manufacturing Plant (needed at Product-Producing Plant ONLY):

In case of inadequate ventilation wear respiratory protection

9. PHYSICAL AND CHEMICAL PROPERTIES

Physical State @20°C

Liquid

Appearance

blue

Odor

Scented

Odor threshold

No information available

Property	Values	Note
pH value	7.7 - 8.6	
Melting Point / Freezing Point	No information available	
Boiling point / boiling range	No information available	
Flash point	65.5 °C / 149.9 °F	Closed cup. Does not sustain combustion.
Evaporation rate	No information available	
Flammability (solid, gas)	No information available	
Flammability Limits in Air		
Upper flammability limit	No information available	
Lower Flammability Limit	No information available	
Vapor pressure	No information available	
Vapor density	No information available	
Relative density	No information available	
Water solubility	No information available	
Partition coefficient: n-octanol/water	No information available	
Autoignition temperature	No information available	.
Decomposition temperature	No information available	.
Viscosity	No information available	
VOC Content (%)	Products comply with US state and federal regulations for VOC content in consumer products.	

10. STABILITY AND REACTIVITY

Reactivity	None under normal use conditions.
Stability	Stable under normal conditions.
Hazardous polymerization	Hazardous polymerization does not occur.
Hazardous Reactions	None under normal processing.
Conditions to Avoid	Keep away from open flames, hot surfaces and sources of ignition.
Incompatible materials	None in particular.
Hazardous Decomposition Products	None under normal use conditions.

11. TOXICOLOGICAL INFORMATION

Product Information

Information on likely routes of exposure

Inhalation	No known effect.
Skin contact	No known effect.
Ingestion	May be harmful if swallowed.
Eye contact	Irritating to eyes.

Delayed and immediate effects as well as chronic effects from short and long-term exposure

Acute toxicity	May be harmful if swallowed.
Skin corrosion/irritation	No known effect.
Serious eye damage/eye irritation	Irritating to eyes.
Skin sensitization	No known effect.
Respiratory sensitization	No known effect.
Germ cell mutagenicity	No known effect.
Neurological Effects	No known effect.
Reproductive toxicity	No known effect.
Developmental toxicity	No known effect.
Teratogenicity	No known effect.
STOT - single exposure	No known effect.
STOT - repeated exposure	No known effect.

Target Organ Effects No known effect.
Aspiration hazard No known effect.
Carcinogenicity No known effect.

Component Information

Chemical Name	CAS-No	Oral LD50	Dermal LD50	Inhalation LC50
Poly(oxy-1,2-ethanediyl), alpha-sulfo-omega-hydroxy-, C10-16-alkyl ethers, sodium salts	68585-34-2	>2001 mg/kg	-	-
Alcohols, C14-15, ethoxylated	68951-67-7	> 300 mg/kg bw	> 2000 mg/kg bw	-
Glycine, N,N-bis[2-[bis(carboxymethyl)amino ethyl]-, sodium salt (1:5)	140-01-2	> 5000 mg/kg bw (OECD 401)	> 2000 mg/kg bw (OECD 402)	-

12. ECOLOGICAL INFORMATION

Ecotoxicity

The product is not expected to be hazardous to the environment.

Persistence and degradability No information available.

Bioaccumulative potential No information available.

Mobility No information available.

Other adverse effects No information available.

13. DISPOSAL CONSIDERATIONS

Waste treatment methods

Waste from Residues/Unused Products Disposal should be in accordance with applicable regional, national and local laws and regulations.

Contaminated packaging Disposal should be in accordance with applicable regional, national and local laws and regulations.

California Hazardous Waste Codes (non-household setting) 331

14. TRANSPORT INFORMATION

DOT Not regulated

IMDG Not regulated

IATA Not regulated

15. REGULATORY INFORMATION

U.S. Federal Regulations

SARA 313

Section 313 of Title III of the Superfund Amendments and Reauthorization Act of 1986 (SARA). This product does not contain any chemicals which are subject to the reporting requirements of the Act and Title 40 of the Code of Federal Regulations, Part 372

CERCLA

This material, as supplied, contains one or more substances regulated as a hazardous substance under the Comprehensive

Environmental Response Compensation and Liability Act (CERCLA) (40 CFR 302):.

Chemical Name	CAS-No	Hazardous Substances RQs	Extremely Hazardous Substances RQs	CERCLA/SARA 302 TPQ
Sodium hydroxide	1310-73-2	1000 lb	-	

Clean Air Act, Section 112 Hazardous Air Pollutants (HAPS) (see 40 CFR 61)

This product does not contain any substances regulated as hazardous air pollutants (HAPS) under Section 112 of the Clean Air Act Amendments of 1990.

Clean Water Act

This product contains the following substances which are regulated pollutants pursuant to the Clean Water Act (40 CFR 122.21 and 40 CFR 122.42):.

Chemical Name	CAS-No	CWA - Reportable Quantities	CWA - Toxic Pollutants	CWA - Priority Pollutants	CWA - Hazardous Substances
Sodium hydroxide	1310-73-2	1000 lb	-	-	X

California Proposition 65

This product is not subject to warning labeling under California Proposition 65.

U.S. State Regulations (RTK)

Chemical Name	CAS-No	New Jersey
Propylene glycol	57-55-6	X

Chemical Name	CAS-No	Massachusetts
Disodium tetraborate pentahydrate	12179-04-3	X

Chemical Name	CAS-No	Pennsylvania
Propylene glycol	57-55-6	X
Ethanol	64-17-5	X
2,2'-Oxybisethanol	111-46-6	X
Sodium hydroxide	1310-73-2	X

International Inventories

United States

All intentionally-added components of this product(s) are listed on the US TSCA Inventory

Canada

This product is in compliance with CEPA for import by P&G

Legend

United States Toxic Substances Control Act Section 8(b) Inventory (TSCA)

CEPA - Canadian Environmental Protection Act

16. OTHER INFORMATION

Issuing Date: 21-Feb-2018

Revision Date: 05-Dec-2018

Disclaimer.

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation,

disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text

End of SDS