



Fibre-Metal®

Type II Non-Vented, Full Brim Industrial Climbing Helmet with HDPE Shell, 8-Point Textile Suspension, Wheel Ratchet Adjustment and a 4-Point Chinstrap

- Full brim shell design provides protection from the elements when working outdoors
- Liquid Crystal Polymer (LCP) yarn in the six strap, eight-point suspension disperses force transferred from the shell to the user
- Non-Newtonian foam combined with a traditional EPS foam liner
- One-way moisture transfer and fast-dry chin strap help elevate user comfort in high-temperature work environments, by providing a dry and comfortable feel
- Compatible with a wide range of safety accessories such as a welding helmet, visor, faceshield, UV shade, earmuffs, or task light
- ANSI/CSA Certified, Type II, Class E

Technical Data

Color	Black, Red, Green, Black Carbon, Gray, White, Yellow, Brown, Blue, Orange
Sizes Available	OS
Packaging	Bagged Each
Packed	8/Case
Case Weight (lbs)	0.00
Country of Origin	China
Shell Material	HDPE
Shell	Non-Vented
Brim Style	Full
Brim Length	Standard
Size Adjustment	Wheel Ratchet
Chin Strap	4-Point Polyester
Certifications	ANSI/ISEA Z89.1, CSA Z94.1 Certified

Performance Data

ANSI Type	Type II
Electrical Class	Class E

SKU Information

SKU	COLOR	SIZE	UPC	UPC (INNER)	UPC (CASE)
CSH12011	Black	OS	883940457499		
CSH12080	Black Carbon	OS	883940457505		
CSH12071	Blue	OS	883940457451		
CSH12012	Brown	OS	883940457482		
CSH12009	Gray	OS	883940457420		
CSH12004	Green	OS	883940457444		
CSH12046	Orange	OS	883940457468		
CSH12015	Red	OS	883940457475		
CSH12001	White	OS	883940457413		
CSH12002	Yellow	OS	883940457437		