

# SAFETY DATA SHEET

According to 29 CFR 1910.1200  
TF22002 SERIES

## Section 1. Identification

**Product name** : TRI-FLOW® Synthetic Grease  
TF22002, TF22003, TF22004

**Product code** : TF22002 SERIES

**Other means of identification** : Not available.

**Product type** : Liquid.

### Relevant identified uses of the substance or mixture and uses advised against

Paint or paint related material.

**Manufacturer** : Tri-Flow Industrial Group  
Cleveland, OH 44115

**Emergency telephone number of the company** : US / Canada: (216) 566-2917  
Mexico: SETIQ 800-00-214-00 / 55-5559-1588 Available 24 hours and 365 days a year

**Product Information Telephone Number** : US / Canada: 877-487-4356  
Mexico: Not Available

**Transportation Emergency Telephone Number** : US / Canada: (800) 424-9300  
Mexico: SETIQ 800-00-214-00 / 55-5559-1588 Available 24 hours and 365 days a year

## Section 2. Hazards identification

**OSHA/HCS status** : While this material is not considered hazardous by the OSHA Hazard Communication Standard (29 CFR 1910.1200), this SDS contains valuable information critical to the safe handling and proper use of the product. This SDS should be retained and available for employees and other users of this product.

**Classification of the substance or mixture** : Not classified.

### GHS label elements

**Signal word** : No signal word.

**Hazard statements** : No known significant effects or critical hazards.

### Precautionary statements

**Prevention** : Not applicable.

**Response** : Not applicable.

**Storage** : Not applicable.

**Disposal** : Not applicable.

**Supplemental label elements** FOR INDUSTRIAL USE ONLY.

Please refer to the SDS for additional information. Keep out of reach of children. Do not transfer contents to other containers for storage.

**Hazards not otherwise classified** : None known.

**Date of issue/Date of revision** : 5/3/2026

**Date of previous issue** : 12/23/2025

**Version** : 10

1/11

TF22002 SERIES TRI-FLOW® Synthetic Grease  
TF22002, TF22003, TF22004

**SHW-85-NA-GHS-US**

## Section 2. Hazards identification

**Hazards identified when used** : No known significant effects or critical hazards.

## Section 3. Composition/information on ingredients

**Substance/mixture** : Mixture  
**Other means of identification** : Not available.

### CAS number/other identifiers

Ingredient name	% by weight	Identifiers
Fumed Amorphous Silica	≤5	112945-52-5

Any concentration shown as a range is to protect confidentiality or is due to batch variation.

**There are no additional ingredients present which, within the current knowledge of the supplier and in the concentrations applicable, are classified and hence require reporting in this section.**

Occupational exposure limits, if available, are listed in Section 8.

## Section 4. First aid measures

### Description of necessary first aid measures

- Eye contact** : Immediately flush eyes with plenty of water, occasionally lifting the upper and lower eyelids. Check for and remove any contact lenses. Get medical attention if irritation occurs.
- Inhalation** : Remove victim to fresh air and keep at rest in a position comfortable for breathing. Get medical attention if symptoms occur.
- Skin contact** : Flush contaminated skin with plenty of water. Remove contaminated clothing and shoes. Get medical attention if symptoms occur.
- Ingestion** : Wash out mouth with water. If material has been swallowed and the exposed person is conscious, give small quantities of water to drink. Do not induce vomiting unless directed to do so by medical personnel. Get medical attention if symptoms occur.

### Most important symptoms/effects, acute and delayed

#### Potential acute health effects

- Eye contact** : No known significant effects or critical hazards.
- Inhalation** : No known significant effects or critical hazards.
- Skin contact** : No known significant effects or critical hazards.
- Ingestion** : No known significant effects or critical hazards.

#### Over-exposure signs/symptoms

- Eye contact** : No specific data.
- Inhalation** : No specific data.
- Skin contact** : No specific data.
- Ingestion** : No specific data.

### Indication of immediate medical attention and special treatment needed, if necessary

- Notes to physician** : Treat symptomatically. Contact poison treatment specialist immediately if large quantities have been ingested or inhaled.
- Specific treatments** : No specific treatment.
- Protection of first-aiders** : No action shall be taken involving any personal risk or without suitable training.

## Section 4. First aid measures

See toxicological information (Section 11)

## Section 5. Fire-fighting measures

### Extinguishing media

**Suitable extinguishing media** : Use an extinguishing agent suitable for the surrounding fire.

**Unsuitable extinguishing media** : None known.

**Specific hazards arising from the chemical** : In a fire or if heated, a pressure increase will occur and the container may burst.

**Hazardous thermal decomposition products** : Decomposition products may include the following materials:  
carbon dioxide  
carbon monoxide  
halogenated compounds  
metal oxide/oxides

**Special protective actions for fire-fighters** : Promptly isolate the scene by removing all persons from the vicinity of the incident if there is a fire. No action shall be taken involving any personal risk or without suitable training.

**Special protective equipment for fire-fighters** : Fire-fighters should wear appropriate protective equipment and self-contained breathing apparatus (SCBA) with a full face-piece operated in positive pressure mode.

## Section 6. Accidental release measures

### Personal precautions, protective equipment and emergency procedures

**For non-emergency personnel** : No action shall be taken involving any personal risk or without suitable training. Evacuate surrounding areas. Keep unnecessary and unprotected personnel from entering. Do not touch or walk through spilled material. Put on appropriate personal protective equipment.

**For emergency responders** : If specialized clothing is required to deal with the spillage, take note of any information in Section 8 on suitable and unsuitable materials. See also the information in "For non-emergency personnel".

**Environmental precautions** : Avoid dispersal of spilled material and runoff and contact with soil, waterways, drains and sewers. Inform the relevant authorities if the product has caused environmental pollution (sewers, waterways, soil or air).

### Methods and materials for containment and cleaning up

**Small spill** : Stop leak if without risk. Move containers from spill area. Absorb with an inert material and place in an appropriate waste disposal container. Dispose of via a licensed waste disposal contractor.

**Large spill** : Stop leak if without risk. Move containers from spill area. Prevent entry into sewers, water courses, basements or confined areas. Wash spillages into an effluent treatment plant or proceed as follows. Dispose of via a licensed waste disposal contractor. Contain and collect spillage with non-combustible, absorbent material e.g. sand, earth, vermiculite or diatomaceous earth and place in container for disposal according to local regulations.

## Section 7. Handling and storage

### Precautions for safe handling

- Protective measures** : Put on appropriate personal protective equipment (see Section 8).
- Advice on general occupational hygiene** : Eating, drinking and smoking should be prohibited in areas where this material is handled, stored and processed. Workers should wash hands and face before eating, drinking and smoking. Remove contaminated clothing and protective equipment before entering eating areas. See also Section 8 for additional information on hygiene measures.

- Conditions for safe storage, including any incompatibilities** : Store in accordance with local regulations. Store in original container protected from direct sunlight in a dry, cool and well-ventilated area, away from incompatible materials (see Section 10) and food and drink. Keep container tightly closed and sealed until ready for use. Containers that have been opened must be carefully resealed and kept upright to prevent leakage. Do not store in unlabeled containers. Use appropriate containment to avoid environmental contamination. See Section 10 for incompatible materials before handling or use.

## Section 8. Exposure controls/personal protection

### Control parameters

#### Occupational exposure limits (OSHA United States)

Ingredient name	CAS #	Exposure limits
Fumed Amorphous Silica	112945-52-5	<b>NIOSH REL (United States, 10/2020)</b> <b>[SILICA, AMORPHOUS] NIA.</b> TWA 10 hours: 6 mg/m <sup>3</sup> .

#### Occupational exposure limits (Canada)

None.

#### Occupational exposure limits (Mexico)

None.

#### Biological exposure indices (United States)

No exposure indices known.

#### Biological exposure indices (Canada)

No exposure indices known.

#### Biological exposure indices (Mexico)

No exposure indices known.

- Appropriate engineering controls** : Good general ventilation should be sufficient to control worker exposure to airborne contaminants.
- Environmental exposure controls** : Emissions from ventilation or work process equipment should be checked to ensure they comply with the requirements of environmental protection legislation. In some cases, fume scrubbers, filters or engineering modifications to the process equipment will be necessary to reduce emissions to acceptable levels.

### Individual protection measures

- Hygiene measures** : Wash hands, forearms and face thoroughly after handling chemical products, before eating, smoking and using the lavatory and at the end of the working period. Appropriate techniques should be used to remove potentially contaminated clothing. Wash contaminated clothing before reusing. Ensure that eyewash stations and safety showers are close to the workstation location.

## Section 8. Exposure controls/personal protection

- Eye/face protection** : Safety eyewear complying with an approved standard should be used when a risk assessment indicates this is necessary to avoid exposure to liquid splashes, mists, gases or dusts. If contact is possible, the following protection should be worn, unless the assessment indicates a higher degree of protection: safety glasses with side-shields.
- Skin protection**
  - Hand protection** : Chemical-resistant, impervious gloves complying with an approved standard should be worn at all times when handling chemical products if a risk assessment indicates this is necessary.
  - Body protection** : Personal protective equipment for the body should be selected based on the task being performed and the risks involved and should be approved by a specialist before handling this product.
  - Other skin protection** : Appropriate footwear and any additional skin protection measures should be selected based on the task being performed and the risks involved and should be approved by a specialist before handling this product.
- Respiratory protection** : Based on the hazard and potential for exposure, select a respirator that meets the appropriate standard or certification. Respirators must be used according to a respiratory protection program to ensure proper fitting, training, and other important aspects of use.

## Section 9. Physical and chemical properties

The conditions of measurement of all properties are at standard temperature and pressure unless otherwise indicated.

### Appearance

- Physical state** : Liquid.
- Color** : Various
- Odor** : Not available.
- Odor threshold** : Not available.
- pH** : Not applicable.
- Melting point/freezing point** : Not available.
- Boiling point or initial boiling point and boiling range** : 100°C (212°F)
- Flash point** : Open cup: 204°C (399.2°F) [Cleveland Open Cup]
- Evaporation rate** : Not available.
- Flammability** : Not available.
- Lower and upper explosion limit/flammability limit** : Not available.
- Vapor pressure** : Not available.
- Relative vapor density** : Not available.
- Relative density** : 0.89
- Density** : 0.89 g/cm<sup>3</sup>
- Solubility(ies)** :

Media	Result
cold water	Not soluble

- Partition coefficient: n-octanol/water** : Not applicable.
- Auto-ignition temperature** : Not available.
- Decomposition temperature** : Not available.

## Section 9. Physical and chemical properties

- Viscosity** : Dynamic (room temperature): Not available.  
Kinematic (room temperature): Not available.  
Kinematic (40°C (104°F)): 781 mm<sup>2</sup>/s (781 cSt)
- Molecular weight** : Not applicable.
- Particle characteristics**
- Median particle size** : Not applicable.

## Section 10. Stability and reactivity

- Reactivity** : No specific test data related to reactivity available for this product or its ingredients.
- Chemical stability** : The product is stable.
- Possibility of hazardous reactions** : Under normal conditions of storage and use, hazardous reactions will not occur.
- Conditions to avoid** : No specific data.
- Incompatible materials** : No specific data.
- Hazardous decomposition products** : Under normal conditions of storage and use, hazardous decomposition products should not be produced.

## Section 11. Toxicological information

### Information on toxicological effects

#### Acute toxicity

Product/ingredient name	Result
Fumed Amorphous Silica	Rat - Oral - LD50 3160 mg/kg

**Conclusion/Summary [Product]** : Not available.

#### Skin corrosion/irritation

Not available.

**Conclusion/Summary [Product]** : Not available.

#### Serious eye damage/eye irritation

Not available.

**Conclusion/Summary [Product]** : Not available.

#### Respiratory corrosion/irritation

Not available.

**Conclusion/Summary [Product]** : Not available.

# Section 11. Toxicological information

## Respiratory or skin sensitization

Not available.

### Skin

**Conclusion/Summary [Product]** : Not available.

### Respiratory

**Conclusion/Summary [Product]** : Not available.

## Germ cell mutagenicity

Not available.

**Conclusion/Summary [Product]** : Not available.

## Carcinogenicity

Not available.

**Conclusion/Summary [Product]** : Not available.

## Classification

Product/ingredient name	OSHA	IARC	NTP
Fumed Amorphous Silica	-	3	-

## Reproductive toxicity

Not available.

**Conclusion/Summary [Product]** : Not available.

## Specific target organ toxicity (single exposure)

Not available.

## Specific target organ toxicity (repeated exposure)

Not available.

## Aspiration hazard

Not available.

## Information on the likely routes of exposure

Not available.

## Potential acute health effects

**Eye contact** : No known significant effects or critical hazards.

**Inhalation** : No known significant effects or critical hazards.

**Skin contact** : No known significant effects or critical hazards.

**Ingestion** : No known significant effects or critical hazards.

# Section 11. Toxicological information

## Symptoms related to the physical, chemical and toxicological characteristics

- Eye contact** : No specific data.
- Inhalation** : No specific data.
- Skin contact** : No specific data.
- Ingestion** : No specific data.

## Delayed and immediate effects and also chronic effects from short and long term exposure

### Short term exposure

- Potential immediate effects** : Not available.
- Potential delayed effects** : Not available.

### Long term exposure

- Potential immediate effects** : Not available.
- Potential delayed effects** : Not available.

## Potential chronic health effects

Not available.

**Conclusion/Summary [Product]** : Not available.

- General** : No known significant effects or critical hazards.
- Carcinogenicity** : No known significant effects or critical hazards.
- Mutagenicity** : No known significant effects or critical hazards.
- Reproductive toxicity** : No known significant effects or critical hazards.

## Numerical measures of toxicity

### Acute toxicity estimates

Product/ingredient name	Oral (mg/kg)	Dermal (mg/kg)	Inhalation (gases) (ppm)	Inhalation (vapors) (mg/l)	Inhalation (dusts and mists) (mg/l)
Fumed Amorphous Silica	3160	N/A	N/A	N/A	N/A

# Section 12. Ecological information

## Toxicity

Not available.

**Conclusion/Summary [Product]** : Not available.

## Persistence and degradability

Not available.

**Conclusion/Summary [Product]** : Not available.

## Section 12. Ecological information

### Bioaccumulative potential

Not available.

### Mobility in soil

**Soil/Water partition coefficient** : Not available.

### Other adverse effects

No known significant effects or critical hazards.

## Section 13. Disposal considerations

**Disposal methods** : The generation of waste should be avoided or minimized wherever possible. Disposal of this product, solutions and any by-products should at all times comply with the requirements of environmental protection and waste disposal legislation and any regional local authority requirements. Dispose of surplus and non-recyclable products via a licensed waste disposal contractor. Waste should not be disposed of untreated to the sewer unless fully compliant with the requirements of all authorities with jurisdiction. Waste packaging should be recycled. Incineration or landfill should only be considered when recycling is not feasible. This material and its container must be disposed of in a safe way. Empty containers or liners may retain some product residues. Avoid dispersal of spilled material and runoff and contact with soil, waterways, drains and sewers.

## Section 14. Transport information

	<b>DOT Classification</b>	<b>TDG Classification</b>	<b>Mexico Classification</b>	<b>IATA</b>	<b>IMDG</b>
<b>UN number</b>	Not regulated.	Not regulated.	Not regulated.	Not regulated.	Not regulated.
<b>UN proper shipping name</b>	-	-	-	-	-
<b>Transport hazard class(es)</b>	-	-	-	-	-
<b>Packing group</b>	-	-	-	-	-
<b>Environmental hazards</b>	No.	No.	No.	No.	No.
<b>Additional information</b>	-	-	-	-	-

## Section 14. Transport information

**Special precautions for user** : Multi-modal shipping descriptions are provided for informational purposes and do not consider container sizes. The presence of a shipping description for a particular mode of transport (sea, air, etc.), does not indicate that the product is packaged suitably for that mode of transport. All packaging must be reviewed for suitability prior to shipment, and compliance with the applicable regulations is the sole responsibility of the person offering the product for transport. People loading and unloading dangerous goods must be trained on all of the risks deriving from the substances and on all actions in case of emergency situations.

**Transport in bulk according to IMO instruments** : Not available.

**Proper shipping name** : Not available.

## Section 15. Regulatory information

**U.S. Federal regulations** :

California Prop. 65

Not applicable.

International regulations

Montreal Protocol

Not listed.

Stockholm Convention on Persistent Organic Pollutants

Not listed.

**International lists**

- Australia inventory (AIIIC)**: Not determined.
- China inventory (IECSC)**: Not determined.
- Japan inventory (CSCL)**: Not determined.
- Japan inventory (ISHL)**: Not determined.
- Korea inventory (KECI)**: Not determined.
- New Zealand Inventory of Chemicals (NZIoC)**: Not determined.
- Philippines inventory (PICCS)**: Not determined.
- Taiwan Chemical Substances Inventory (TCSI)**: Not determined.
- Thailand inventory**: Not determined.
- Turkey inventory**: Not determined.
- Vietnam inventory**: Not determined.

## Section 16. Other information

**Hazardous Material Information System (U.S.A.)**

Health	/	0
Flammability		1
Physical hazards		0

The customer is responsible for determining the PPE code for this material. For more information on HMIS® Personal Protective Equipment (PPE) codes, consult the HMIS® Implementation Manual.

**Caution:** HMIS® ratings are based on a 0-4 rating scale, with 0 representing minimal hazards or risks, and 4 representing significant hazards or risks. Although HMIS® ratings and the associated label are not required on SDSs or products leaving a facility under 29 CFR 1910.1200, the preparer may choose to provide them. HMIS® ratings are to be used with a fully implemented HMIS® program. HMIS® is a registered trademark and service mark of the American Coatings Association, Inc.

[Procedure used to derive the classification](#)

# Section 16. Other information

Classification	Justification
Not classified.	

## History

**Date of printing** : 5/3/2026

**Date of issue/Date of revision** : 5/3/2026

**Date of previous issue** : 12/23/2025

**Version** : 10

**Key to abbreviations** :

- ATE = Acute Toxicity Estimate
- BCF = Bioconcentration Factor
- GHS = Globally Harmonized System of Classification and Labelling of Chemicals
- IATA = International Air Transport Association
- IBC = Intermediate Bulk Container
- IMDG = International Maritime Dangerous Goods
- LogPow = logarithm of the octanol/water partition coefficient
- MARPOL = International Convention for the Prevention of Pollution From Ships, 1973 as modified by the Protocol of 1978. ("Marpol" = marine pollution)
- N/A = Not available
- SGG = Segregation Group
- UN = United Nations

🔍 Indicates information that has changed from previously issued version.

## Notice to reader

It is recommended that each customer or recipient of this Safety Data Sheet (SDS) study it carefully and consult resources, as necessary or appropriate, to become aware of and understand the data contained in this SDS and any hazards associated with the product. This information is provided in good faith and believed to be accurate as of the effective date herein. However, no warranty, express or implied, is given. The information presented here applies only to the product as shipped. The addition of any material can change the composition, hazards and risks of the product. Products shall not be repackaged, modified, or tinted except as specifically instructed by the manufacturer, including but not limited to the incorporation of products not specified by the manufacturer, or the use or addition of products in proportions not specified by the manufacturer. Regulatory requirements are subject to change and may differ between various locations and jurisdictions. The customer/buyer/user is responsible to ensure that his activities comply with all country, federal, state, provincial or local laws. The conditions for use of the product are not under the control of the manufacturer; the customer/buyer/user is responsible to determine the conditions necessary for the safe use of this product. The customer/buyer/user should not use the product for any purpose other than the purpose shown in the applicable section of this SDS without first referring to the supplier and obtaining written handling instructions. Due to the proliferation of sources for information such as manufacturer-specific SDS, the manufacturer cannot be responsible for SDSs obtained from any other source.