U1P-Aqua - 4T Full Synthetic Motor Oil

SAE 10W-40 NMMA FC-W

Marine | United States

Product Description



U1P-AQUA SAE 10W-40 Full Synthetic 4T Marine Engine Oil, NMMA FC-W is a high-performance oil formulated to exceed the toughest marine industry standards. Combining advanced synthetic base-stock with a specialized marine additive package, it delivers superior wear and corrosion protection for both salt and freshwater engines. Designed for maximum power delivery, it reduces internal friction, enhancing engine life and performance under extreme temperatures, high loads, and high speeds. Perfect for heavy-duty and leisure use, it ensures optimal engine cleanliness, proper oil pressure, and protection against deposits, rust, and corrosion. Compatible with gasoline-fueled four-stroke inboards, outboards, inboard/outboards, and personal watercraft, meeting the needs of major engine manufacturers.



Features and BenefitS

- For all 4-stroke marine engines. All HP ranges.
- Suitable for high performance Outboards, Stern Drive and Inboard engines.
- NMMA FC - W specification ensures optimum anti wear and corrosion protection.
- Extends engine and key component's life, leading to reduced maintenance cost.
- Higher lubrication film strength and viscosity retention to increase fuel efficiency.
- Improved deposit protection and minimum sludge build up for engine cleanliness.
- Reduces oil thickening facilitating extended oil life, inside the manufacturer's oil change interval recommendation.
- Exceeds NMMA FC-W. Compatible with previous certifications.
- Suitable for 4-stroke engines with or without catalytic converter.



Product Code

Presentation	SKU	Manufacture ID	UPC
QT	UFS10404TFCWL	UL424	810050653305
US Gallon (4 QTS)	UFS10404TFCWG	UL424	810050653299
5 Gallon Pail	UFS10404TFCWP	UL424	810050653282
55 Gallon Drum	UFS10404TFCWD	UL424	810050653275
265 Gallon Tote	UFS10404TFCWT	UL424	810050653268



This product meets or exceeds the requirements of:

NMMA FC-W



Properties and Specifications*

Parameter	Result
Appearance	Amber, liquid
Viscosity @ 40°C, cSt, ASTM D445	93.3
Viscosity @ 100°C, cSt, ASTM D445	14.1
Viscosity index, ASTM D2270	155
Pour point, °C (°F) ASTM D97	-38 (-36)
Flash point, °C (°F) ASTM D92	240 (464)
TBN, mgKOH/g, ASTM D2896	7.9

*Typical Properties are typical of those obtained with normal production tolerance and do not constitute a specification. Variations that do not affect product performance are to be expected during normal manufacture and at different blending locations. The information contained herein is subject to change without notice.

Revised: 03/06/2025