Safety Data Sheet

NEVER SEEZ REGULAR GRADE
Revision Number 3

Revision Date 09-May-2018
Supersedes Date: 24-Oct-2017

Section 1: IDENTIFICATION OF THE SUBSTANCE/MIXTURE AND OF THE COMPANY/UNDERTAKING

1.1. Product Identifier

Product Name NEVER SEEZ REGULAR GRADE

1.2. Relevant identified uses of the substance or mixture and uses advised against

Recommended use lubricant.
Uses advised against No information available

1.3. Details of the supplier of the safety data sheet

Responsible Party
Bostik Inc.
11320 W. Watertown Plank Road
Wauwatosa, Wisconsin 53226 USA
Phone: +1 (800) 843-0844 (Domestic Toll Free)
Phone: +1 (414) 774-2250 (International)
Fax: +1 (414) 774-8075

E-mail msds@bostik-us.com

1.4. Emergency telephone number

Telephone: 1-800-227-0332
(Outside U.S.) 1-703-527-3887

Section 2: HAZARD IDENTIFICATION

2.1. Classification of the substance or mixture

Not a dangerous substance or mixture according to OSHA 29 CFR 1910.1200.

2.2. Label Elements

EMERGENCY OVERVIEW

The product contains no substances which at their given concentration, are considered to be hazardous to health

Appearance Paste **Physical State** Liquid **Odor** Petroleum distillates

Precautionary Statements - Prevention
Not applicable

Precautionary Statements - Response
Not applicable

Precautionary Statements - Storage
Not applicable

Precautionary Statements - Disposal
Not applicable

Hazards Not Otherwise Classified (HNOC)
Not applicable

2.3. Other Information

No information available.

Section 3: COMPOSITION/INFORMATION ON INGREDIENTS

3.1 Substances
Mixture

3.2 Mixtures

Chemical Name	CAS No	Weight-%
Graphite	7782-42-5	10 - 30
Copper	7440-50-8	5 - 10
Zinc oxide	1314-13-2	1 - 5
Aluminum	7429-90-5	1 - 5

The exact percentage (concentration) of composition has been withheld as a trade secret.

Section 4: FIRST AID MEASURES

4.1. Description of first aid measures

General Advice If medical advice is needed, have product container or label at hand.

Eye contact In case of contact with substance, immediately flush skin or eyes with running water for at least 20 minutes. If eye irritation persists: Get medical advice/attention.

Skin Contact Wash off immediately with soap and plenty of water while removing all contaminated clothes and shoes. Wash contaminated clothing before reuse. If skin irritation occurs: Get medical advice/ attention.

Inhalation Remove victim to fresh air and keep at rest in a position comfortable for breathing. Get medical attention if symptoms occur.

Ingestion Clean mouth with water and drink afterwards plenty of water. Do NOT induce vomiting. Never give anything by mouth to an unconscious person. Get medical attention if symptoms occur.

Self-Protection of the First Aider Ensure that medical personnel are aware of the material(s) involved, take precautions to protect themselves and prevent spread of contamination.

4.2. Most important symptoms and effects, both acute and delayed

Symptoms No information available.

4.3. Indication of any immediate medical attention and special treatment needed

Note to physicians Treat symptomatically.

4.4. Reference to Other Sections

Reference to other sections Section 8: EXPOSURE CONTROLS/PERSONAL PROTECTION

Section 5: FIRE-FIGHTING MEASURES

5.1. Extinguishing media

Suitable Extinguishing Media
Dry chemical, CO2, water spray or regular foam. Dike fire-control water for later disposal.

Unsuitable Extinguishing Media
Do not scatter spilled material with high pressure water streams.

5.2. Special hazards arising from the substance or mixture

Specific Hazards Arising from the Chemical
Some may burn but none ignite readily.

Explosion Data

Sensitivity to Mechanical Impact	None.
Sensitivity to Static Discharge	None.

5.3. Advice for firefighters

Protective equipment and precautions for firefighters
As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.

Section 6: ACCIDENTAL RELEASE MEASURES

6.1. Personal precautions, protective equipment and emergency procedures

Personal Precautions	Use personal protective equipment as required. Do not touch or walk through spilled material. Stop leak if you can do it without risk.

6.2. Environmental precautions

Environmental Precautions	Prevent entry into waterways, sewers, basements or confined areas. See Section 12 for additional Ecological Information.

6.3. Methods and material for containment and cleaning up

Methods for Containment	Cover with plastic sheet to prevent spreading.
Methods for cleaning up	Use personal protective equipment as required. Take up with sand or other non-combustible absorbent material and place into containers for later disposal. With clean shovel place material into clean, dry container and cover loosely; move containers from spill area. Clean contaminated surface thoroughly.

6.4. Reference to other sections

Reference to other sections	Section 7: HANDLING AND STORAGE Section 8: EXPOSURE CONTROLS/PERSONAL PROTECTION Section 13: DISPOSAL CONSIDERATIONS

Section 7: HANDLING AND STORAGE

7.1. Precautions for safe handling

Advice on safe handling	Use personal protective equipment as required. Handle in accordance with good industrial

hygiene and safety practice. Do not eat, drink or smoke when using this product. Ensure adequate ventilation, especially in confined areas. Wash hands thoroughly after handling.

7.2. Conditions for safe storage, including any incompatibilities

Storage Conditions Keep container tightly closed in a dry and well-ventilated place.

Incompatible Materials None known based on information supplied.

7.3. Specific end use(s)

Other Information No information available.

7.4. References to Other Sections

Reference to other sections Section 13: DISPOSAL CONSIDERATIONS
Section 10: STABILITY AND REACTIVITY

Section 8: EXPOSURE CONTROLS/PERSONAL PROTECTION

8.1. Control parameters

Exposure Guidelines . This product contains substances which in their raw state are powder form, however in this product they are in a non-respirable form. Inhalation of powder/dust particles is unlikely to occur from exposure to this product.

Chemical Name	ACGIH TLV	NIOSH IDLH	OSHA PEL	Mexico
Graphite 7782-42-5	TWA: 2 mg/m³ respirable particulate matter all forms except graphite fibers	IDLH: 1250 mg/m³ TWA: 2.5 mg/m³ natural respirable dust	TWA: 15 mg/m³ total dust synthetic TWA: 5 mg/m³ respirable fraction synthetic TWA: 15 mppcf natural	TWA: 2 mg/m³
Copper 7440-50-8	TWA: 0.2 mg/m³ fume TWA: 1 mg/m³ Cu dust and mist	IDLH: 100 mg/m³ dust, fume and mist IDLH: 100 mg/m³ Cu dust and mist TWA: 1 mg/m³ dust and mist TWA: 0.1 mg/m³ fume TWA: 1 mg/m³ Cu dust and mist	TWA: 0.1 mg/m³ fume TWA: 1 mg/m³ dust and mist	TWA: 0.2 mg/m³ TWA: 1 mg/m³ STEL: 2 mg/m³
Zinc oxide 1314-13-2	STEL: 10 mg/m³ respirable particulate matter TWA: 2 mg/m³ respirable particulate matter	IDLH: 500 mg/m³ Ceiling: 15 mg/m³ dust TWA: 5 mg/m³ dust and fume STEL: 10 mg/m³ fume	TWA: 5 mg/m³ fume TWA: 15 mg/m³ total dust TWA: 5 mg/m³ respirable fraction	TWA: 5 mg/m³ TWA: 10 mg/m³ STEL: 10 mg/m³
Aluminum 7429-90-5	TWA: 1 mg/m³ respirable particulate matter	TWA: 10 mg/m³ total dust TWA: 5 mg/m³ respirable dust TWA: 5 mg/m³ Al	TWA: 15 mg/m³ total dust TWA: 5 mg/m³ respirable fraction	TWA: 10 mg/m³ TWA: 5 mg/m³

Chemical Name	Argentina	Brazil	Chile	Venezuela
Graphite 7782-42-5	TWA: 2 mg/m³	-	TWA: 1.75 mg/m³	TWA: 2 mg/m³
Copper 7440-50-8	TWA: 0.2 mg/m³ TWA: 1 mg/m³	-	TWA: 0.18 mg/m³ TWA: 0.88 mg/m³	TWA: 0.2 mg/m³ TWA: 1 mg/m³
Zinc oxide 1314-13-2	TWA: 5 mg/m³ TWA: 10 mg/m³ STEL: 10 mg/m³	-	TWA: 4.4 mg/m³	STEL: 10 mg/m³ TWA: 2 mg/m³ TWA: 10 mg/m³
Aluminum 7429-90-5	TWA: 10 mg/m³ TWA: 5 mg/m³	-	TWA: 8.75 mg/m³ TWA: 4.5 mg/m³ TWA: 4.4 mg/m³	TWA: 10 mg/m³

8.2. Exposure controls

Engineering Controls Showers
Eyewash stations
Ventilation systems.

Personal protective equipment [PPE]

Eye/Face Protection Wear safety glasses with side shields (or goggles).

Skin and Body Protection Wear suitable chemical resistant gloves. The selection of suitable gloves does not only depend on the material, but also on further marks of quality and various manufacturers.

Respiratory Protection If exposure limits are exceeded or irritation is experienced, NIOSH/MSHA approved respiratory protection should be worn. Positive-pressure supplied air respirators may be required for high airborne contaminant concentrations. Respiratory protection must be provided in accordance with current local regulations.

General Hygiene Considerations Use personal protective equipment as required. Handle in accordance with good industrial hygiene and safety practice. When using do not eat, drink or smoke. Wash hands thoroughly after handling. Take off all contaminated clothing and wash it before reuse. Regular cleaning of equipment, work area and clothing is recommended.

Section 9: PHYSICAL AND CHEMICAL PROPERTIES

9.1. Information on basic physical and chemical properties

Physical State	Liquid
Appearance	Paste
Color	Gray
Odor	Petroleum distillates
Odor Threshold	No information available

Property	**Values**	**Remarks • Method**
pH	No information available	
Melting point / freezing point	No information available	
Boiling point / boiling range	No information available	
Flash Point	246 °C / 475 °F	
Evaporation Rate	No information available	
Flammability (solid, gas)	No information available	
Flammability Limit in Air		
Upper flammability limit:	No information available	
Lower flammability limit:	No information available	
Vapor Pressure	No information available	
Vapor Density	No information available	
Relative Density	No information available	
Water Solubility	No information available	
Solubility in Other Solvents		
Partition Coefficient	No information available	
Autoignition Temperature	No information available	
Decomposition Temperature	No information available	

Kinematic Viscosity	No information available
Dynamic Viscosity	No information available
Explosive Properties	No information available
Oxidizing Properties	No information available

9.2. Other information

Softening Point	No information available
Molecular Weight	No information available

Solvent content (%)	No information available
Solid content (%)	No information available
Density	1.190 g/cm³
VOC	No information available

Section 10: STABILITY AND REACTIVITY

10.1. Reactivity

None under normal use conditions.

10.2. Chemical stability

Stable under recommended storage conditions.

10.3. Possibility of hazardous reactions

None under normal processing.

10.4. Conditions to avoid

Extremes of temperature and direct sunlight.

10.5. Incompatible materials

None known based on information supplied.

10.6. Hazardous decomposition products

None known based on information supplied.

Section 11: TOXICOLOGY INFORMATION

11.1. Information on toxicological effects

Product Information	No data available
Inhalation	Based on available data, the classification criteria are not met.
Eye contact	Based on available data, the classification criteria are not met.
Skin Contact	Based on available data, the classification criteria are not met.
Ingestion	Based on available data, the classification criteria are not met.

Component Information

Chemical Name	Oral LD50	Dermal LD50	Inhalation LC50
Zinc oxide 1314-13-2	> 5000 mg/kg (Rat)	LD50 >2000 mg/Kg (Rat) (OECD 402)	LC50 (4h) >5.7 mg/l
Aluminum 7429-90-5	LD50 >10,000 mg/Kg (Rat)(OECD Guideline 401)	-	-

Delayed and immediate effects as well as chronic effects from short and long-term exposure

Symptoms	No information available.
Skin Corrosion/Irritation	No information available.
Serious Eye Damage/Eye Irritation	No information available.
Irritation	No information available.
Corrosivity	No information available.
Sensitization	No information available.
Germ Cell Mutagenicity	No information available.
Reproductive Toxicity	No information available.

Developmental Toxicity	No information available.
Teratogenicity	No information available.
STOT - Single Exposure	No information available.
STOT - Repeated Exposure	No information available.
Chronic Toxicity	No information available.
Target Organ Effects	No information available.
Aspiration hazard	No information available.
Carcinogenicity	This product does not contain any carcinogens or potential carcinogens as listed by ACGIH, OSHA, IARC or NTP at or above 0.1 wt%.

Section 12: ECOLOGICAL INFORMATION

This product contains a chemical which is listed as a severe marine pollutant according to DOT.

12.1. Toxicity

Chemical Name	Algae/aquatic plants	Fish	Toxicity to Microorganisms	Crustacea
Copper 7440-50-8	EC50 96 h 0.031 - 0.054 mg/L (Pseudokirchneriella subcapitata) EC50 72 h 0.0426 - 0.0535 mg/L (Pseudokirchneriella subcapitata)	LC50 96 h = 0.8 mg/L (Cyprinus carpio static)		EC50 48 h = 0.03 mg/L (Daphnia magna Static)
Zinc oxide 1314-13-2	LC 50 (72Hr) 0.136 mg/L	LC50 (96h) =0.7 mg/L Fish (Danio rerio)		LC 50 (48Hr) =0.5 mg/l (Ceriodaphnia dubia)

12.2. Persistence and degradability

No information available.

12.3. Bioaccumulative potential

No information available.

12.4. Mobility in soil

No information available.

Other adverse effects

No information available

Section 13: DISPOSAL CONSIDERATIONS

13.1. Waste treatment methods

Disposal of Wastes	It is the responsibility of the waste generator to determine the toxicity and physical properties of the material generated to determine the proper waste identification and disposal methods in compliance with applicable regulations
Contaminated Packaging	Dispose of in accordance with federal, state and local regulations

Section 14: TRANSPORTATION INFORMATION

Note: The shipping descriptions shown here are for bulk shipments only, and may not apply to shipments made in non-bulk packages (see regulatory definition) The information shown here, may not always agree with the bill of lading shipping description for the material 49 CFR 171.4(c) "Exceptions. Except when all or part of the transportation is by vessel, the requirements of this subchapter specific to marine pollutants do not apply to non-bulk packagings transported by motor vehicle, rail car or aircraft."

DOT

UN/ID No	UN3082
Proper Shipping Name	Environmentally hazardous substance, liquid, n.o.s. (Copper, Zinc oxide), Marine Pollutant
Hazard Class	9
Packing Group	III
Special Provisions	8, 146, 173, 335, IB3, T4, TP1, TP29
Marine Pollutant	This product contains a chemical which is listed as a severe marine pollutant according to DOT.
Description	UN3082, Environmentally hazardous substance, liquid, n.o.s. (Copper, Zinc oxide), 9, III, Marine Pollutant
Emergency Response Guide Number	171

IATA

UN/ID No	UN3082
Proper Shipping Name	Environmentally hazardous substance, liquid, n.o.s. (Copper, Zinc oxide)
Transport hazard class(es)	9
Packing Group	III
ERG Code	9L
Special Provisions	A97, A158, A197
Description	UN3082, Environmentally hazardous substance, liquid, n.o.s. (Copper, Zinc oxide), 9, III

IMDG

UN Number	UN3082
Proper Shipping Name	Environmentally hazardous substance, liquid, n.o.s. (Copper,Zinc oxide), Marine Pollutant
Transport hazard class(es)	9
Packing Group	III
EmS-No	F-A, S-F
Special Provisions	274, 335, 969
Description	UN3082, Environmentally hazardous substance, liquid, n.o.s. (Copper,Zinc oxide), 9, III, Marine Pollutant

Section 15: REGULATORY INFORMATION

Global Inventories

TSCA	Listed
DSL	Listed

Legend:
TSCA - United States Toxic Substances Control Act Section 8(b) Inventory
DSL - Canadian Domestic Substances List
Listed - The components of this product are either listed or exempt from listing on inventory.
Not Listed - One or more components of this product are not listed on inventory.

Canada

This product has been classified in accordance with the hazard criteria of the Controlled Products Regulations (CPR) and the MSDS contains all the information required by the CPR

United States of America

SARA 313
Section 313 of Title III of the Superfund Amendments and Reauthorization Act of 1986 (SARA). This product contains a chemical or chemicals which are subject to the reporting requirements of the Act and Title 40 of the Code of Federal Regulations, Part 372

Chemical Name	CAS No
Copper	7440-50-8
Zinc oxide	1314-13-2
Aluminum	7429-90-5

SARA 311/312 Hazard Categories

Acute Health Hazard	No
Chronic Health Hazard	No
Fire Hazard	No
Sudden release of pressure hazard	No
Reactive Hazard	No

Europe

Restrictions of Use of Hazardous Substances (RoHS) Directive 2011/65/EU
This product does not contain Lead (7439-92-1), Cadmium (7440-43-9), Mercury (7439-97-6), Hexavalent chromium (7440-47-3), Polybrominated biphenyls (PBB), and Polybrominated diphenyl ethers (PBDE) above the regulated limit mentioned in this regulation.

EU-REACH (1907/2006) - Candidate List of Substances of Very High Concern (SVHC) for Authorization in accordance with Article 59
This product does not contain candidate substances of very high concern at a concentration >=0.1% (Regulation (EC) No. 1907/2006 (REACH), Article 59)

Section 16: OTHER INFORMATION

Key or legend to abbreviations and acronyms used in the safety data sheet
No information available

Key Literature References and Sources for Data
No information available

Prepared By	Product Safety & Regulatory Affairs
Revision Date	09-May-2018
Revision Note	SDS sections updated, 1, 5, 6, 8, 9, 12, 14, 16.
Training Advice	No information available
Further information	No information available

Disclaimer
The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text.

End of Safety Data Sheet