

1. IDENTIFICATION

Product Name	Dawn Professional® Heavy Duty Degreaser
Product Code(s)	6-10
Product Identifier	15154367_PROF_NG
Product Type:	Finished Product - Professional Use Only
Recommended Use	Degreaser.
Restrictions on Use	Use only as directed on label.
Details of the supplier of the safety data sheet	Procter & Gamble Professional 1 P&G Plaza Cincinnati, Ohio 45202 Procter & Gamble Inc. P.O. Box 355, Station A Toronto, ON M5W 1C5 1-800-332-7787
E-mail Address	pgsds.im@pg.com
Emergency Telephone	Transportation (24 HR) CHEMTREC - 1-800-424-9300 (U.S./ Canada) or 1-703-527-3887 Mexico toll free in country: 800-681-9531

2. HAZARD IDENTIFICATION

This product is classified under 29CFR 1910.1200(d) and the Canadian Hazardous Products Regulation as follows:.

Hazard Category

Eye Damage / Irritation Category 2A

Signal Word WARNING

Hazard Statements Causes serious eye irritation

Hazard pictograms



Precautionary Statements None

Precautionary Statements - IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if

Response present and easy to do. Continue rinsing
If eye irritation persists: Get medical advice/attention
IF SWALLOWED:
Drink 1 or 2 glasses of water

Precautionary Statements - Storage None

Precautionary Statements - Disposal Dispose of contents/container in accordance with local regulation

Hazards not otherwise classified (HNOC) None

3. COMPOSITION/INFORMATION ON INGREDIENTS

Ingredients are listed according to 29CFR 1910.1200 Appendix D and the Canadian Hazardous Products Regulation

Hazardous ingredients None.

Chemical Name	Synonyms	Trade Secret	CAS-No	Weight-%
2-(2-Butoxyethoxy ethanol) Diethylene glycol monobutyl ether	Butoxydiglycol	Yes	112-34-5	5 - 10
Benzenesulfonic acid, (1-methylethyl)-, sodium salt (1:1)	Benzenesulfonic acid, (1-methylethyl)-, sodium salt (1:1)	Yes	28348-53-0	3 - 7
Tetrasodium ethylenediaminetetraacetate	Glycine, N,N'-1,2-ethanediylbis[N-(carboxymethyl)-, sodium salt (1:4)]	Yes	64-02-8	1 - 5
Sodium carbonate	Carbonic acid sodium salt (1:2)	Yes	497-19-8	0.5 - 1.5
Benzenesulfonic acid, mono-C10-16-alkyl derivs., sodium salts	Benzenesulfonic acid, mono-C10-16-alkyl derivs., sodium salts	Yes	68081-81-2	0.5 - 1.5

Additional information Actual concentrations withheld as trade secret in accordance with Canadian HPR

4. FIRST AID MEASURES

First aid measures for different exposure routes

Eye contact Rinse with plenty of water. Get medical attention immediately if irritation persists.

Skin contact Rinse with plenty of water. Get medical attention if irritation develops and persists.

Ingestion Drink 1 or 2 glasses of water. Do NOT induce vomiting. Get medical attention immediately if symptoms occur.

Inhalation Move to fresh air. If symptoms persist, call a physician.

Most important symptoms/effects, acute and delayed None under normal use conditions.

F. Indication of immediate medical attention and special treatment needed, if necessary

Notes to Physician Treat symptomatically.

5. FIRE-FIGHTING MEASURES

Suitable extinguishing media Dry chemical, CO₂, alcohol-resistant foam or water spray.

Unsuitable Extinguishing Media	None.
Special hazard	None known.
Special protective equipment for fire-fighters	As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.
Specific hazards arising from the chemical	None.

6. ACCIDENTAL RELEASE MEASURES

Personal precautions, protective equipment and emergency procedures

Personal precautions	Use personal protective equipment. Do not get in eyes, on skin, or on clothing.
Advice for emergency responders	Use personal protective equipment as required.

Methods and materials for containment and cleaning up

Methods for containment	Absorb with earth, sand or other non-combustible material and transfer to containers for later disposal.
Methods for cleaning up	Contain spillage, and then collect with non-combustible absorbent material, (e.g. sand, earth, diatomaceous earth, vermiculite) and place in container for disposal according to local / national regulations (see section 13).

7. HANDLING AND STORAGE

Precautions for safe handling

Advice on safe handling	Use personal protective equipment as required. Keep container closed when not in use. Never return spills in original containers for re-use. Keep out of the reach of children.
--------------------------------	---

Conditions for safe storage, including any incompatibilities

Storage Conditions	Keep containers tightly closed in a dry, cool and well-ventilated place.
Incompatible products	None known.

8. EXPOSURE CONTROLS/PERSONAL PROTECTION

Control parameters

Exposure Guidelines

Chemical Name	CAS-No	ACGIH TLV	OSHA PEL	Mexico PEL
2-(2-Butoxyethoxy ethanol) Diethylene glycol monobutyl ether	112-34-5	TWA: 10 ppm inhalable fraction and vapor		

Chemical Name	CAS-No	Alberta	Quebec	Ontario TWAEV	British Columbia
2-(2-Butoxyethoxy ethanol) Diethylene glycol monobutyl ether	112-34-5			TWA: 10 ppm	

No relevant exposure guidelines for other ingredients

Exposure controls

Engineering Measures	Distribution, Workplace and Household Settings: Ensure adequate ventilation
-----------------------------	---

Product Manufacturing Plant (needed at Product-Producing Plant ONLY):
Where reasonably practicable this should be achieved by the use of local exhaust ventilation and good general extraction

Personal Protective Equipment

Eye Protection

Distribution, Workplace and Household Settings:
No special protective equipment required

Product Manufacturing Plant (needed at Product-Producing Plant ONLY):
Use appropriate eye protection

Hand Protection

Distribution, Workplace and Household Settings:
No special protective equipment required

Product Manufacturing Plant (needed at Product-Producing Plant ONLY):
Protective gloves

Skin and Body Protection

Distribution, Workplace and Household Settings:
No special protective equipment required

Product Manufacturing Plant (needed at Product-Producing Plant ONLY):
Wear suitable protective clothing

Respiratory Protection

Distribution, Workplace and Household Settings:
No special protective equipment required

Product Manufacturing Plant (needed at Product-Producing Plant ONLY):
In case of inadequate ventilation wear respiratory protection

9. PHYSICAL AND CHEMICAL PROPERTIES

Physical State @20°C	Liquid	
Appearance	purple	
Odor	Scented	
Odor threshold	No information available	
<u>Property</u>	<u>Values</u>	<u>Note</u>
pH value	10.4	
Melting Point / Freezing Point	Not available	Not available. This property is not relevant for the safety and classification of this product
Boiling point / boiling range	No information available	
Flash point	> 93.3 °C / > 200 °F	.
Evaporation rate	Not available	Not available. This property is not relevant for the safety and classification of this product
Flammability (solid, gas)	Not available	Not applicable. This property is not relevant for liquid product forms
Flammability Limits in Air		
Upper flammability limit	No information available	
Lower Flammability Limit	No information available	
Vapor pressure	No information available	Not available. This property is not relevant for the safety and classification of this product
Vapor density	Not available	Not available. This property is not relevant for the safety and classification of this product
Relative density	1.12	
Water solubility	100%	
Partition coefficient: n-octanol/water	No information available	Not available. This property is not relevant for

Autoignition temperature	Not available	the safety and classification of this product Not available. This property is not relevant for the safety and classification of this product .
Decomposition temperature	Not available	Not available. This property is not relevant for the safety and classification of this product .
Viscosity	No information available	
VOC Content (%)	Products comply with US state and federal regulations for VOC content in consumer products.	

10. STABILITY AND REACTIVITY

Reactivity	None under normal use conditions.
Stability	Stable under normal conditions.
Hazardous polymerization	Hazardous polymerization does not occur.
Hazardous Reactions	None under normal processing.
Conditions to Avoid	None under normal processing.
Incompatible materials	None in particular.

Hazardous Decomposition Products None under normal use conditions.

11. TOXICOLOGICAL INFORMATION

Product Information

Information on likely routes of exposure

Inhalation	No known effect.
Skin contact	No known effect.
Ingestion	No known effect.
Eye contact	Causes serious eye irritation.

Delayed and immediate effects as well as chronic effects from short and long-term exposure

Acute toxicity	No known effect.
Skin corrosion/irritation	No known effect.
Serious eye damage/eye irritation	Causes serious eye irritation.
Skin sensitization	No known effect.
Respiratory sensitization	No known effect.
Germ cell mutagenicity	No known effect.
Neurological Effects	No known effect.
Reproductive toxicity	No known effect.
Developmental toxicity	No known effect.
Teratogenicity	No known effect.
STOT - single exposure	No known effect.
STOT - repeated exposure	No known effect.
Target Organ Effects	No known effect.
Aspiration hazard	No known effect.
Carcinogenicity	No known effect.

Component Information

Chemical Name	CAS-No	Oral LD50	Dermal LD50	Inhalation LC50
2-(2-Butoxyethoxy ethanol) Diethylene glycol monobutyl ether	112-34-5	2410 mg/kg bw (Similar to OECD 401; mouse)	2764 mg/kg bw (Similar to OECD 402; rabbit)	> 14.48 mg/L (Guideline not indicated; rat)
Benzenesulfonic acid, (1-methylethyl)-, sodium salt (1:1)	28348-53-0	> 7000 mg/kg bw (OECD 401)	> 2000 mg/kg bw (//OECD 402)	> 6.41 mg/L air
Tetrasodium ethylenediaminetetraacetate	64-02-8	> 1780 mg/kg bw	-	-
Sodium carbonate	497-19-8	2800 mg/kg bw	> 2000 mg/kg bw (US EPA	-

			16 CFR 1500.40)	
--	--	--	-----------------	--

12. ECOLOGICAL INFORMATION

Ecotoxicity

The product is not expected to be hazardous to the environment.

Persistence and degradability	No information available.
Bioaccumulative potential	No information available.
Mobility	No information available.
Other adverse effects	No information available.

13. DISPOSAL CONSIDERATIONS

Waste treatment methods

Waste from Residues/Unused Products	Disposal should be in accordance with applicable regional, national and local laws and regulations.
Contaminated packaging	Disposal should be in accordance with applicable regional, national and local laws and regulations.
California Hazardous Waste Codes (non-household setting)	331

14. TRANSPORT INFORMATION

<u>DOT</u>	Not regulated
<u>IMDG</u>	Not regulated
<u>IATA</u>	Not regulated

15. REGULATORY INFORMATION

U.S. Federal Regulations

SARA 313

Section 313 of Title III of the Superfund Amendments and Reauthorization Act of 1986 (SARA). This product contains a chemical or chemicals which are subject to the reporting requirements of the Act and Title 40 of the Code of Federal Regulations, Part 372:

CERCLA

This material, as supplied, does not contain any substances regulated as hazardous substances under the Comprehensive Environmental Response Compensation and Liability Act (CERCLA) (40 CFR 302) or the Superfund Amendments and Reauthorization Act (SARA) (40 CFR 355). There may be specific reporting requirements at the local, regional, or state level pertaining to releases of this material.

Clean Air Act, Section 112 Hazardous Air Pollutants (HAPs) (see 40 CFR 61)

This product contains the following substance(s) which are either listed as hazardous air pollutants (HAPS) or VOC's per the Clean Air Act:

Clean Water Act

This product does not contain any substances regulated as pollutants pursuant to the Clean Water Act (40 CFR 122.21 and 40 CFR 122.42).

California Proposition 65

This product is not subject to warning labeling under California Proposition 65.

U.S. State Regulations (RTK)

.

Chemical Name	CAS-No	Pennsylvania
2-Aminoethanol	141-43-5	X

International Inventories

United States

All intentionally-added components of this product(s) are listed on the US TSCA Inventory.

Canada

This product is in compliance with CEPA for import by P&G.

Legend

United States Toxic Substances Control Act Section 8(b) Inventory (TSCA)

CEPA - Canadian Environmental Protection Act

16. OTHER INFORMATION

HMIS Ratings

Health hazard	-
Flammability	1
Physical hazard	0

NFPA Ratings

Health hazard	2
Flammability	1
Instability	0

Issuing Date: 09-Jan-2015

Revision Date: 14-May-2018

Disclaimer.

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text

End of SDS