

# NEER™ Zinc Bushed Conduit Nipples

NEC/CEC:  
Listed for Ordinary Locations

## Applications

- Use through knockout to connect box to conduit coupling.
- Use with a locknut to connect two boxes side by side or back to back.
- Use with a locknut to connect fixture housings to continuous runs.

## Features

- Male hub threads — NPS.
- Available with insulated throat.

## Material/Finish

- Zinc diecast

## NEC/CEC Certifications and Compliances

- UL Standard: 514B
- UL Listed: E-14814
- CSA Standard: C22.2 No. 18
- CSA Certified: 065178
- NEMA: FB-1



CNI-100

Trade Size (Inches)	Dimensions in Millimeters (Inches)			Catalog Number
	Maximum Diameter	Body Length		
1/2	23.9 (0.94)	15.0 (0.59)		<b>CNN-100</b>
3/4	30.2 (1.19)	18.3 (0.72)		<b>CNN-200</b>
1	35.1 (1.38)	21.6 (0.85)		<b>CNN-300</b>
1-1/4	44.2 (1.74)	22.1 (0.87)		<b>CNN-400</b>
1-1/2	53.8 (2.12)	22.9 (0.90)		<b>CNN-500</b>
2	64.8 (2.55)	29.2 (1.15)		<b>CNN-600</b>
2-1/2	81.5 (3.21)	36.3 (1.43)		<b>CNN-700</b>
3	96.5 (3.80)	36.3 (1.43)		<b>CNN-800</b>
3-1/2	108.5 (4.27)	36.3 (1.43)		<b>CNN-900</b>
4	121.7 (4.79)	36.3 (1.43)		<b>CNN-1000</b>

Trade Size (Inches)	Dimensions in Millimeters (Inches)			Catalog Number
	Maximum Diameter	Body Length		
1/2	23.9 (0.94)	17.0 (0.67)		<b>CNI-100</b>
3/4	30.2 (1.19)	20.3 (0.80)		<b>CNI-200</b>
1	35.1 (1.38)	23.6 (0.93)		<b>CNI-300</b>
1-1/4	44.2 (1.74)	24.1 (0.95)		<b>CNI-400</b>
1-1/2	53.8 (2.12)	24.9 (0.98)		<b>CNI-500</b>
2	64.8 (2.55)	31.2 (1.23)		<b>CNI-600</b>