

JET

DO MORE™

JWDP-10
10" BENCHTOP DRILL PRESS

DRILLING PERFORMANCE THAT EARNS ITS SPACE.

OVERVIEW

The JET 10" Benchtop Drill Press gives woodworkers, makers, and hands-on professionals dependable drilling performance in a compact, easy-to-place format. Built for shops, garages, classrooms, and jobsites where space and flexibility matter, it combines a stable benchtop design with the capacity needed for everyday drilling tasks. Easy to move, simple to use, and backed by JET's 5-year warranty, it delivers practical performance and long-term value without taking over the workspace.

IDEAL FOR

- Serious Hobbyists
- Small-Shop Craftsmen
- Finish Carpenters
- Vocational & Trade Schools

THE JET ADVANTAGES

- **Portable Drilling Without Restraints.** Built for flexibility in the shop, garage, or jobsite, the JET 10" Benchtop Drill Press is easy to move, reposition, and power almost anywhere. Its bench-friendly design supports one-person handling, while the stable base delivers confident drilling performance wherever work happens.
- **Big Capacity In A Smaller Space.** The compact footprint helps save valuable bench space without sacrificing capability. Its vertical design maximizes working area, while the 10-inch swing and adjustable worktable provide the versatility needed for everyday drilling applications in smaller shops and shared workspaces.
- **Performance At Value.** The JET 10" Benchtop Drill Press delivers dependable drilling performance without unnecessary complexity or added cost. A durable build, versatile 5-speed range, and 5-year warranty provide long-term value users can rely on.

SEE IT IN ACTION.
VISIT JETTOOLS.COM TO LEARN MORE.

INDUSTRY-LEADING SERVICE & SUPPORT

5 YEAR WARRANTY

JWDP-10
10" BENCHTOP DRILL PRESS



STOCK NO.	JT1-3162
Model No.	JWDP-10
HP	1/3 HP
Phase	1PH
Voltage	120V
Throat Capacity	10"
Chuck Size	JT33
Drilling Capacity	1/16" – 1/2"
Column Distance to Spindle	5"
Number of Spindle Speeds	5
Speed	630-3,330 RPM
Spindle Travel	2"
Spindle Distance to Base	17-5/16"
Max Spindle Distance to Table	13-3/8"
Table Size	7-1/2" x 6-1/2"
Table Tilt	±45°
Table Travel	10-7/16"
Table Weight Capacity	44 lbs.
Base Dimensions	13" x 8"
Net Weight	48.5 lbs.
Gross Weight	52 lbs.
Overall Dimensions	11" x 19" x 28-3/4"



DEPTH STOP SYSTEM
Set repeatable drilling depths for consistent results.



ADJUSTABLE WORKTABLE
Tilts and adjusts for angled drilling and material support.



MULTI-SPEED CONTROL
5 speed range from 630 to 3,300 RPM supports optimized drilling.



INTEGRATED WORK LIGHT & LASERS
Improves visibility for precision drilling tasks.



KEYED CHUCK
Secure bit retention for accurate and stable drilling.

SEE IT IN ACTION.
VISIT JETTOOLS.COM TO LEARN MORE.

JET
DO MORE™