

SAFETY DATA SHEET

Issuing Date No data available

Revision Date 01-Jan-2018

Revision Number 4

1. IDENTIFICATION OF THE SUBSTANCE/PREPARATION AND OF THE COMPANY/UNDERTAKING

Product identifier 515-6050

Product Name F-26 Grease Stick Polishing Lubricant

Other means of identification

Synonyms None

Recommended use of the chemical and restrictions on use

Recommended Use Abrasive

Uses advised against No information available

Details of the supplier of the safety data sheet

Supplier Name Formax Mfg. Corporation
Supplier Address 168 Wealthy St. S.W.
Grand Rapids
MI
49503
US

Supplier Phone Number Phone:1-616-456-5458
Fax:1-616-456-7507
Contact Phone1-616-456-7507

Supplier Email sales@formaxmfg.com

Emergency telephone number

2. HAZARDS IDENTIFICATION

Classification

This chemical is not considered hazardous by the 2012 OSHA Hazard Communication Standard (29 CFR 1910.1200)

GHS Label elements, including precautionary statements

Emergency Overview

The product contains no substances which at their given concentration, are considered to be hazardous to health

Appearance Brown	Physical State Solid Gel Consistency	Odor Mild
-------------------------	---	------------------

Precautionary Statements - Prevention
Obtain special instructions before use

Precautionary Statements - Response
None

Precautionary Statements - Storage
None

Precautionary Statements - Disposal
None

Hazards not otherwise classified (HNOC)

Not applicable

Unknown Toxicity
None

Other information

May cause slight eye irritation

Interactions with Other Chemicals
No information available.

3. COMPOSITION/INFORMATION ON INGREDIENTS

The product contains no substance which at their given concentration, are considered to be hazardous to health.

4. FIRST AID MEASURES

First aid measures

Eye Contact	Rinse thoroughly with plenty of water, also under the eyelids. If symptoms persist, call a physician.
Skin Contact	Wash with soap and water.
Inhalation	Remove to fresh air.
Ingestion	Rinse mouth immediately and drink plenty of water. Never give anything by mouth to an unconscious person.

Most important symptoms and effects, both acute and delayed

Most Important Symptoms and Effects No information available.

Indication of any immediate medical attention and special treatment needed

Notes to Physician Treat symptomatically.

5. FIRE-FIGHTING MEASURES

Suitable Extinguishing Media

Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.

Unsuitable extinguishing media

CAUTION: Use of water spray when fighting fire may be inefficient.

Specific Hazards Arising from the Chemical

No information available.

Hazardous Combustion Products

Carbon oxides.

Explosion Data

Sensitivity to Mechanical Impact No.

Sensitivity to Static Discharge No.

Protective equipment and precautions for firefighters

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.

6. ACCIDENTAL RELEASE MEASURES

Personal precautions, protective equipment and emergency procedures

Personal Precautions Avoid contact with eyes.

Environmental Precautions

Environmental Precautions Refer to protective measures listed in Sections 7 and 8.

Methods and material for containment and cleaning up

Methods for Containment Prevent further leakage or spillage if safe to do so.

Methods for cleaning up Pick up and transfer to properly labeled containers.

7. HANDLING AND STORAGE

Precautions for safe handling

Handling Handle in accordance with good industrial hygiene and safety practice. Avoid contact with skin, eyes or clothing.

Conditions for safe storage, including any incompatibilities

Storage Keep container tightly closed.

Incompatible Products None known based on information supplied.

8. EXPOSURE CONTROLS/PERSONAL PROTECTION

Control parameters

Exposure Guidelines This product, as supplied, does not contain any hazardous materials with occupational exposure limits established by the region specific regulatory bodies

Appropriate engineering controls

Engineering Measures Showers
Eyewash stations
Ventilation systems

Individual protection measures, such as personal protective equipment

Eye/Face Protection For buffing machines wear safety glasses and/or face shield helmets. See OSH 29 CFR 1910.122 (Safety Glasses).

Skin and Body Protection Protective work clothing, heavy duty gloves, body apron or belly pads, safety shoes as needed

Respiratory Protection Respiratory protection (specify type): OSHA 24 CFR/134 NIOSH/MSHA Approved respirators for particulates from buffing debris. If exposure limits are exceeded or irritation is experienced, ventilation and evacuation may be required. If exposure limits are exceeded or irritation is experienced, ventilation and evacuation may be required.

Hygiene Measures Handle in accordance with good industrial hygiene and safety practice.

9. PHYSICAL AND CHEMICAL PROPERTIES

Physical and Chemical Properties

Physical State	Solid Gel Consistency	Odor	Mild
Appearance	Soft Grease	Odor Threshold	No information available
Color	Brown		

<u>Property</u>	<u>Values</u>	<u>Remarks</u>	<u>Method</u>
pH	No data available	None known	
Melting / freezing point	125F/145F	None known	
Boiling point / boiling range	Over 250F	None known	

Flash Point	Over 350F	None known
Evaporation Rate	No data available	None known
Flammability (solid, gas)	No data available	None known
Flammability Limit in Air		
Upper flammability limit	No data available	
Lower flammability limit	No data available	
Vapor pressure	No data available	None known
Vapor density	(Air=1) greater than 5	None known
Specific Gravity	0.85 typical	None known
Water Solubility	Emulsifies and disperses	None known
Solubility in other solvents	Alkaline Cleaner/Chlorinated Solvents	None known
Partition coefficient: n-octanol/water	No data available	None known
Autoignition temperature	No data available	None known
Decomposition temperature	No data available	None known
Kinematic viscosity	No data available	None known
Dynamic viscosity	No data available	None known
Explosive properties	No data available	
Oxidizing Properties	No data available	

Other Information

Softening Point	No data available
VOC Content (%)	None
Particle Size	No data available
Particle Size Distribution	

10. STABILITY AND REACTIVITY

Reactivity

No data available.

Chemical stability

Stable under recommended storage conditions.

Possibility of Hazardous Reactions

None under normal processing.

Hazardous Polymerization

Hazardous polymerization does not occur.

Conditions to avoid

None known based on information supplied.

Incompatible materials

None known based on information supplied.

Hazardous Decomposition Products

Carbon oxides.

11. TOXICOLOGICAL INFORMATION

Information on likely routes of exposure**Product Information**

Specific test data for the substance or mixture is not available.

Inhalation	Specific test data for the substance or mixture is not available.
Eye Contact	Specific test data for the substance or mixture is not available.
Skin Contact	Specific test data for the substance or mixture is not available.
Ingestion	Specific test data for the substance or mixture is not available.

Component Information**Information on toxicological effects**

Symptoms No information available.

Delayed and immediate effects as well as chronic effects from short and long-term exposure

Sensitization No information available.

Mutagenic Effects No information available.

Carcinogenicity Contains no ingredient listed as a carcinogen.

Reproductive Toxicity No information available.

STOT - single exposure No information available.

STOT - repeated exposure No information available.

Chronic Toxicity No known effect based on information supplied.

Target Organ Effects None known.

Aspiration Hazard No information available.

Numerical measures of toxicity Product Information

The following values are calculated based on chapter 3.1 of the GHS document
Not applicable

12. ECOLOGICAL INFORMATION

Ecotoxicity

The environmental impact of this product has not been fully investigated.

Persistence and Degradability

No information available.

Bioaccumulation

No information available

Other adverse effects

No information available.

13. DISPOSAL CONSIDERATIONS

Waste treatment methods

Disposal methods

This material, as supplied, is not a hazardous waste according to Federal regulations (40 CFR 261). This material could become a hazardous waste if it is mixed with or otherwise comes in contact with a hazardous waste, if chemical additions are made to this material, or if the material is processed or otherwise altered. Consult 40 CFR 261 to determine whether the altered material is a hazardous waste. Consult the appropriate state, regional, or local regulations for additional requirements.

Contaminated Packaging

Dispose of contents/containers in accordance with local regulations.

14. TRANSPORT INFORMATION

DOT NOT REGULATED

TDG Not regulated

MEX Not regulated

ICAO Not regulated

IATA Not regulated

IMDG/IMO Not regulated
 Proper Shipping Name Non Regulated
 Hazard Class N/A

RID Not regulated

ADR Not regulated

ADN Not regulated

15. REGULATORY INFORMATION

International Inventories

TSCA Complies
 DSL All components are listed either on the DSL or NDSL.

TSCA - United States Toxic Substances Control Act Section 8(b) Inventory
 DSL/NDSL - Canadian Domestic Substances List/Non-Domestic Substances List

US Federal Regulations

SARA 313

Section 313 of Title III of the Superfund Amendments and Reauthorization Act of 1986 (SARA). This product does not contain any chemicals which are subject to the reporting requirements of the Act and Title 40 of the Code of Federal Regulations, Part 372

SARA 311/312 Hazard Categories

Acute Health Hazard	No
Chronic Health Hazard	No
Fire Hazard	No
Sudden release of pressure hazard	No
Reactive Hazard	No

CWA (Clean Water Act)

This product does not contain any substances regulated as pollutants pursuant to the Clean Water Act (40 CFR 122.21 and 40 CFR 122.42)

CERCLA

This material, as supplied, does not contain any substances regulated as hazardous substances under the Comprehensive Environmental Response Compensation and Liability Act (CERCLA) (40 CFR 302) or the Superfund Amendments and Reauthorization Act (SARA) (40 CFR 355). There may be specific reporting requirements at the local, regional, or state level pertaining to releases of this material

US State Regulations

California Proposition 65

This product does not contain any Proposition 65 chemicals.

U.S. State Right-to-Know Regulations

. This product does not contain any substances regulated by state right-to-know regulations

International Regulations

Canada
 WHMIS Hazard Class
 Non-controlled

16. OTHER INFORMATION

NFPA	Health Hazards	1	Flammability	0	Instability	0	Physical and Chemical Hazards - Personal Protection X
HMIS	Health Hazards	1	Flammability	0	Physical Hazard	0	

Prepared By Formax Mfg. Corporation
168 Wealthy St. S.W.
Grand Rapids, MI 49503
1-616-456-5458

Revision Date 01-Jan-2018

Revision Note No information available

Disclaimer

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text. The information and recommendations set forth herein are taken from sources believed to be accurate as of the date hereof; however, Formax Mfg. makes no warranty with respect to the accuracy of the information or the suitability of the recommendation, and assumes no liability to any user thereof.

End of Safety Data Sheet