

SAFETY DATA SHEET

ZEP FOAMING GLASS CLEANER 20N19 12CT

Version 6.1

Revision Date 10/01/2023

Print Date 01/16/2026

SECTION 1. PRODUCT AND COMPANY IDENTIFICATION

Material name : ZEP FOAMING GLASS CLEANER 20N19 12CT

Material number : ZUFGC19

Manufacturer or supplier's details

Company : Zep Inc.

Address : 350 Joe Frank Harris Parkway, SE
Emerson, GA 30137

Telephone : Compliance Services - 877-428-9937

Emergency telephone numbers

For SDS Information : Compliance Services - 877-428-9937

For a Medical Emergency : 877-541-2016 Toll Free - All Calls Recorded

For a Transportation
Emergency : CHEMTREC: 800-424-9300 - All Calls Recorded.
In the District of Columbia 202-483-7616

Recommended use of the chemical and restrictions on use

SECTION 2. HAZARDS IDENTIFICATION

Emergency Overview

Appearance	Aerosol containing a liquefied gas
Colour	colourless
Odour	pleasant

GHS Classification

Gases under pressure : Liquefied gas

GHS label elements

Hazard pictograms :



Gas cylinder

Signal word : Warning

Hazard statements : H280 Contains gas under pressure; may explode if heated.

Precautionary statements : **Storage:**
P410 + P403 Protect from sunlight. Store in a well-ventilated place.

SECTION 3. COMPOSITION/INFORMATION ON INGREDIENTS

SAFETY DATA SHEET

ZEP FOAMING GLASS CLEANER 20N19 12CT

Version 6.1

Revision Date 10/01/2023

Print Date 01/16/2026

Substance / Mixture : Mixture

Hazardous components

Chemical name	CAS-No.	Concentration [%]
ethanol	64-17-5	≥ 3 - < 5
butane	106-97-8	≥ 1 - < 3
propan-2-ol	67-63-0	≥ 1 - < 3
propane	74-98-6	≥ 1 - < 3

The exact percentages of disclosed substances are withheld as trade secrets.

SECTION 4. FIRST AID MEASURES

- General advice : Do not leave the victim unattended.
Move out of dangerous area.
Show this safety data sheet to the doctor in attendance.
- If inhaled : If unconscious, place in recovery position and seek medical advice.
Consult a physician after significant exposure.
- In case of skin contact : If skin irritation persists, call a physician.
Wash off immediately with plenty of water for at least 15 minutes.
If on clothes, remove clothes.
- In case of eye contact : Remove contact lenses.
Protect unharmed eye.
Keep eye wide open while rinsing.
If eye irritation persists, consult a specialist.
Rinse immediately with plenty of water for at least 15 minutes.
- If swallowed : Keep respiratory tract clear.
Never give anything by mouth to an unconscious person.
If symptoms persist, call a physician.
DO NOT induce vomiting unless directed to do so by a physician or poison control center.
Take victim immediately to hospital.
- Most important symptoms and effects, both acute and delayed : Effects are immediate and delayed.
Effects are dependent on exposure (dose, concentration, contact time).
Overexposure may cause mild eye or skin irritation.
Review section 2 of SDS to see all potential hazards.
- Notes to physician : Treat symptomatically. Symptoms may be delayed.

SECTION 5. FIREFIGHTING MEASURES

- Suitable extinguishing media : Use water spray, alcohol-resistant foam, dry chemical or carbon dioxide.

SAFETY DATA SHEET

ZEP FOAMING GLASS CLEANER 20N19 12CT

Version 6.1

Revision Date 10/01/2023

Print Date 01/16/2026

Unsuitable extinguishing media	: High volume water jet
Specific hazards during firefighting	: Do not allow run-off from fire fighting to enter drains or water courses.
Hazardous combustion products	: Carbon dioxide (CO ₂) Carbon monoxide Smoke
Specific extinguishing methods	: Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.
Further information	: Standard procedure for chemical fires. Collect contaminated fire extinguishing water separately. This must not be discharged into drains. Fire residues and contaminated fire extinguishing water must be disposed of in accordance with local regulations. For safety reasons in case of fire, cans should be stored separately in closed containments. Use a water spray to cool fully closed containers.
Special protective equipment for firefighters	: Wear self-contained breathing apparatus for firefighting if necessary.

SECTION 6. ACCIDENTAL RELEASE MEASURES

Personal precautions, protective equipment and emergency procedures	: Use personal protective equipment. Ensure adequate ventilation. Remove all sources of ignition. Evacuate personnel to safe areas. Beware of vapours accumulating to form explosive concentrations. Vapours can accumulate in low areas.
Environmental precautions	: Prevent further leakage or spillage if safe to do so. Prevent product from entering drains. If the product contaminates rivers and lakes or drains, inform respective authorities.
Methods and materials for containment and cleaning up	: Soak up with inert absorbent material (e.g. sand, silica gel, acid binder, universal binder, sawdust). Sweep up or vacuum up spillage and collect in suitable container for disposal.

SECTION 7. HANDLING AND STORAGE

Advice on safe handling	: Avoid exposure - obtain special instructions before use. Avoid contact with skin and eyes. For personal protection see section 8. Smoking, eating and drinking should be prohibited in the application area. Do not breathe vapours or spray mist. Take precautionary measures against static discharges.
-------------------------	--

SAFETY DATA SHEET

ZEP FOAMING GLASS CLEANER 20N19 12CT

Version 6.1

Revision Date 10/01/2023

Print Date 01/16/2026

Provide sufficient air exchange and/or exhaust in work rooms.
Dispose of rinse water in accordance with local and national regulations.

Always replace cap after use.

Conditions for safe storage : BEWARE: Aerosol is pressurized. Keep away from direct sun exposure and temperatures over 50 °C. Do not open by force or throw into fire even after use. Do not spray on flames or red-hot objects.
Keep container tightly closed in a dry and well-ventilated place.
Observe label precautions.
Electrical installations / working materials must comply with the technological safety standards.
Keep in a dry, cool and well-ventilated place.

Materials to avoid : Oxidizing agents

SECTION 8. EXPOSURE CONTROLS/PERSONAL PROTECTION

Components with workplace control parameters

Components	CAS-No.	Value type (Form of exposure)	Control parameters / Permissible concentration	Basis
ethanol	64-17-5	TWA	1,000 ppm	ACGIH
		TWA	1,000 ppm 1,900 mg/m3	NIOSH REL
		TWA	1,000 ppm 1,900 mg/m3	OSHA Z-1
		TWA	1,000 ppm 1,900 mg/m3	OSHA P0
		STEL	1,000 ppm	ACGIH
		PEL	1,000 ppm 1,900 mg/m3	CAL PEL
butane	106-97-8	TWA	800 ppm 1,900 mg/m3	NIOSH REL
		TWA	800 ppm 1,900 mg/m3	OSHA P0
		PEL	800 ppm 1,900 mg/m3	CAL PEL
		STEL	1,000 ppm	ACGIH
propan-2-ol	67-63-0	TWA	200 ppm	ACGIH
		STEL	400 ppm	ACGIH
		TWA	400 ppm 980 mg/m3	NIOSH REL
		ST	500 ppm 1,225 mg/m3	NIOSH REL
		TWA	400 ppm 980 mg/m3	OSHA Z-1
		TWA	400 ppm 980 mg/m3	OSHA P0
		STEL	500 ppm 1,225 mg/m3	OSHA P0

SAFETY DATA SHEET**ZEP FOAMING GLASS CLEANER 20N19 12CT**

Version 6.1

Revision Date 10/01/2023

Print Date 01/16/2026

		PEL	400 ppm 980 mg/m ³	CAL PEL
		STEL	500 ppm 1,225 mg/m ³	CAL PEL
propane	74-98-6	TWA	1,000 ppm 1,800 mg/m ³	NIOSH REL
		TWA	1,000 ppm 1,800 mg/m ³	OSHA Z-1
		TWA	1,000 ppm 1,800 mg/m ³	OSHA P0
		PEL	1,000 ppm 1,800 mg/m ³	CAL PEL

Biological occupational exposure limits

Component	CAS-No.	Control parameters	Biological specimen	Sampling time	Permissible concentration	Basis
PROPAN-2-OL	67-63-0	Acetone	Urine	End of shift at end of workweek	40 mg/l	ACGIH BEI

Engineering measures : effective ventilation in all processing areas

Personal protective equipment

Respiratory protection : Use respiratory protection unless adequate local exhaust ventilation is provided or exposure assessment demonstrates that exposures are within recommended exposure guidelines.

Hand protection

Material

Remarks

: Protective gloves

: The suitability for a specific workplace should be discussed with the producers of the protective gloves.

Eye protection

: Access to clean water to rinse eyes must be available, options include: eye wash stations or showers, or eye wash bottles with pure water.

Safety glasses

Skin and body protection

: Impervious clothing

Choose body protection according to the amount and concentration of the dangerous substance at the work place.

Hygiene measures

: Wash hands before breaks and at the end of workday.

When using do not eat, drink or smoke.

When using do not smoke.

SECTION 9. PHYSICAL AND CHEMICAL PROPERTIES

Appearance

: Aerosol containing a liquefied gas

SAFETY DATA SHEET

ZEP FOAMING GLASS CLEANER 20N19 12CT

Version 6.1

Revision Date 10/01/2023

Print Date 01/16/2026

Colour	: colourless
Odour	: pleasant
Odour Threshold	: No data available
pH	: 10 - 11
Melting point/freezing point	: No data available
Boiling point	: No data available
Flash point	: No data available
Evaporation rate	: No data available
Upper explosion limit	: No data available
Lower explosion limit	: No data available
Vapour pressure	: No data available
Relative vapour density	: No data available
Density	: 0.986 g/cm ³
Solubility(ies)	
Water solubility	: soluble in cold water, soluble in hot water
Partition coefficient: n-octanol/water	: No data available
Auto-ignition temperature	: not determined
Thermal decomposition	: No data available
Viscosity	
Viscosity, kinematic	: No data available

SECTION 10. STABILITY AND REACTIVITY

Reactivity	: Stable
Chemical stability	: Stable under normal conditions.
Possibility of hazardous reactions	: No decomposition if stored and applied as directed.
Conditions to avoid	: Heat, flames and sparks. Extremes of temperature and direct sunlight.
Incompatible materials	: Oxidizing agents
Hazardous decomposition products	: Carbon oxides

SECTION 11. TOXICOLOGICAL INFORMATION

SAFETY DATA SHEET

ZEP FOAMING GLASS CLEANER 20N19 12CT

Version 6.1

Revision Date 10/01/2023

Print Date 01/16/2026

Potential Health Effects

Aggravated Medical Condition : None known.

Symptoms of Overexposure : Effects are immediate and delayed.
Effects are dependent on exposure (dose, concentration, contact time).
Overexposure may cause mild eye or skin irritation.
Review section 2 of SDS to see all potential hazards.
Treat symptomatically. Symptoms may be delayed.

Carcinogenicity:

IARC No component of this product present at levels greater than or equal to 0.1% is identified as probable, possible or confirmed human carcinogen by IARC.

ACGIH Confirmed animal carcinogen with unknown relevance to humans
ethanol 64-17-5
2-butoxyethanol 111-76-2

OSHA No component of this product present at levels greater than or equal to 0.1% is on OSHA's list of regulated carcinogens.

NTP No component of this product present at levels greater than or equal to 0.1% is identified as a known or anticipated carcinogen by NTP.

Acute toxicity

Product:

Acute oral toxicity : Acute toxicity estimate : > 5,000 mg/kg
Method: Calculation method

Components:

ethanol:

Acute oral toxicity : LD50 Oral Rat: 7,060 mg/kg

Acute inhalation toxicity : LC50 Rat: 124.7 mg/l
Exposure time: 4 h
Test atmosphere: vapour

propan-2-ol:

Acute oral toxicity : LD50 Oral Rat: 4,396 mg/kg
Method: Calculation method

Skin corrosion/irritation

No data available

Serious eye damage/eye irritation

No data available

Respiratory or skin sensitisation

No data available

SAFETY DATA SHEET

ZEP FOAMING GLASS CLEANER 20N19 12CT

Version 6.1

Revision Date 10/01/2023

Print Date 01/16/2026

Germ cell mutagenicity

No data available

Carcinogenicity

No data available

Reproductive toxicity

No data available

STOT - single exposure

No data available

STOT - repeated exposure

No data available

Aspiration toxicity

No data available

Further information

Product:

Remarks: No data available

SECTION 12. ECOLOGICAL INFORMATION

Ecotoxicity

No data available

Persistence and degradability

No data available

Bioaccumulative potential

Product:

Partition coefficient: n-octanol/water : Remarks: No data available

Components:

ethanol :

Partition coefficient: n-octanol/water : Remarks: No data available

butane :

Partition coefficient: n-octanol/water : Pow: 2.89

propan-2-ol :

Partition coefficient: n-octanol/water : log Pow: 0.05

Mobility in soil

No data available

SAFETY DATA SHEET

ZEP FOAMING GLASS CLEANER 20N19 12CT

Version 6.1

Revision Date 10/01/2023

Print Date 01/16/2026

Other adverse effects

No data available

Product:

Regulation

40 CFR Protection of Environment; Part 82 Protection of Stratospheric Ozone - CAA Section 602 Class I Substances

Remarks

This product neither contains, nor was manufactured with a Class I or Class II ODS as defined by the U.S. Clean Air Act Section 602 (40 CFR 82, Subpt. A, App.A + B).

Additional ecological information

: No data available

SECTION 13. DISPOSAL CONSIDERATIONS

Disposal methods

Waste from residues

: Do not dispose of waste into sewer.
Do not contaminate ponds, waterways or ditches with chemical or used container.
Dispose of in accordance with local regulations.

Contaminated packaging

: Empty remaining contents.
Dispose of as unused product.
Do not re-use empty containers.
Do not burn, or use a cutting torch on, the empty drum.

SECTION 14. TRANSPORT INFORMATION

Transportation Regulation: 49 CFR (USA):

UN1950, AEROSOLS, NON-FLAMMABLE, 2.2, - Limited quantity

Transportation Regulation: IMDG (Vessel):

UN1950, AEROSOLS, 2.2, - Limited quantity

Transportation Regulation: IATA (Cargo Air):

UN1950, AEROSOLS, NON-FLAMMABLE, 2.2, - Limited quantity

Transportation Regulation: IATA (Passenger Air):

UN1950, AEROSOLS, NON-FLAMMABLE, 2.2, - Limited quantity

Transportation Regulation: TDG (Canada):

UN1950, AEROSOLS, NON-FLAMMABLE, 2.2, - Limited quantity

The product as delivered to the customer conforms to packaging requirements for shipment by road under US Department of Transportation (DOT) regulations. Additional transportation classifications noted above are for reference only, and not a certification or warranty of the suitability of the packaging for shipment under these alternative transport regulations.

SAFETY DATA SHEET

ZEP FOAMING GLASS CLEANER 20N19 12CT

Version 6.1

Revision Date 10/01/2023

Print Date 01/16/2026

SECTION 15. REGULATORY INFORMATION

TSCA list : No substances are subject to a Significant New Use Rule.

No substances are subject to TSCA 12(b) export notification requirements.

EPCRA - Emergency Planning and Community Right-to-Know Act

CERCLA Reportable Quantity

This material does not contain any components with a CERCLA RQ.

SARA 304 Extremely Hazardous Substances Reportable Quantity

This material does not contain any components with a section 304 EHS RQ.

SARA 311/312 Hazards : Gases under pressure

SARA 302 : No chemicals in this material are subject to the reporting requirements of SARA Title III, Section 302.

SARA 313 : This material does not contain any chemical components with known CAS numbers that exceed the threshold (De Minimis) reporting levels established by SARA Title III, Section 313.

California Prop. 65

This product does not contain any chemicals known to State of California to cause cancer, birth defects, or any other reproductive harm.

The components of this product are reported in the following inventories:

DSL All components of this product are on the Canadian DSL
TSCA On TSCA Inventory

For information on the country notification status for other regions please contact the manufacturer's regulatory group.

Inventory Acronym and Validity Area Legend:

TSCA (USA), DSL (Canada), NDSL (Canada)

SECTION 16. OTHER INFORMATION

SAFETY DATA SHEET

ZEP FOAMING GLASS CLEANER 20N19 12CT

Version 6.1

Revision Date 10/01/2023

Print Date 01/16/2026

Further information

NFPA:

HEALTH	3
FLAMMABILITY	0
INSTABILITY	0
SPECIAL HAZARD.	

0 = not significant, 1 = Slight,
2 = Moderate, 3 = High
4 = Extreme

HMIS III:

HEALTH	3
FLAMMABILITY	0
PHYSICAL HAZARD	2

0 = not significant, 1 = Slight,
2 = Moderate, 3 = High
4 = Extreme, * = Chronic

OSHA - GHS Label Information:

Hazard pictograms



Gas cylinder

Signal word

: **Warning:**

Hazard statements

: Contains gas under pressure; may explode if heated.

Precautionary statements

:

Storage: Protect from sunlight. Store in a well-ventilated place.

Version:	6.1
Revision Date:	10/01/2023
Print Date:	01/16/2026

SAFETY DATA SHEET

ZEP FOAMING GLASS CLEANER 20N19 12CT

Version 6.1

Revision Date 10/01/2023

Print Date 01/16/2026

We believe the statements, technical information and recommendations contained herein are reliable, but they are given without warranty or guarantee of any kind. The information in this document applies to this specific material as supplied. It may not be valid for this material if it is used in combination with any other materials. Users should make their own investigations to determine the suitability and applicability of the information for their particular purposes. This SDS has been prepared by the Compliance Services organization supporting this manufacturer, supplier or distributor.