•TRUSTED QUALITY SINCE 1921•
RUST-OLEUM® SPECIALTY

RUST-OLEUM® 2X CAMOUFLAGE SPRAYS

DESCRIPTION AND USES

Rust-Oleum® 2X Camouflage Sprays are flat, non-reflective spray paint designed for use on wood, metal, and other surfaces for the purpose of creating a camouflage pattern. 2X Camouflage Sprays are formulated to include twice the solids per container for coverage on wood, metal, most plastic, wicker and more when compared to similar Rust-Oleum general purpose paints like Quick Color and Touch N' Tone. It covers surfaces with less spray passes, allowing projects to be completed faster and easier. Any angle spray feature allows you to spray in any direction, even upside down. Do not use on galvanized surfaces.

PRODUCTS

SKUS	DESCRIPTION
279175	Flat Deep Forest Green
279176	Flat Army Green
279177	Flat Khaki
279178	Flat Earth Brown
279179	Flat Black
279180	Flat Sand

PRODUCT APPLICATION

SURFACE PREPARATION

ALL SURFACES: Remove all dirt, grease, oil, salt, and chemical contaminants by washing the surface with a commercial detergent, or other suitable cleaning method. Mold and mildew must be cleaned with a chlorinated cleaner or bleach solution. Rinse with fresh water and allow to thoroughly dry.

STEEL: Scrape and wire brush or power tool clean to remove loose rust, scale, and deteriorated coatings. Use 7569838 Red Primer for sound rusted or clean metal before application of a finish coat.

PREVIOUSLY COATED: Previously coated surfaces must be sound and in good condition. Smooth, hard, or glossy surfaces should be scarified by sanding to create a surface profile.

WARNING! If you scrape, sand, or remove old paint from any surface, you may release lead paint dust. LEAD IS TOXIC. EXPOSURE TO LEAD DUST CAN CAUSE SERIOUS ILLNESS, SUCH AS BRAIN DAMAGE, ESPECIALLY IN CHILDREN. PREGNANT WOMEN SHOULD ALSO AVOID EXPOSURE. Wear a NIOSH approved respirator to control lead exposure. Clean up carefully with a HEPA vacuum and a wet mop. Before you start, find out how to protect yourself and your family by contacting the National Lead Information Hotline at 1-800-424-LEAD or log on to www.epa.gov/lead.

PRODUCT APPLICATION (cont.)

APPLICATION

Apply only when air and surface temperatures are between 50-90°F (10-32°C) and the relative humidity is below 85% to ensure proper drying. Use outdoors or in areas with good ventilation. Avoid spraying in very windy or dusty conditions. Cover surrounding area to protect from overspray. Overspray can carry a significant distance.

Shake can vigorously for one minute after the mixing ball begins to rattle. Shake often during use. Hold can 12-16" from surface and spray in a steady back-and-forth motion, slightly overlapping each stroke. Keep the can the same distance from the surface. Keep the can in motion while spraying. **Do not use near open flame.**

Apply a base coat of one color first. Then use leaves and twigs as stencils and lay them on the surface to make a random pattern. Then use three or more colors to paint stripes and patterns over the leaves and twigs.

DRY & RECOAT

Dry and recoat times are based on 70ºF and 50% relative humidity. Allow more time at cooler temperatures. Dries to touch in 20 minutes, to handle in 1 hour, and is fully dry in 24 hours. Apply a second coat or clear coat within 1 hour or after 24 hours. Apply clear in 2-3 light coats a few minutes apart.

NOTE: On plastic maximum paint adhesion and durability is achieved in 5-7 days.

CLEAN-UP

Wipe off tip before storing. Clean-up wet paint with xylene or mineral spirits. Properly discard empty container. Do not burn or place in home trash compactor.

CLOGGING

If the value clogs, twist and pull off spray tip and rinse in a solvent such as mineral spirits. Do not insert any object into can valve opening.

Form: GDH-917
Rev.: 073126

• TRUSTED QUALITY SINCE 1921 •
RUST-OLEUM® SPECIALTY

RUST-OLEUM® 2X CAMOUFLAGE SPRAYS

PHYSICAL PROPERTIES

		2X CAMOUFLAGE SPRAYS
Resin Type		Acrylic Modified Alkyd
Fill Weight		12 oz.
MIR		0.80 Max
Recommended Dry Film Thickness (DFT) per Coat		1.0-2.0 mils
Estimated Practical Coverage at Recommended DFT (assumes 15% material loss)		Approximately 10-12 sq.ft./can Actual coverage may vary depending on surface and environmental conditions and application methods
Dry Times at 70-80°F (21-27°C) and 50% Relative Humidity	**Touch**	20 minutes
	Handle	1 hour
	Recoat	Within 1 hour or after 24 hours
Dry Heat Resistance		200°F (93°C)
Shelf Life		5 years
Flash Point		-156°F (-104°C)
Safety Information		For additional information, see SDS

Calculated values are shown and may vary from the actual manufactured material.

The technical data and suggestions for use contained herein are correct to the best of our knowledge, and offered in good faith. The statements of this literature do not constitute a warranty, express, or implied, as to the performance of these products. As conditions and use of our materials are beyond our control, we can guarantee these products only to conform to our standards of quality, and our liability, if any, will be limited to replacement of defective materials. All technical information is subject to change without notice.