

Flexible, soft and skin friendly synthetic glove, palm-dipped with nitrile foam.

TEGERA® 884A

Learn more

TOUCH SCREEN FUNCTION AND GREAT GRIP

Flexible and soft knitted 15 gg synthetic glove, palm-dipped with nitrile foam and nitrile dots for great grip. Touch screen function. Perfect for precision work, fine assembly work, inspection work, and other kinds of light weight work in dry and moist environments. Withstands contact heat up to 100°C/212°F. Skin friendly with Derma-test and Oeko-Tex certificate.

CHARACTERISTICS

- Good fingertip sensitivity
- Flexible
- Very durable
- Good grip
- Comfortable

FUNCTIONS

- Withstands contact heat up to 100°C
- For touchscreen

ORIGINAL EXCELLENT 2021 dermatest dermatest-guarantee.com

OEKO TEX® STANDARD 100 SE 14-214 RISE

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.

PREVENTS RISK OF

Abrasion injuries, Grazes, Scratches, lacerations, Contact with dirt

PRIMARY ENVIRONMENTS OF USE

Dry environments, Moist environments, Dirty environments

PRIMARY AREAS OF USE

Agricultural work, Airport work, Assembly, Building and construction, Carpentry, Construction, Electrical installation, Engineering, Fine assembly, Gardening, HVAC installation, Inspection work, Installation work, Machine driving, Machine operating, Painting, Repair work, Soil preparation, Transport work, Warehouse work

PRIMARY INDUSTRIES OF USE

Agriculture, forestry and fishing, Automotive manufacturing, Automotive repair and maintenance, Basic metals manufacturing, Building and construction, Electrical equipment manufacturing, Electricity and gas supply, Machinery and equipment manufacturing, Metal manufacturing and fabrication, Mining and quarrying, Rubber and plastics manufacturing, Transport equipment manufacturing, Transportation and logistics, Warehousing

TYPE OF WORK

Light weight

SPECIFICATION

TYPE Assembly gloves, Heat protection gloves, Precision work gloves
CATEGORY Cat. II
KNITTING GAUGE (GG) 15
LINING MATERIAL Nylon, Spandex
LENGTH 220-260 mm
DEXTERITY 5
GRIP DESIGN Dots
COLOUR Black
PAIRS PER: BUNDLE/CARTON 12/120
DISPLAY TYPE Hook with hangtag
DIPPING Palm-dipped
DIPPING MATERIAL Nitrile foam, Nitrile-dots
CUFF STYLE Knitwrist cuff
CUFF MATERIAL Textile
CUT RESISTANCE (EN ISO 13997) Cut resistance level A
INNER MATERIAL SPECIFICATION Nylon, Natural latex, Elastane
OUTER MATERIAL SPECIFICATION Nitrile

COMPLIANCE

CE Cat. II

EAC TP TC 019:2011

EN ISO 21420:2020

EN 388:2016+A1:2018 4131A

EN 407:2020 (No flame protection) X1XXXX

ANSI 4 ABR

Contact heat rating valid for palm area only

FEATURES

For touchscreen

SIZE		ARTICLE NUMBER	EAN
5	XXS	884A-5	7340118381282
6	XS	884A-6	7340118381435
7	S	884A-7	7340118322254
8	M	884A-8	7340118322261
9	L	884A-9	7340118322278
10	XL	884A-10	7340118322223
11	XXL	884A-11	7340118322230
12	3XL	884A-12	7340118322247

ejendals
Limavägen 28, SE-793 32 Leksand, Sweden
Phone +46 (0) 247 360 00 | info@ejendals.com | order@ejendals.com

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.