ABB BALDOR RELIANCE

Customer information packet

VXM14242T-5

2HP, 1765RPM, 3PH, 60HZ, 145TC, 3528M, XPFC, F1
Class - CLI GP D; CLII GP F,G
Division - Division I

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/5/2026 9:27:00 AM

Specifications

Enclosure	XPFC
Frame	145TC
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Class and Group	CLI GP D; CLII GP F,G
Haz Area Division	Division I
Motor Letter Type	Three Phase
Output @ Frequency	2.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	575.0 V @ 60 HZ
Agency Approvals	CSA EEV
	UL
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	No Mounting
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	2.150 A @ 575.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	86.5 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Shaft Indicator	None
Heater Indicator	No Heater
High Voltage Full Load Amps	2.2 a
Insulation Class	F
Inverter Code	Not Inverter
KVA Code	L

Part Detail

Revision	E
Type	AC
Mech. spec.	35E380
Base	
Status	PRD/A
Elec. spec.	35WGZ823
Layout	35LYE380
Eff. date	03-19-2026
CD Diagram	CD0006
Poles	04
Leads	3#18
Proprietary	False
Created date	02-23-2023

Lifting Lugs	No Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Max Speed	2700 rpm
Motor Lead Quantity/Wire Size	3 @ 18 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3540M
Mounting Arrangement	F1
Number of Poles	4
Overall Length	13.84 IN
Power Factor	81
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	C-Face
Pulley Shaft Indicator	Standard
Rodent Screen	None
Service Factor	1.00
Shaft Diameter	0.875 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Speed	1765 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	Normally Closed Thermostat
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP0887XPSLEV											
NO.				**CC**	010A						
S/N				**TEMP CODE**	T3C						
SPEC.	35E380Z823			**INV.TYPE**	PWM						
CAT.NO.	VXM14242T-5			**C HP FR**	60	**C HP TO**	90				
HP	2			**CT HZ FROM**	6			**CT HZ TO**	60		
VOLTS	575			**VT HZ FROM**	6			**VT HZ TO**	60		
AMPS	2.15		**MAG CUR**	1.15							
RPM	1765		**MX RPM**	2700							
HZ	60	**PH**	3	**CL**	F	**NOM.EFF.**	86.5				
SER.F.	1.00	**DES**	B	**SL HZ**	1.17	**WK2**	0.202				
FRAME	145TC	**RATING**	40C AMB-CONT								
	NEMA MG-1 PART 5, IP54										
	1.15 SF ON SINE WAVE										

AC Induction Motor Performance Data
Record # 88444
Preliminary Data Sheet

Winding: 35WGZ823-R001	**Type:** 3528M	**Enclosure:** TEFC

Nameplate Data				**575 V, 60 Hz: Single Voltage Motor**	
Rated Output (HP)			2	**Full Load Torque**	5.95 LB-FT
Volts			575	**Start Configuration**	direct on line
Full Load Amps			2.15	**Breakdown Torque**	22.1 LB-FT
R.P.M.			1765	**Pull-up Torque**	13.1 LB-FT
Hz	60	**Phase**	3	**Locked-rotor Torque**	15.85 LB-FT
NEMA Design Code	B	**KVA Code**	K	**Starting Current**	18.31 A
Service Factor (S.F.)			1.15	**No-load Current**	1.15 A
NEMA Nom. Eff.	86.5	**Power Factor**	81	**Line-line Res. @ 25ºC**	15.5 Ω
Rating - Duty			40C AMB-CONT	**Temp. Rise @ Rated Load**	81°C
S.F. Amps			2.45	**Temp. Rise @ S.F. Load**	98°C
				Locked-rotor Power Factor	57
				Rotor inertia	0.202 lb-ft²

Load Characteristics 575 V, 60 Hz, 2 HP

% of Rated Load	**25**	**50**	**75**	**100**	**125**	**150**	**S.F.**
Power Factor	39	60	73	80	84	86	82
Efficiency	80.1	86.2	87.3	86.9	85.6	83.9	86.1
Speed	1791	1783	1773	1765	1755	1742	1759
Line amperes	1.23	1.45	1.76	2.15	2.62	3.1	2.43


ABB Motors and Mechanical Inc.

WINDING # 35WGZ823


2 HP 3 PH 60 HZ 1765 RPM 575 V 3528M

Typical performance - not guaranteed values.

TORQUES(LB-FT): PO=22.1 PU=13.1 LR=15.85 LRA=18.31





11/5/2026 ACPERF, record # 88444


35LYE380
510-520 = 14.33
521-528 =15.21
529-535 = 16.09
536-546 = 17.47
4.72
2.25
.13
2.12
.12
.19 KEY
1.38 LONG
Ø7.19
X-PROOF NAMEPLATE
BALDOR
PT. NO. 35CB3500
Ø6.45
Ø4.500
4.497
.8750
.8745
6.71
6.92
45°
45°
LEAD HOLE
.75 NPT
5.33
4 HOLES
.38-16 TAP
.56 DEEP ON
5.88 DIA. B.C.
.09
.0015 MAX
CLEARANCE
.006
.004
1.00
MIN
DRIVE END DETAIL
CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT THE PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION
REV. DESC: CONVERT AUTOCAD DRW TO SWD DRW
REV: M
VERSION: 04
REVISED: 01:18:59 04/20/2023
TDR: 000001207032
MODEL NO. 35LYE380
REF: -
BY: ENALEM0
B
BALDOR - RELIANCE®
STD VERT 143-5TC XPFC X35M CLI GP D, CLII GP F&G
35LYE380


CD0006

TYPICAL WYE–CONNECTED MOTOR





TYPICAL DELTA–CONNECTED MOTOR



NOTES:

1. THREE LEAD MOTOR MAY BE EITHER WYE CONNECTED OR DELTA CONNECTED.
2. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
3. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
4. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY VARY.
5. LEAD COLORS ARE OPTIONAL. LEADS MUST BE NUMBERED AS SHOWN.

CD0006

REV. DESC: ADD CLASS CONN00000007		
REV. LTR: E	VERSION: 01	TDR: 000001099922
FILE: \AAA\00005\141	REVISED: 10:24:49 02/19/2019	BY: ENBRIR0
MTL: –		

BALDOR - RELIANCE®

3PH, SV, 3 LEADS, WYE OR DELTA CONNECTED

SH 1 of 1