



K2A31U2N, AL Universal Terminal, 2-Conductor, 2-Hole

By Burndy
Catalog # [K2A31U2N](#)



2-Conductor, 2-Hole, 1/2" Stud, 1.75" Spacing, #6 AWG-350 kcmil, Tin Plated

Features

- Dual rated panelboard lugs
- Constructed from high strength, extruded aluminum alloy
- Electro tin-plated to provide low contact resistance

Application

For Aluminum and Copper Conductors

Specifications

Buy American Compliant	Yes
EU RoHS Indicator	Yes
Buy America(n) Qualified	• Buy America Compliant (All status valid till December 2026) • Buy American Act Compliant (All status valid till December 2026) • BABA Compliant (All status valid till December 2026)
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
Certification - UL Listed Direct Burial	No
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - AL Str Size	• 6 AWG • 4 AWG • 3 AWG • 2 AWG • 1 AWG • 1/0 AWG • 2/0 AWG • 3/0 AWG • 4/0 AWG • 250 kcmil • 266 kcmil • 300 kcmil • 336 kcmil • 350 kcmil
Conductor - AL Str Size Range	6 Str.- 350 Kcmil

Conductor - Copper Str Size	• 6 AWG • 5 AWG • 4 AWG • 3 AWG • 2 AWG • 1 AWG • 1/0 • 2/0 AWG • 3/0 AWG • 4/0 AWG • 250 kcmil • 300 kcmil • 350 kcmil
Conductor Size	6 AWG-350 KCMIL
Number Of Conductors	2
Conductor Type	• AL C Str-Size • CU C Str-Size
Conductor - Copper Str Size Range	6 Str.- 350 Kcmil

Configuration

Physical Attribute - Number of Holes	2
Connector Type	Parallel Set-Screw

Dimensions

Dimension - Pad Width inch	2.31 in
Package Height	3.400 in
Dimension - Height mm	35.3 mm
Dimension - Height inch	1.39 in
Dimension - Height fraction	1.4 in
Package Weight	1.610 lb.
Package Length	5.500 in
Package Width	4.750 in
Dimension - L Length Overall mm	114 mm
Dimension - Width fraction	2-31/100 in
Dimension - Hole Size mm	14 mm
Dimension - Hole Size inch	0.56 in
Dimension - Screw Size inch	3/8
Dimension - Stud Size inch	1/2 in
Dimension - Bolt Hole Size inch	0.50 in
Dimension - Bolt Size fraction	1/2
Dimension - Width mm	59 mm
Dimension - Width inch	2.31 in
Dimension - D inch	3.00 in

Dimension - N inch	0.63 in	Plating Type	Tin plated
Dimension - Length Overall inch	4.50 in	UPC 12 Digit	781810600160
		Hardware Type	3/8 UNC Slotted Set Screw
		UPC 14 Digit GTIN	00781810600160
Force Related		Logistics	
Installation Torque Recommended in-lb	275 LBS/in	Minimum Pack Quantity	1
		Pallet Quantity	1728
		Carton Quantity	54
General		Operational	
Material - Hardware	Aluminum	Temperature Rating	194
Physical Attribute - Screw Type	Slot		
Plated	N		
Sub Brand	UNIVERSAL TERM		
UPC	781810600160		
Type	Bolted Lugs & Terminals		
Material	Aluminum	Product Assets	
		Catalog [English]	



A Hubbell brand